





NOTE:
 1. Operating Force: 240gf±80gf
 2. Travel : 2.4±0.2mm



Circuit Diagram



NO.	Operating Type	Part No.
1	Push To Lock	K8-2213A-L1
2	Push No Lock	K8-2213A-N1
3	Push No Sound No Lock	K8-2213A-NN

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑧	Terminal	—	6	Brass strip	Plating silver	—
⑦	Contact	—	2	Phosphor bronze	Plating silver	—
⑥	Securing glue	—	2	PA66	Black	—
⑤	Spring	—	1	SUS	Natural	—
④	Base	—	1	PBT	Black	—
③	Crochet Needle	—	1	SUS	Natural	—
②	Cover	—	1	POM	Black	—
①	Knob	—	1	POM	White	—

APPROVALS		DATE		ELECTRONICS CO.,LTD			
DRAWN	CHECKED	DATE	TITLE:	PUSHBUTTON SWITCHS			
J.X.Zhang		2013/10/12					
APPROVALS		DATE		PART NO.			
TOLERANCES ARE		30 ± 0.15	± 0.30	ANGLE	UNIT:	SCALE:	PROJ:
$10 \sim 30$	± 0.20	$5 \sim 10$	± 0.15	$\pm 2^\circ$	mm	1:1	
~ 5	± 0.10	± 0.10			DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW

CHANGE.	CHECK.	APPRO.