

Approved by:
Checked by:
Issued by:

# Surface-Acoustic-Wave Resonator SPECIFICATION

LR433T2

SMD 7.5X3.5



433.92MHz SAW Resonator

433.92 MHz SAW Resonator

Low Series Resistance Quartz Stability Rugged, Hermetic, Low-profile SMD7.5X3.5 Case

The R433T2 is a true one-port, surface-acoustic-wave (SAW) resonator in low-profile SMD case. It provides reliable, fundamental-mode. quartz frequency stabilization of fixed-frequency transmitters operating at 433.92 MHz. The R433T2 is designed specifically for remote-controls and wireless security transmitters. Operating in the Europe underETS11-ETS 300 220 and in Germany under FTZ 17 TR 2100.

## **Absolute Maximum Ratings**

Rating	Value	Units
CW RF Power Dissipation (See Typical Test Circuit)	+0	dBm
DC Voltage Between Any Two Pins (Observe ESD Precautions)	±30	VDC
Case Temperature	-40 to +85	°C

#### **Electrical Characteristics**

	Characteristics	Sym	Notes	Minimum	Typical	Maximum	Units					
Center Frequency (+25°C) Absolute Frequency		f <sub>c</sub>		433.845		433.995	MHz					
	Tolerance from 433.920MHz	Δ f <sub>c</sub>	2,3,4,5			±75	KHz					
Insertion Loss		IL	2,5,6		1.5	2.0	dB					
Quality Factor	Unloaded Q	Q <sub>U</sub>			12.800							
	50 $\Omega$ loaded Q	$Q_L$	5,6,7		2.000							
Temperature Stability	Turnover Temperature	To		24	39	54	$^{\circ}$					
	Turnover Frequency	f <sub>O</sub>	5,7,8		f <sub>c</sub> +2.7		KHz					
	Frequency Temperature Coefficient	FTC			0.037		ppm/°C²					
Frequency Aging	Absolute Value during the First Year	If <sub>A</sub> I	1		≦10		ppm/y τ					
DC Insulation Resistance b		5	1.0			ΜΩ						
RF Equivalent RLC Model	R <sub>M</sub>			18	26	Ω						
Motional Inductance		L <sub>M</sub>	570		86.0075		μН					
	Motional Capacitance	См	5,7,9		1.56417		pF					
	Pin 1 to Pin 2 Static Capacitance	Co	5,6,9	1.7	2.0	2.3	pF					
	Transducer Static Capacitance	C <sub>P</sub>	5,6,7,9		1.7		pF					
Test Fixture Shunt Inductar	Test Fixture Shunt Inductance				78		nH					
Lid Symbolization (in Additi	Lid Symbolization (in Addition to Lot and/or Date Code				LR433T2							

### CAUTION: electrostatic Sensitive Device, Observe precautions for handling.

## Notes:

- 5. Frequency aging is the change in f<sub>C</sub> with time and is specified at +65°C or less. Aging may exceed the specification for prolonged temperatures above +65°C. Typically, aging is greatest the first year after manufacture, decreasing significantly in subsequent years.
- 6. The center frequency,  $f_c$ , is measured at the minimum insertion loss point,  $IL_{MIN}$  with the resonator in the  $50\,\Omega$  test system(VSWR  $\leqq$  1.2:1).The shunt inductance,  $L_{TEST}$ , is turned for parallel resonator with  $C_O$  at  $f_c$ . Typically,  $f_{OSCILLATOR}$  or  $f_{TRANSMITTER}$  is less than the resonator  $f_c$ .
- One or more of following United States patents apply:4,454,488 and 4,616,197 and others pending.
- Typically, equipment designs utilizing this device require emissions testing and government approval, which is the responsibility of the equipment manufacturer.
- Unless noted otherwise, case temperature T<sub>c</sub>=25 °C ±2 °C.
- The design, manufacturing process, and specifications of this device are subject to change without notice.

- 2. Derived mathematically from one or more of the following directly measured parameter:  $f_c$ , IL, 3dB bandwidth,  $f_c$  versus  $T_c$ , and  $C_o$ .
- Turnover temperature, T<sub>o</sub>, is the temperature of maximum (or turnover) frequency, f<sub>o</sub>. The nominal frequency at any case temperature, T<sub>c</sub>. may be calculated from:
  - f=f\_o [1-FTC(T\_o-T\_c)^2]. Typically, oscillator T\_o is 20  $^\circ\! C$  less than the specified resonator T\_o.
- 4. This equivalent RLC model approximates resonators performance near the resonant frequency and is provided for reference only. The capacitance Co is the static (non-motional) capacitance between pin 1 and pin 2 measured at low frequency (10MHz) with a capacitance meter. The measurement includes case parasitic capacitance with a floating case. For usual grounded case applications (with ground connected to either pin 1 or pin 2 and to the case), add approximately 0.25pF to Co.

## **Electrical Connections**

This one-port, two-terminal SAW resonator is bi-directional. The terminals are interchangeable with the exception of circuit board layout.

Pin	Connection
1	Terminal 1
2	Terminal 2




# **Typical Test Circuit**

The test circuit inductor,  $L_{\text{TEST}},$  is turn to resonate with the static capacitance,  $C_o$  at  $F_c.$ 


**Electrical Test:** 

#### **Power Test:**




# **Typical Application Circuits**

**Typical Low-Power Transmitter Application:** 




Typical Local Oscillator Application:




# **Temperature Characteristics**

The curve shown on the right accounts for resonator contribution only and does not include oscillator temperature characteristics.




## **Equivalent LC Model**


The following equivalent LC model is valid near resonance:



## Case Design



## **Frequency Response**



433.92MHz SAW Resonator

# **Taping structure**

Component load: per 7' reel 2500pcs or per13' reel 8000pcs

ITEM	W	Αo	Во	Κo	E	F	Do	D1	Po	P1	P2	Т	
DIM	16.0	3.40	7.85	2.00	1.75	7.50	Ø1.50	Ø1.50	4.00	4.00	2.00	0. 30	PCS/R
TOLE	+0.30 -0.30	+0.10 -0.00	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.00	+0.25 -0.00	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.05 -0.05	M/R

