


RS2AF THRU RS2MF

SURFACE MOUNT FAST RECOVERY RECTIFIER

Reverse Voltage - 50 to 1000 Volts Forward Current -2.0 Ampere

SMAF



Dimensions in inches and (millimeters)

FEATURES

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- For surface mounted applications
- ◆ Fast switching for high efficiency
- Low reverse leakage
- ◆ Built-in strain relief, ideal for automated placement
- High forward surge current capability
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- Glass passivated chip junction

MECHANICAL DATA

Case: JEDEC SMAF molded plastic body over passivated chip **Terminals**: Solder plated, solderable per MIL-STD-750,

Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.0018 ounce, 0.064 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz resistive or inductive load for capacitive

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

1	I							
SYMBOLS	RS2AF	RS2BF	RS2DF	RS2GF	RS2JF	RS2KF	RS2MF	UNITS
Vrrm	50	100	200	400	600	800	1000	VOLTS
VRMS	35	70	140	280	420	560	700	VOLTS
VDC	50	100	200	400	600	800	1000	VOLTS
l(AV)				2.0				Amp
lfsm	50.0						Amps	
VF	1.3						Volts	
lr	5.0 50.0						μΑ	
trr	150 250 500				ns			
Cı	50.0						pF	
Reja	20.0						°C/W	
TJ.Tstg	-50 to +150						°C	
	VRRM VRMS VDC I(AV) IFSM VF IR CJ RθJA	VRRM 50 VRMS 35 VDC 50 I(AV) IFSM VF IR CJ R@JA	V _{RRM} 50 100 V _{RMS} 35 70 V _{DC} 50 100 I(AV) IFSM VF IR C _J RθJA	V _{RRM} 50 100 200 V _{RMS} 35 70 140 V _{DC} 50 100 200 I(AV) IFSM VF IR trr 150 CJ RθJA	V _{RRM} 50 100 200 400 V _{RMS} 35 70 140 280 V _{DC} 50 100 200 400 I(AV) 2.0 IFSM 50.0 VF 1.3 IR 5.0 50.0 Trr 150 CJ 50.0 RθJA 20.0	VRRM 50 100 200 400 600 VRMS 35 70 140 280 420 Vpc 50 100 200 400 600 I(AV) 2.0 IFSM 50.0 VF 1.3 IR 50.0 50.0 50.0 CJ 50.0 RθJA 20.0	V _{RRM} 50 100 200 400 600 800 V _{RMS} 35 70 140 280 420 560 V _{DC} 50 100 200 400 600 800 I(AV) 2.0 IFSM 50.0 VF 1.3 IR 50.0 50.0 250 500 CJ 50.0 R@JA 20.0	V _{RRM} 50 100 200 400 600 800 1000 V _{RMS} 35 70 140 280 420 560 700 V _{DC} 50 100 200 400 600 800 1000 I(AV) 2.0 IFSM 50.0 VF 1.3 5.0 50.0 IR 50.0 50.0 50.0 CJ 50.0 50.0 250 500 R@JA 20.0 20.0 600 800 1000


Note:1.Reverse recovery condition IF=0.5A,IR=1.0A,Irr=0.25A

2.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3.P.C.B. mounted with 0.2x0.2"(5.0x5.0mm) copper pad areas



RATINGS AND CHARACTERISTIC CURVES RS2AF THRU RS2MF



The cruve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!

