



## P2803NVG

### N&P-Channel Enhancement Mode MOSFET

#### PRODUCT SUMMARY

$V_{(BR)DSS}$	$R_{DS(ON)}$	$I_D$	Channel
30V	27.5m $\Omega$ @ $V_{GS} = 4.5V$	7A	N
-30V	34m $\Omega$ @ $V_{GS} = -4.5V$	-6A	P



#### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ C$ Unless Otherwise Noted)

PARAMETERS/TEST CONDITIONS	SYMBOL	CH.	LIMITS	UNITS
Drain-Source Voltage	$V_{DS}$	N	30	V
		P	-30	
Gate-Source Voltage	$V_{GS}$	N	$\pm 20$	
		P	$\pm 20$	
Continuous Drain Current	$I_D$	N	7	A
		P	-6	
		N	6	
		P	-5	
Pulsed Drain Current <sup>1</sup>	$I_{DM}$	N	20	
		P	-20	
Power Dissipation	$P_D$	N	2	W
		P	2	
		N	1.3	
		P	1.3	
Junction & Storage Temperature Range	$T_J, T_{STG}$	-55 to 150		°C

THERMAL RESISTANCE	SYMBOL	TYPICAL	MAXIMUM	UNITS
Junction-to-Ambient	$R_{QJA}$		62.5	°C / W

<sup>1</sup>Pulse width limited by maximum junction temperature.

<sup>2</sup>Duty cycle  $\leq 1\%$

## P2803NVG

### N&P-Channel Enhancement Mode MOSFET

#### ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ , Unless Otherwise Noted)

PARAMETER	SYMBOL	TEST CONDITIONS	LIMITS			UNIT
			MIN	TYP	MAX	
<b>STATIC</b>						
Drain-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0\text{V}, I_D = 250\mu\text{A}$	N	30		V
		$V_{\text{GS}} = 0\text{V}, I_D = -250\mu\text{A}$	P	-30		
Gate Threshold Voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{DS}} = V_{\text{GS}}, I_D = 250\mu\text{A}$	N	1.0	1.5	2.5
		$V_{\text{DS}} = V_{\text{GS}}, I_D = -250\mu\text{A}$	P	-1.0	-1.5	-2.5
Gate-Body Leakage	$I_{\text{GSS}}$	$V_{\text{DS}} = 0\text{V}, V_{\text{GS}} = \pm 20\text{V}$	N			$\pm 100$
		$V_{\text{DS}} = 0\text{V}, V_{\text{GS}} = \pm 20\text{V}$	P			$\pm 100$
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{\text{DS}} = 24\text{V}, V_{\text{GS}} = 0\text{V}$	N		1	$\mu\text{A}$
		$V_{\text{DS}} = -24\text{V}, V_{\text{GS}} = 0\text{V}$	P		-1	
		$V_{\text{DS}} = 20\text{V}, V_{\text{GS}} = 0\text{V}, T_J = 55^\circ\text{C}$	N		10	
		$V_{\text{DS}} = -20\text{V}, V_{\text{GS}} = 0\text{V}, T_J = 55^\circ\text{C}$	P		-10	
		$V_{\text{DS}} = 5\text{V}, V_{\text{GS}} = 10\text{V}$	N	20		A
On-State Drain Current <sup>1</sup>	$I_{\text{D}(\text{ON})}$	$V_{\text{DS}} = -5\text{V}, V_{\text{GS}} = -10\text{V}$	P	-20		
		$V_{\text{GS}} = 4.5\text{V}, I_D = 6\text{A}$	N		30	40
Drain-Source On-State Resistance <sup>1</sup>	$R_{\text{DS}(\text{ON})}$	$V_{\text{GS}} = -4.5\text{V}, I_D = -5\text{A}$	P		43.5	56
		$V_{\text{GS}} = 10\text{V}, I_D = 7\text{A}$	N		20.5	27.5
		$V_{\text{GS}} = -10\text{V}, I_D = -6\text{A}$	P		27.5	34
		$V_{\text{DS}} = 5\text{V}, I_D = 7\text{A}$	N		16	S
Forward Transconductance <sup>1</sup>	$g_{\text{fs}}$	$V_{\text{DS}} = -5\text{V}, I_D = -6\text{A}$	P		13	

<b>DYNAMIC</b>						
Input Capacitance	$C_{\text{iss}}$	N-Channel $V_{\text{GS}} = 0\text{V}, V_{\text{DS}} = 15\text{V}, f = 1\text{MHz}$  P-Channel $V_{\text{GS}} = 0\text{V}, V_{\text{DS}} = -15\text{V}, f = 1\text{MHz}$	N		680	pF
Output Capacitance			P		920	
Reverse Transfer Capacitance			N		105	
Total Gate Charge <sup>2</sup>			P		190	
Gate-Source Charge <sup>2</sup>			N		75	
Gate-Drain Charge <sup>2</sup>			P		120	
	$Q_g$	N-Channel $V_{\text{DS}} = 0.5V_{(\text{BR})\text{DSS}}, V_{\text{GS}} = 10\text{V}, I_D = 7\text{A}$  P-Channel $V_{\text{DS}} = 0.5V_{(\text{BR})\text{DSS}}, V_{\text{GS}} = -10\text{V}, I_D = -6\text{A}$	N		14	nC
			P		18.5	
			N		1.9	
			P		2.7	
			N		3.3	
			P		4.5	

## P2803NVG

### N&P-Channel Enhancement Mode MOSFET

DYNAMIC						
Turn-On Delay Time <sup>2</sup>	$t_{d(on)}$	N-Channel $V_{DD} = 10V$ $I_D \geq 1A, V_{GS} = 10V, R_{GEN} = 3\Omega$	N		4.6	7
Rise Time <sup>2</sup>	$t_r$		P		7.7	11.5
Turn-Off Delay Time <sup>2</sup>	$t_{d(off)}$		N		4	6
Fall Time <sup>2</sup>	$t_f$		P		5.7	8.5
			N		20	30
			P		20	30
			N		5	8
			P		9.5	14
SOURCE-DRAIN DIODE RATINGS AND CHARACTERISTICS ( $T_J = 25^\circ C$ )						
Continuous Current	$I_S$		N			1.3
Pulsed Current <sup>3</sup>	$I_{SM}$		P			-1.3
Forward Voltage <sup>1</sup>	$V_{SD}$	$I_F = 1A, V_{GS} = 0V$ $I_F = -1A, V_{GS} = 0V$	N			2.6
			P			-2.6
			N			1
			P			-1

<sup>1</sup>Pulse test : Pulse Width  $\leq 300 \mu sec$ , Duty Cycle  $\leq 2\%$ .







<sup>2</sup>Independent of operating temperature.

<sup>3</sup>Pulse width limited by maximum junction temperature.

## P2803NVG





### N&P-Channel Enhancement Mode MOSFET

#### N-CHANNEL



## P2803NVG







### N&P-Channel Enhancement Mode MOSFET



## P2803NVG






### N&P-Channel Enhancement Mode MOSFET

#### P-CHANNEL



## P2803NVG

### N&P-Channel Enhancement Mode MOSFET



## P2803NVG

### N&P-Channel Enhancement Mode MOSFET

#### Package Dimension

#### SOP-8 MECHANICAL DATA

Dimension	mm			Dimension	mm		
	Min.	Typ.	Max.		Min.	Typ.	Max.
A	4.8	4.9	5.0	H	0.4	0.6	0.93
B	3.8	3.9	4.0	I	0.19	0.21	0.25
C	5.79	6.0	6.2	J	0.25	0.375	0.5
D	0.33	0.4	0.51	K	0°	3°	18°
E	1.25	1.27	1.29				
F	1.1	1.3	1.65				
G	0.05	0.15	0.25				

