

Dual Transient Voltage Suppressors Array for ESD Protection

The LGSOT05CLT1G is a dual monolithic voltage suppressor designed to protect components which are connected to data and transmission lines against ESD. It clamps the voltage just above the logic level supply for positive transients, and to a diode drop below ground for negative transients. It can also work as bidirectional suppressor by connecting only pin1 and 2.

● APPLICATIONS

- 1) Computers, Printers
- 2) Communication systems

● FEATURES

- 1) 2 Unidirectional Transil functions
- 2) Low leakage current: $I_R \text{ max} < 20 \mu\text{A}$ at V_{RM}
- 3) 300W peak pulse power(8/20μs)
- 4) Transient protection for data lines as per
IEC61000-4-2(ESD) 15kV(air) 8kV(contact)
IEC61000-4-5(Lightning) see IPPM below
- 5) We declare that the material of product compliant with
RoHS requirements and Halogen Free.


● DEVICE MARKING AND RESISTOR VALUES

Device	Marking	Shipping
LGSOT05CLT1G	05C	3000/Tape&Reel
LGSOT05CLT3G	05C	10000/Tape&Reel


● ABSOLUTE RATINGS($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Limits	Unit
IEC 61000-4-2 (ESD) Contact Air		± 8	kV
		± 15	
Peak Pulse Power ($t_p = 8/20\mu\text{s}$)	PPP	300	W
Maximum Junction Temperature	T_J	150	$^\circ\text{C}$
Storage temperature	T_{stg}	-55 ~ +150	$^\circ\text{C}$
Operating Temperature Range	T_{OP}	-40 ~ +125	$^\circ\text{C}$
Lead Solder Temperature - Maximum (10 Second Duration)	T_L	260	$^\circ\text{C}$

LGSOT05CLT1G



LGSOT05CLT1G



Electrical Parameter

Symbol	Parameter
V_{RM}	Stand-off voltage
V_{BR}	Breakdown voltage
V_{CL}	Clamping voltage
I_{RM}	Leakage current
I_{PPM}	Peak pulse current

●ELECTRICAL CHARACTERISTICS (Ta= 25°C)

Device	VRWM (V)	IR (u A) @VRWM	VBR (V) @ IT (Note 1)	IT	Vc (V) @Ipp = 1 A	Vc (V) @Ipp = 5A	I _{PP} (A) @tp=8/20μs	C (pF)
	Max	Max	Min	mA	Max	Max	Max	Max
LGSOT05CLT1G	5	5	6	1	9.8	12.5	17	220

1. VBR is measured with a pulse test current IT at an ambient temperature of 25°C.

LGSOT05CLT1G

ELRCTIRCAL CHARACTERISTICS CURVES




Fig 1. Forward character




Fig 2. Reverse character





Fig 3. Capacitance character

LGSOT05CLT1G

SOT-23

NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M,1982
2. CONTROLLING DIMENSION: INCH.



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.1102	0.1197	2.80	3.04
B	0.0472	0.0551	1.20	1.40
C	0.0350	0.0440	0.89	1.11
D	0.0150	0.0200	0.37	0.50
G	0.0701	0.0807	1.78	2.04
H	0.0005	0.0040	0.013	0.100
J	0.0034	0.0070	0.085	0.177
K	0.0140	0.0285	0.35	0.69
L	0.0350	0.0401	0.89	1.02
S	0.0830	0.1039	2.10	2.64
V	0.0177	0.0236	0.45	0.60

