


GENERAL PURPOSE APPLICATION.
DPAK FOR SURFACE MOUNT APPLICATIONS.

FEATURES

- Low Collector Saturation Voltage
: $V_{CE(sat)}=1.0V(\text{Max.})$ at $I_C=2A, I_B=0.2A$.
- Straight Lead (IPAK, "L" Suffix)
- Complementary to KTA1040D/L.

MAXIMUM RATING (Ta=25)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V_{CBO}	60	V
Collector-Emitter Voltage	V_{CEO}	60	V
Emitter-Base Voltage	V_{EBO}	7	V
Collector Current	I_C	3	A
Base Current	I_B	0.5	A
Collector Power Dissipation	P_C	Ta=25	1.0
		Tc=25	20
Junction Temperature	T_j	150	
Storage Temperature Range	T_{stg}	-55 150	



ELECTRICAL CHARACTERISTICS (Ta=25)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current	I_{CBO}	$V_{CB}=60V, I_E=0$	-	-	100	μA
Emitter Cut-off Current	I_{EBO}	$V_{EB}=7V, I_C=0$	-	-	100	μA
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C=50mA, I_B=0$	60	-	-	V
DC Current Gain	h_{FE} (Note)	$V_{CE}=5V, I_C=0.5A$	100	-	300	-
Collector Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=2A, I_B=0.2A$	-	0.5	1.0	V
Base-Emitter Voltage	V_{BE}	$V_{CE}=5V, I_C=0.5A$	-	0.7	1.0	V
Transition Frequency	f_T	$V_{CE}=5V, I_C=0.5A$	-	30	-	MHz
Collector Output Capacitance	C_{ob}	$V_{CB}=10V, I_E=0, f=1MHz$	-	35	-	pF
Switching Time	Turn-on Time	t_{on}	-	0.65	-	μs
	Storage Time	t_{stg}	-	1.3	-	
	Fall Time	t_f	-	0.65	-	

Note : h_{FE} Classification Y:100~200, GR:150~300.

KTC2020D

