


# 520 Series Metric OMNI-BLOK® Molded Base Fuse Block for 5×20mm Fuses





#### **Agency Approval**

Agency	Agency File Number		
<b>"17</b>	E14721		
<b>(</b>	7316		
	97121		

### **Additional Information**







#### **Compatible Fuse** 5×20mm Fuses Sizes The metric Omni-Blok® fuse block, for 5×20mm size fuses, is a low profile design that is available with a choice of solder type terminals, NEMA style QC terminals, or PC board mountable terminals. Each of these designs has tin plated brass terminals. A unique Description design feature provides self-alignment of the clips to the fuse caps. This feature, plus a one-piece clip/terminal design, assures low contact resistance. An antione-piece clip/terminal design, assures low contact resistance. An anti rotation feature is also available on the solder and QC terminal designs. UL/CSA VDE


**Product Characteristics** 

Electrical	Solder Type — 10A, 600V., 6.3A, 250V Q.C. Type — 10A, 600V. 6.3A, 250V PCB Type — 10A, 600V. 6.3A, 250V			
Dielectric Strength	1500V., Minimum			
Clip/Terminals	Tin-Plated Spring Brass			
Base	Glass reinforced Thermoplastic. UL 94V0 flammability rating. Gray color (GY) for anti-rotational series, black color for all others.			
Ambient Temperature	-40°C to +85°C			




# **Product Dimensions**


## SolderTerminalsType:



## PC Board Mount Type:



## Q.C.TerminalsType:



# **Ordering Information**

Ordering PN	Part Number	Width (B)	Clip/Terminal Material	Anti-Rotation Boss	Packing
SolderTerminalsType					
05200004Z	520004	.40"	Brass	No	Bulk starting at 1 piece
Q.C. Terminals (NEMA Style .					
05200003Z	520003	.40"	Brass	No	Bulk starting at 1 piece
05200005ZXGY	520005GY	.40"	Brass	Yes	Bulk starting at 1 piece
P.C. Board MountType					
05200101Z	520101	.40"	Brass	No	Bulk starting at 1 piece