

FR101 THRU FR107

1.0 AMP.Fast Recovery Rectifiers

Features

· Low power loss.

· High current capability

· High reliability

· High surge current capability

• Plastic material-UL flammability 94V-0

Mechanical Data


· Case: Molded plastic DO-41

 Terminals: Plated leads solderable per MIL-STD-202, Method 208 guaranteed

· Polarity: Color band dentes cathode end

Mounting Position: AnyMaking: Type Number

· Lead Free: For RoHS/Lead Free Version



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load

For capacitive load derate current by 20%

Type Number	SYMBOL	FR101	FR102	FR103	FR104	FR105	FR106	FR107	Unit	
Maximum Recurrent Peak Reverse Voltage	Vrrm	50	100	200	400	600	800	1000	V	
Maximum RMS Voltage	VRMS	35	70	140	280	420	560	700	V	
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V	
Average Rectified Output Current (Note 1) @T _L =90 °C	I F(AV)	1.0							Α	
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	Ігѕм	30							Α	
I ² t Rating for Fusing (t < 8.3ms)	l²t	3.735							A ² s	
Forward Voltage @IF=1.0A	V _{FM}	1.3							V	
Peak Reverse Current @T _A =25°C	J _R 5.0									
At Rated DC Blocking Voltage @T _A =125 °C	IR IR	100							uA	
Maximum Reverse Recovery Time (Note 2)	T _{RR}	150		250	50	00	nS			
Typical Junction Capacitance (Note 3)	Сл	25 15					pF			
Typical Thermal Resistance Junction to Ambient(Note 1)	RвJA	25						°C/W		
Operating Temperature Range	Тл	-55 to + 125							$^{\circ}$	
Storage Temperature Range	Тѕтс	-55 to + 150							${\mathbb C}$	

Note: 1. Leads maintained at ambient temperature at a distance of 9.5mm from the case

- 2. Reverse Recovery Test Conditions: IF=0.5A, IR=1A, Irr=0.25A.
- 3. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C

FR101 THRU FR107

FIG. 1 – FORWARD CURRENT DERATING CURVE





FIG.2-TYPICAL FORWARD CHARACTERISTICS



INSTANTANEOUS FORWARD (V)

FIG. 3 - MAXIMUM NON-REPETITIVE SURGE CURRENT





FIG.4 - TYPICAL JUNCTION CAPACITANCE





FR101 THRU FR107

Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from DIYI.
- DIYI reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- DIYI disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- DIYI does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
 - DIYI makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own ris k andagree to fully indemnify DIYI for any damages resulting from such improper use or sale.
- Since DIYI uses lot number as the tracking base, please provide the lot number for tracking when complaining.