



江苏华能电子有限公司

JIANGSU HUANENG ELECTRONICS CO., LTD.

CUSTOMER:

MODEL NO.: MLT-5020 中孔

OUR PART NO ..:

CUSTOMER PART NO .:

CUSTOMER	APPROVED	CHECKED

Add: Chenbao Industrial Park, Chenbao Town, Xinghua, Taizhou City, Jiangsu China. 江苏省兴化市陈堡镇工业园区 Tel:+86-523-83710666 Fax:+86-523-83724866 Email: hn@huawha.com; http://www.huawha.com




HNDZ

Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City,China. Jiangsu China. Tel:+86-523-83710666 Fax:+86-523-83724866 Email: hn@huawha.com: http://www.huawha.com


		Entail: Int@nddwnd.com		
Specification for Electro-Magnetic Buzzer (SMD Type)			Page 2 of 6	
		Des.	Chk.	
Model No.:	MLT-5020	Part No.		
woder No	IVIL 1-5020	Fart NO.	7/20/2017	7/20/2017

1. Technical Parameter **Measuring condition** Part shall be measured under a condition (Temperature: $5 \sim 35^{\circ}$ C, Humidity: $45\% \sim 85\%$ R.H., Atmospheric pressure: 860 \sim 1060hPa) unless the standard condition (Temperature: 25±3°C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: $860 \sim 1060$ hPa) is regulated to measure. 1 Rated Voltage 3.6Vo-p 2 **Operating Voltage** 2.0~5.0Vo-p 3 Rated Current Max.100mA 4 Min. 80dB Sound Output at 10cm 12±3Ω 5 Coil Resistance 6 **Resonant Frequency** 4000Hz 7 **Operating Temperature** -30°C~+70°C 8 -40°C~+85°C



2. Dimensions

Unit: mm



*Unit: mm; Tolerance: ± 0.5mm Except Specified *Housing Material: Black LCP *Terminal plate: 3 soldering pads, tin Plating Brass




Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City,China. Jiangsu China. Tel:+86-523-83710666 Fax:+86-523-83724866 Email: hn@huawha.com; http://www.huawha.com

Specification for Electro-Magnetic Buzzer (SMD Type)		Des.	Page 3 of 6 Chk.		
Model No.:	MLT-5020	Part No.		7/20/2017	7/20/2017


Recommended Setting

3. Electrical And Acoustical Measuring Condition

Recommended Driving Circuit



Resonant frequency, 1/2 duty cycle. Square wave. Signal amplitude should be large enough tosaturate the transistor.



084 dB 20.0 PPa ms 96 Oct 110 dB 160 090 080 070 060 300 500 600 800 1k 2k 5k 6k 7k 8k 10k 200Hz 400 Эk 4k

3.6Vo-p 50% duty Square wave,10cm

4. Frequency Response



Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City,China. Jiangsu China. Tel:+86-523-83710666 Fax:+86-523-83724866


Email: hn@huawha.com; http://www.huawha.com

Specification for Electro-Magnetic Buzzer			Page 4 of 6		
(SMD Type)		Des.	Chk.		
Model No.:		Part No.			
woder No	MLT-5020	Part NO.		7/20/2017	7/20/2017

5. Surface mounting condition

5.1 Reflow soldering

Recommendable reflow soldering condition is as follows.



Note: (1) In automated mounting of the SMD sound transducers on PCB, any bending, expanding and pulling forces or shocks against the SMD sound transducers shall be kept minimum to prevent them from electrical failures and mechanical damages of the devices.
(2) In the reflow soldering, too high soldering temperatures and too large temperature Gradient such as rapid heating or cooling may cause electrical failures and mechanical damages of the devices.



JIANG SU HUANENG ELECTRONICS CO.,LTD

Specification for Electro-Magnetic Buzzer (SMD Type)		Des.	Page 5 of 6 Chk.	
Model No.:	MLT-5020	Part No.	7/20/2017	7/20/2017

6. Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

6.1 Ordinary Temperature Life Test

The part shall be subjected to 96 hours at $25\pm10^{\circ}$ C. Input rated voltage Resonant frequency, 1/2 duty Square wave.

6.2 High Temperature Test

The part shall be capable of with standing a storage temperature of +80 $^\circ\!\mathrm{C}$ for 96 hours.

6.3 Low Temperature Test

The part shall be capable of with standing a storage temperature of -30 $^\circ\!{\rm C}$ for 96 hours.

6.4 Humidity Test

Temperature:+40 °C \pm 3 °C Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

6.5 Temperature Shock Test

Temperature:60 °C /1hour→ 25 °C/3hours→-20 °C/1hour→ 25 °C/3hours (1cycle) Total cycle: 10 cycles

6.6 Drop Test

Standard Packaging From 75cm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

6.7 Vibration Test

Vibration:1000cycles /min. Amplitude:1.5mm, Duration: 1 hour in each 3 axes

6.8 Reflow Test

Use recommendable reflow soldering condition (as shown in 5.1)

(1) No abnormality should be found after reflow

(2) Good soldering to meet soldering requirements

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.



Chenbao Industrial Park, Chenbao Town, Xinghua,Taizhou City,China. Jiangsu China. Tel:+86-523-83710666

Fax:+86-523-83724866 Email: hn@huawha.com; http://www.huawha.com

Specification for Electro-Magnetic Buzzer (SMD Type)		Des.	Page 6 of 6 Chk.		
Model No.:	MLT-5020	Part No.		7/20/2017	7/20/2017

7 Packing

