


# **GBU15005 THRU GBU1510**

SINGLE PHASE 15.0AMP GLASS PASSIVATED BRIDGE RECTIFIER

#### **Features**



dimensions in inches and (millimeters)

#### **Maximum Ratings and Electrical Characteristics**

Rating at 25°C ambient temperature unless otherwise specified. Single Phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

TYPE NUMBER	SYMBOL	GBU 15005	GBU 1501	GBU 1502	GBU 1504	GBU 1506	GBU 1508	GBU 1510	UNITS
Peak Repetitive Reverse Voltage	Vrrm								
Working Peak Reverse Voltage	Vrwm	50	100	200	400	600	800	1000	V
DC Blocking Voltage	VDC								
RMS Reverse Voltage	VRMS	35	70	140	280	420	560	700	V
Average Rectified Output Current (Note 1)@Tc=90°C	lf(AV)	15.0							A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	Іғѕм	200						A	
Forward Voltage per element @IF=7.5A @IF=15A	Vfm	1.0 1.1						V	
Peak Reverse Current@TA =25 ℃At Rated DC Blocking Voltage@TA =125 ℃	lr	5.0 500							uA
I <sup>2</sup> t Rating for fusing (t <8.3ms)	l <sup>2</sup> t	166							A <sup>2</sup> s
Typical Junction Capacitance per leg(Note 2)	CJ	70							pF
Typical Thermal Resistance per leg (Note 3)	Reja	30.9							°C/W
	Rejl	7.3							
Operating and Storage Temperature Range	TJ,TSTG	-55to+150							°C


Note:1. Mounted on glass epoxy PC board with 1.3mm<sup>2</sup> solder pad.


2. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.


3. Device mounted on 50mm x 50mm x 1.6mm Cu Plate Heatsink.



## **GBU15005 THRU GBU1510**







0.01

0

20

40

60

80

PERCENT OF RATED PEAK REVERSE VOLTAGE

100

120

140



### **Important Notice and Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from DIYI.
- DIYI reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- DIYI disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- DIYI does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
  DIYI makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace

machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify DIYI for any damages resulting from such improper use or sale.

• Since DIYI uses lot number as the tracking base, please provide the lot number for tracking when complaining.