




N-Channel Enhancement Mode MOSFET

Feature SOT-23

 $\cdot 60 \text{V}/0.2 \text{A}, \, \text{Rds}(\text{on}) = 3.5 \Omega(\text{MAX}) \,\, \text{@Vgs} = 5 \text{V}. \, \text{Id} = 0.2 \text{A}$ $\text{Rds}(\text{on}) = 10 \Omega(\text{MAX}) \,\, \text{@Vgs} = 2.75 \text{V}. \, \text{Id} = 0.2 \text{A}$

- ·Super High dense cell design for extremely low RDS(ON).
- ·Reliable and Rugged.
- ·Low Threshold Voltage (0.5V—1.5V) Make it Ideal for Low Voltage Applications.
- ·SOT-23 for Surface Mount Package.



1: Gate 2: Source 3: Drain

Applications

·Power Management in DC/DC Converters

Portable and Battery-powered Products.

Absolute Maximum Ratings

Parameter	Symbol	Limit	Units
Drain-Source Voltage	V _{DS}	60	v
Gate-Source Voltage	V _{GS}	±20	v
Drain Current-Continuous	ID	0.2	A

TA=25℃ Unless Otherwise noted

Electrical Characteristics TA=25°C Unless Otherwise noted

	30.0 (5.00.00)	F200 800 N 80000	92,6908	190 88	9889	(CON 1870)
Parameter	Symbol	Test Conditions	Min	Typ.	Max	Units
Off Characteristics						
Drain to Source Breakdown Voltage	BVDSS	VGS=0V, ID=250μA	60	-	-	V
Zero-Gate Voltage Drain Current	IDSS	VDS=50V, VGS=0V		15	0.5	5 μΑ
Zero-Gale voltage Drain Current	1033	VDS=25V, VGS=0V	-	-	0.1	μΑ
Gate Body Leakage Current, Forward	IGSSF	VGS=20V, VDS=0V		- 92	100	nA
Gate Body Leakage Current, Reverse	IGSSR	VGS=-20V, VDS=0V		15	-100	nA
On Characteristics						
Gate Threshold Voltage	VGS(th)	VGS=VDS, ID=1.0 mA	0.5	-	1.5	V
Static Drain-source	PDS/ON)	VGS =5.0V, ID =0.2A	21	12	3.5	Ω
On-Resistance	RDS(ON)	VGS =2.75V, ID =0.2A	-	-	10	Ω
Drain-Source Diode Characterist	ics and Maximum	Ratings	•		•	
Drain-Source Diode Forward Voltage	VSD	VGS =0V, IS=0.2A			2.5	V

SHIKE MAKE CONSCIOUS PRODUCT

Conscious Products Begin With Conscious People





Typical Characteristics




Figure 1. Output Characteristics




Figure 3. Breakdown Voltage Variation with Temperature




Figure 2. Transfer Characteristics




Figure 4. Gate Threshold Variation with Temperature

SHIKE MAKE CONSCIOUS PRODUCT
CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE





Typical Characteristics




Figure 5. On-Resistance Variation with Temperature




Figure 6. On-Resistance vs. Drain Current




Figure 7. On-Resistance vs. Gate-to-Source Voltage




Figure 8. Source-Drain Diode Forward Voltage


SHIKE MAKE CONSCIOUS PRODUCT
CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE








SOT-23 Package Outline Dimensions (UNIT: mm)



	SOT-23		
Dim	Min	Max	
Α	2.85	2.95	
В	1.25	1.35	
С	1.0Ty	/pical	
D	0.37	0.43	
Е	0.35	0.48	
G	1.85	1.95	
Н	0.02	0.1	
J	0.1Ty	/pical	
K	2.35	2.45	
All Di	mensions i	n mm	

Soldering Footprint



SHIKE MAKE CONSCIOUS PRODUCT
CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE

