

# EDLC 2.7V 5F




## FEATURES

- Electric double layer capacitor
- Higher power density with ultra low ESR
- Semi-permanent, quick charge and discharge than batteries
- Suitable for short-term peak power assistance application
- UL and ISO/TS certificated, RoHS compliant
- Radial design with lead terminal type



## DIMENSIONS



Dimensions in mm			
D +1.0 Max	L ± 1.5	d ± 0.1	P ± 0.5
Φ10.0	20.0	Φ0.6	5.0

This drawing is not to be scaled.

## SPECIFICATIONS

Part Number	Rated Voltage, $V_R$ (V)	Rated Capacitance (F)	AC ESR 1kHz (mΩ)	DC IR (mΩ)	Maximum Current (A)	Leakage Current (mA)	Stored Energy (J)	Dimension D x L (mm)	Weight (g)
VEC 2R7 505 QG	2.7	5.	55.00	85.00	4.5	0.010	18.2	10.0 x 20.0	2.1

\* Maximum Current: 1 second discharge to  $\frac{1}{2} \cdot V_R$

\* Leakage Current: After 72hours at  $V_R$  and 25 °C

Item	Characteristics	Remarks
Rated Voltage( $V_R$ )	2.7V	
Capacitance Tolerance	-10 ~ 30%	
Operating Temperature ( $T_{min} \sim T_{max}$ )	-40 ~ +65 °C	$ \Delta cap  \leq 30\%$ of initial value at 25 °C $ \Delta ESR  \leq 100\%$ of specified value at 25 °C After 1,000 hours application of $V_R$ at $T_{max}$
Storage Temperature	-40 ~ 70 °C	
Cycle Life	500,000 cycles	$ \Delta cap  \leq 30\%$ of initial value at 25 °C $ \Delta ESR  \leq 100\%$ of specified value at 25 °C Cycles from $V_R$ to $\frac{1}{2} \cdot V_R$ under constant current at 25 °C
Shelf Life	2 years	$ \Delta cap  \leq 10\%$ of initial value at 25 °C $ \Delta ESR  \leq 50\%$ of specified value at 25 °C Without electrical charge under $T_{max}$