

Data sheet acquired from Harris Semiconductor SCHS063B – Revised July 2003

CD4094B Types

CMOS 8-Stage Shift-and-Store Bus Register

High-Voltage Types (20-Volt Rating)

■ CD4094B is an 8-stage serial shift register having a storage latch associated with each stage for strobing data from the serial input to parallel buffered 3-state outputs. The parallel outputs may be connected directly to common bus lines. Data is shifted on positive clock transitions. The data in each shift register stage is transferred to the storage register when the STROBE input is high. Data in the storage register appears at the outputs whenever the OUTPUT-ENABLE signal is high.

Two serial outputs are available for cascading a number of CD4094B devices. Data is available at the QS serial output terminal on positive clock edges to allow for high-speed operation in cascaded systems in which the clock rise time is fast. The same serial information, available at the Q'S terminal on the next negative clock edge, provides a means for cascading CD4094B devices when the clock rise time is slow.


The CD4094B types are supplied in 16-lead hermetic dual-in-line ceramic packages (F3A suffix), 16-lead dual-in-line plastic packages (E suffix), 16-lead small-outline packages (NSR suffix), and 16-lead thin shrink small-outline packages (PW and PWR suffixes).

Features:

- 3-state parallel outputs for connection to common bus
- Separate serial outputs synchronous to both positive and negative clock edges for cascading
- Medium speed operation -- 5 MHz at 10 V (typ.)
- Standardized, symmetrical output characteristics
- 100% tested for quiescent current at 20 V
- Maximum input current of 1 µA at 18 V over full package temperature range; 100 nA at 18 V and 25°C
- Noise margin (full package temperature range):
 1 V at V_{DD} = 5 V
 2 V at V_{DD} = 10 V
 2.5 V at V_{DD} = 15 V
- 5-V, 10-V, and 15-V parametric ratings
- Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices"

Applications:

- Serial-to-parallel data conversion
- Remote control holding register
- Dual-rank shift, hold, and bus applications







Fig. 1 - Terminal assignment.

MAXIMUM RATINGS, Absolute-Maximum Values:

	DC SUPPLY-VOLTAGE RANGE, (V _{DD})
0.5V to +20V	Voltages referenced to VSS Terminal)
0.5V to Vnn +0.5V	INPUT VOLTAGE RANGE, ALL INPUTS
±10mA	DC INPUT CURRENT, ANY ONE INPUT
	POWER DISSIPATION PER PACKAGE (PD):
500mW	For T _A = -55°C to +100°C
rate Linearity at 12mW/OC to 200mW	For T _A = +100°C to +125°C
•	DEVICE DISSIPATION PER OUTPUT TRANSISTOR
100mW	FOR TA = FULL PACKAGE-TEMPERATURE RANGE (All Package Ty
55°C to +125°C	OPERATING-TEMPERATURE RANGE (TA)
65°C to +150°C	STORAGE TEMPERATURE RANGE (Tstg)
	LEAD TEMPERATURE (DURING SOLDERING):
1.20500	At distance 1/16 + 1/32 inch (1.59 + 0.79mm) from case for 10e may






Fig. 3 — Timing diagram.

CD4094B Types

RECOMMENDED OPERATING CONDITIONS at $T_A = 25^{\circ}C$, Except as Noted. For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges:

OUADA OTERICTIO	VDD	LIR		
CHARACTERISTIC	(V)	MIN.	MAX.	UNITS
Supply-Voltage Range (For TA=Full Package-Temperature Range)		3	18	V
	5	125	_	
Data Setup Time, ts	10	55		ns
-	15	35	-	1
	5	200	_	
Clock Pulse Width, tw	10	100	-	ns
	15	83		
	5		1.25	
Clock Input Frequency, fCL	10	dc		MHz
	5 125 - 10 55 - 15 35 - 5 200 - 10 100 - 15 83 - 5 10 dc 2.5 15 3 5 10 - 15 5			
Clock Input Rise or Fall time,	5	1	15	
t _r CL, t _f CL:*	15	_	5	μς
, , , , , , , , , , , , , , , , , , , ,	5	200	-	
Strobe Pulse Width, tw	10	80	-	ns
	15	70	- :	

^{*}If more than one unit is cascaded trCL (for QS only) should be made less than or equal to the sum of the fixed propagation delay at 50 pF and the transition time of the output driving stage for the estimated capacitive load.




Fig. 5 - Minimum output low (sink) current characteristics.




Fig. 8 - Clock-to-serial output Q_S propagation delay vs C delay vs C_L.




Fig. 6 - Typical output high (source) current characteristics.




Fig. 9 — Clock-to-serial output Q'_{S} propagation delay vs CL.

TRUTH TABLE

CL▲	Output	Strobe	Data		railei tputs	Se Out	rial puts
	Enable	311000	Date	Q1	QN	œ.	0.2
7	0	х	х	ос	ос	Q7	NC
🥄	0	×	x	ос	ос	NC	Q7
<u> </u>	- 1	0	x	NC.	NC	Q7	NC
-	1.	1 1	Ö	0	QN-1	Q 7	NC
[1	1	1	1	QN-1	Q7	NC
	1	۱ ،	1	NC	NC	NC	Q7

- 4 = Level Change X = Don't Care NC = No Change
- Logic 1 ≡ High Logic 0 ≡ Low
- OC = Open Circuit
- At the positive clock edge information in the 7th shift register stage is transferred to the 8th register stage and the OS output.




Fig. 4 - Typical output low (sink) current characteristics.




Fig. 7 - Minimum output high (source) current characteristics.




Fig. 10 — Clock-to-parallel output propagation delay vs C_L .

CD4094B Types

STATIC ELECTRICAL CHARACTERISTICS

CHARACTER-	COND	OITIO	ıs	LIMI	LIMITS AT INDICATED TEMPERATURES (°C)						
ISTIC	Vo	VIN	VDD						+25	T	UNITS
	(V)	(V)	(V)	-55	-40	+85	+125	Min.	Тур.	Max.	L
Quiescent Device	-	0,5	5	5	5	150	150	-	0.04	5	
Current,	_	0,10	10	10	10	300	300		0.04	-10	μΑ
IDD Max.		0,15	15	20	20	600	600	- ,	0.04	20	1 1 1
	_	0,20	20	100	100	3000	3000	- ;	0.08	100	:
Output Low	0.4	0,5	5	0.64	0.61	0.42	0.36	0.51	1	-	
(Sink) Current	0.5	0,10	10	1.6	1.5	1.1	0.9	1.3	2.6	-	
Output High (Source) Current, IOH Min.	1.5	0,15	15	4.2	4	2.8	2.4	34	6.8		
	4.6	0,5	5	-0.64	-0.61	-0.42	-0.36	-0.51	-1	-	mA
	2.5	0,5	5	-2	-1.8	-1.3	-1.15	-1.6	-3.2		
	9.5	0,10	1,0	-1.6	-1.5	-1.1	-0.9	-1.3	-2.6		
	13.5	0,15	15	-4.2	-4	-2.8	-2.4	-3.4	-6.8		
Output Voltage:	1 =	0,5	5	2	0	.05			0	0.05	
Low Level, VOL Max.	-	0,10	10		0	.05			0	0.05	
VOL Wax.	_	0,15	15		ō	.05		- :	0	0.05	l v
Output Voltage:	-	0,5	5		4	.95		4.95	5	-	`
High-Level,	-	0,10	.10		9	.95		9.95	10	-	
VOH Min.	_	0,15	15		14	1.95		14.95	15	-	
Input Low	0.5, 4.5	-	5		1	1.5		_	_	1.5	
Voltage,	1, 9	_	10			3		_	_	3	}
VIL Max.	1.5,13.5	_	15			4				4	
Input High	0.5, 4.5	-	5			3.5		3.5	_		٧
Voltage,	1, 9	_	10			7		7			
VIH Min.	1.5,13.5	-	15			11		11	-		· ·
Input Current IJN Max.		0,18	18	±0.1	±0.1	±1	±1	-	±10-5	±0.1	μА
3 State Output Leakage Current IOUT Max.	0,18	0,18	18	±0.4	±0.4	±12	±12		±10 ⁴	±0.4	μΑ




Fig. 14 - Remote control holding register.




Fig. 11 – Strobe-to-parallel output propagation delay vs C_L.




Fig. 12 — Output enable-to-parallel output propagation delay vs C_L .




Fig. 13 - Typical transition time vs. load capacitance.





Fig. 15 — Typical maximum-clock-frequency vs. supply voltage.

DYNAMIC ELECTRICAL CHARACTERISTICS

At $T_A=25^{\circ}C$; Input t_r , $t_f=20$ ns, $C_L=50$ pF, $R_L=200$ k Ω

CHARACTERISTIC	Van		LIMITS			
on and teniorio	VDD (V)	MIN.	TYP.	MAX.	UNITS	
Propagation Delay Time,			1			
tPHL, tPLH	_		200	000		
Clock to Serial Output Q _S	10	_	300 125	600 250		
clock to Serial Output QS	15	_	95	190	ns	
	5	 	230	460		
Clock to Serial Output Q'S	10	_	110	220	l ns	
	15	_	75	150		
	5	_	420	840		
Clock to Parallel Output	10	-	195	390	ns	
	15	-	135	270		
	- 5	_	290	580		
Strobe to Parallel Output	10	-	145	290	ns	
	15		100	200		
Output Enable to Parallel	5	-	140	280		
Output:	10	-	60	120	ns	
tPHZ ^{, t} PZH	15	_	45	90	, ,	
4	5	-	100	200		
^t PLZ ^{, t} PZL	10	-	50	100	ns	
	15	-	40	80		
Minimum Strobe Pulse	5	-	100	200		
Width, tw	10	-	. 40	80	ns	
	15		35	70		
Minimum Clock Pulse	5	-	100	200		
Width, tw	10	_	50	100	ns	
	15		40	83		
Minimum Data Setup	5	_	60	125		
Time, t _S	10	-	30	55	ns	
	15		20	35		
Transition Time;	5	-	100	200		
THL, TLH	10	-	50	100	ns	
	15		40	80		
Maximum Clock Input Rise	5 10	15 5	_	_	μs	
or Fall Time, t _F CL, t _f CL	15	5			μs 	
Maximum Clock Input	5	1.25	2.5			
Frequency, fCL	10	2.5	5	-	MHz	
	15	3	6			
Input Capacitance C _{IN}	_	_	5	7.5	pF	
(Any Input)		1	1		Α.	






Fig. 16 – Dynamic power dissipation vs input clock frequency.




Fig. 17 — Quiescent device current test circuit.




Fig. 18 - Input voltage test circuit.





Fig. 19 - Input current test circuit.



Dimensions and Pad Layout for CD4094B Chip.





10-Jun-2014

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
7702501EA	ACTIVE	CDIP	J	16	1	TBD	A42	N / A for Pkg Type	-55 to 125	7702501EA CD4094BF3A	Samples
CD4094BE	ACTIVE	PDIP	N	16	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-55 to 125	CD4094BE	Samples
CD4094BEE4	ACTIVE	PDIP	N	16	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-55 to 125	CD4094BE	Samples
CD4094BF	ACTIVE	CDIP	J	16	1	TBD	A42	N / A for Pkg Type	-55 to 125	CD4094BF	Samples
CD4094BF3A	ACTIVE	CDIP	J	16	1	TBD	A42	N / A for Pkg Type	-55 to 125	7702501EA CD4094BF3A	Samples
CD4094BNSR	ACTIVE	so	NS	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4094B	Samples
CD4094BPW	ACTIVE	TSSOP	PW	16	90	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM094B	Samples
CD4094BPWG4	ACTIVE	TSSOP	PW	16	90	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM094B	Samples
CD4094BPWR	ACTIVE	TSSOP	PW	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM094B	Samples
CD4094BPWRG4	ACTIVE	TSSOP	PW	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM094B	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.





10-Jun-2014

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF CD4094B, CD4094B-MIL:

Catalog: CD4094B

Military: CD4094B-MIL

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 8-Apr-2013

TAPE AND REEL INFORMATION





A0	<u> </u>
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD4094BPWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1

www.ti.com 8-Apr-2013



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
CD4094BPWR	TSSOP	PW	16	2000	367.0	367.0	35.0	

MECHANICAL DATA

NS (R-PDSO-G**)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

PW (R-PDSO-G16)

PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M—1994.
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
- E. Falls within JEDEC MO-153



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.