

P.C.B. LAYOUT






Table 1

EPM(R)-10-V	10	25.30[.996]	22.86[.900]
EPM(R)-08-V	8	20.22[.796]	17.78[.700]
EPM(R)-06-V	6	15.14[.596]	12.70[.500]
EPM(R)-04-V	4	10.06[.400]	7.62[.300]
EPM(R)-02-V	2	4.98[.196]	2.54[.100]
PROD. NO.	NO. OF POS.	DIM. A	DIM. B

SCHEMATIC(TYP.)



(2,4,6,8,10 POS AVAIL)

- NOTE:
- 1.ALL DIMENSIONS ARE IN MILLIMETERS, BRACKETED DIMENSIONS ARE IN INCHES.
 - 2.GENERAL TOLERANCES ±0.20mm.
 - 3.MATERIAL & *:SEE SPECIFICATION.
 - 4.P-Pitch=2.54mm[0.100]

04,08 Poles Available Now

ZON/REV	DESCRIPTION	DATE	APPD.
A	DWG.REL		

APPD:	QTY:	SCALE:	4:1	UNITS:	mm	PART NO.:	See Table 1	MAT'L:		DWG NO.:	EPM(R)-□□-V
CHKD:											
DR:	張文達	REV/A									
DESIGN:	張文達										
圓達實業股份有限公司 DIPTRONICSMANUFACTURING INC.											
								PART NAME:	Piano type End Stackable		