



NOTE:  
 Rating: DC 12V 50mA  
 Operating Force: 20±10gf  
 Lifetime: 100,000 Cycles

PART NO.	K5-1619UA-01
	K5-1619UN-01

ITEM	PART NAME	TER. NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	PA46	Black	—
②	Cover	—	1	SUS	Natural	—
①	Slider	—	1	PA46	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhang	2013/8/29	DETECTOR SWITCHES

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.												
	A		NEW															
TOLERANCES ARE: <table border="1" style="display: inline-table; margin-left: 10px;"> <tr> <td>30~0.15</td> <td>±0.30</td> <td>ANGLE</td> </tr> <tr> <td>10~30</td> <td>±0.20</td> <td>UNIT: mm</td> </tr> <tr> <td>5~10</td> <td>±0.15</td> <td>SCALE: 1:1</td> </tr> <tr> <td>~5</td> <td>±0.10</td> <td>DRAWING NO.</td> </tr> </table>							30~0.15	±0.30	ANGLE	10~30	±0.20	UNIT: mm	5~10	±0.15	SCALE: 1:1	~5	±0.10	DRAWING NO.
30~0.15	±0.30	ANGLE																
10~30	±0.20	UNIT: mm																
5~10	±0.15	SCALE: 1:1																
~5	±0.10	DRAWING NO.																
APPROVALS: <table border="1" style="display: inline-table; margin-left: 10px;"> <tr> <td>PART NO.</td> <td>SCALE: 1:1</td> <td>PROJ. </td> </tr> <tr> <td></td> <td></td> <td>SHEET 1 OF 1</td> </tr> </table>							PART NO.	SCALE: 1:1	PROJ.			SHEET 1 OF 1						
PART NO.	SCALE: 1:1	PROJ.																
		SHEET 1 OF 1																