
Vishay Semiconductors

Hyperfast Rectifier, 30 A FRED Pt®



www.vishay.com

PRODUCT SUMMARY								
Package	TO-247AD 2L							
I _{F(AV)}	30 A							
V _R	600 V							
V _F at I _F	1.4 V							
t _{rr} typ.	26 ns							
T _J max.	175 °C							
Diode variation	Single die							

FEATURES

- Low forward voltage drop
- Hyperfast soft recovery time
- 175 °C operating junction temperature
- Designed and qualified according to commercial qualification



RoHS

COMPLIANT

HALOGEN

FREE

 Material categorization: for definitions of compliance please see www.vishav.com/doc?99912

DESCRIPTION / APPLICATIONS

Hyperfast recovery rectifiers designed with optimized performance of forward voltage drop, hyperfast recovery time, and soft recovery.

The planar structure and the platinum doped life time control guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in PFC Boost stage in the AC/DC section of SMPS, inverters or as freewheeling diodes.

The extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

ABSOLUTE MAXIMUM RATINGS									
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS					
Repetitive peak reverse voltage	V _{RRM}		600	V					
Average rectified forward current	I _{F(AV)}	T _C = 112 °C	30	٨					
Non-repetitive peak surge current	I _{FSM}	$T_C = 25 \ ^{\circ}C$, $t_p = 8.3 \ ms$ half sine wave	240	A					
Operating junction and storage temperatures	T _J , T _{Stg}		-55 to +175	°C					

ELECTRICAL SPECIFICATIONS ($T_J = 25$ °C unless otherwise specified)									
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS			
Breakdown voltage, blocking voltage	V _{BR} , V _R	I _R = 100 μA	600	-	-				
Forward voltage	V _F	I _F = 30 A	-	2.0	2.65	V			
		I _F = 30 A, T _J = 150 °C	-	1.4	1.8				
De construit de construit	I _R	$V_R = V_R$ rated	-	0.02	30				
Reverse leakage current		$T_J = 150 \text{ °C}, V_R = V_R \text{ rated}$	-	-	300	μA			
Junction capacitance	CT	V _R = 600 V	-	20	-	pF			
Series inductance	L _S	Measured lead to lead 5 mm from package body	-	8.0	-	nH			

Revision: 03-Mar-17

1

Document Number: 95780

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




www.vishay.com

Vishay Semiconductors

DYNAMIC RECOVERY CHARACTERISTICS ($T_J = 25$ °C unless otherwise specified)										
PARAMETER	SYMBOL	TEST CO	MIN.	TYP.	MAX.	UNITS				
		$I_F = 1 \text{ A}, \text{ d}I_F/\text{d}t = 50 \text{ A}$	$I_F = 1 \text{ A}, \text{ d}I_F/\text{d}t = 50 \text{ A}/\mu\text{s}, \text{ V}_R = 30 \text{ V}$			-				
Reverse recovery time	t _{rr}	T _J = 25 °C		-	26	-	ns			
		T _J = 125 °C		-	70	-				
Pook receivery ourrent	I _{RRM}	T _J = 25 °C	I _F = 30 A dI _F /dt = 200 A/µs V _B = 200 V	-	3.5	-	A			
Peak recovery current		T _J = 125 °C		-	7.6	-				
Reverse recovery charge	Q _{rr}	T _J = 25 °C		-	50	-				
		T _J = 125 °C		-	280	-	nC			


THERMAL - MECHANICAL SPECIFICATIONS									
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS			
Maximum junction and storage temperature range	T _J , T _{Stg}		-55	-	175	°C			
Thermal resistance, junction to case	R _{thJC}		-	0.7	1.1	°C/W			
Thermal resistance, junction to ambient per leg	R _{thJA}	Typical socket mount	-	-	70				
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth, and greased	-	0.5	-				
Weight			-	5.5	-	g			
Weight			-	0.2	-	oz.			
Mounting torque			1.2 (10)	-	2.4 (20)	kgf · cm (lbf · in)			
Marking device		Case style TO-247AD 2L		EPH	3006L				


Vishay Semiconductors




www.vishay.com

SHAY













Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage



 l_1 , Rectangular Pulse Duration (s)

Fig. 4 - Max. Thermal Impedance $Z_{thJC} \mbox{ Characteristics}$





VS-EPH3006L-N3

1000


1000

Vishay Semiconductors





ORDERING INFORMATION TABLE



ORDERING INFORMATION (Example)								
PREFERRED P/N	QUANTITY PER TUBE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION					
VS-EPH3006L-N3	25	500	Antistatic plastic tube					


LINKS TO RELATED DOCUMENTS							
Dimensions	TO-247AD 2L	www.vishay.com/doc?95536					
Part marking information	TO-247AD 2L	www.vishay.com/doc?95648					



Vishay Semiconductors


TO-247AD 2L

DIMENSIONS in millimeters and inches



(4) Section C - C, D - D

(b, b2)



SYMBOL	MILLIM	MILLIMETERS INCHES NOTES		SYMBOL		INCHES		NOTES				
STIVIDUL	MIN.	MAX.	MIN.	MAX.	NOTES	NOTES	STIVIDUL	MIN.	MAX.	MIN.	MAX.	INUTES
А	4.65	5.31	0.183	0.209			E	15.29	15.87	0.602	0.625	3
A1	2.21	2.59	0.087	0.102			E1	13.46	-	0.53	-	
A2	1.50	2.49	0.059	0.098			е	5.46	BSC	0.215	5 BSC	
b	0.99	1.40	0.039	0.055			ØK	0.2	254	0.0	010	
b1	0.99	1.35	0.039	0.053			L	19.81	20.32	0.780	0.800	
b2	1.65	2.39	0.065	0.094			L1	3.71	4.29	0.146	0.169	
b3	1.65	2.34	0.065	0.092			ØР	3.56	3.66	0.14	0.144	
С	0.38	0.89	0.015	0.035			Ø P1	-	6.98	-	0.275	
c1	0.38	0.84	0.015	0.033			Q	5.31	5.69	0.209	0.224	
D	19.71	20.70	0.776	0.815	3]	R	4.52	5.49	0.178	0.216	
D1	13.08	-	0.515	-	4		S	5.51	BSC	0.217	7 BSC	
D2	0.51	1.35	0.020	0.053]						

Notes

⁽¹⁾ Dimensioning and tolerancing per ASME Y14.5M-1994

(2) Contour of slot optional

- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- ⁽⁵⁾ Lead finish uncontrolled in L1
- ⁽⁶⁾ Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- $^{(7)}$ Outline conforms to JEDEC $^{\circledast}$ outline TO-247 with exception of dimension Q

Revision: 20-Apr-17

Document Number: 95536 1 sia@vishay.com, DiodesEurope@vishay.com For technical questions within your region: DiodesAmericas@vishay.com, DiodesA THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.