

**REVERSE VOLTAGE:** 50 to 1000 VOLTS  
**FORWARD CURRENT:** 1.0 AMPERE

### FEATURES

- Plastic material has Underwriters Laboratory Flammability Classification 94V-0
- High surge overload rating of 50 Amperes peak
- Ideal for printed circuit board
- Glass passivated chip junction

### MECHANICAL DATA

Case: Molded plastic, DB-S


Epoxy: UL 94V-0 rate flame retardant

Terminals: Leads solderable per MIL-STD-202, method 208 guaranteed

Mounting position: Any

Weight: 0.02ounce, 0.4gram

### DB-S



Dimensions in inches and (millimeters)

### Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

	Symbols	DB101S	DB102S	DB103S	DB104S	DB105S	DB106S	DB107S	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	$V_{RMS}$	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	$V_{DC}$	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Rectified Current at $T_A=40^\circ\text{C}$ (Note 2)	$I_{(AV)}$	1.0							Amp
Peak Forward Surge Current, 8.3ms single half-sine-wave superimposed on rated load (JEDEC method)	$I_{FSM}$	50							Amp
Maximum Forward Voltage at 1.0A DC and 25°C	$V_F$	1.1							Volts
Maximum Reverse Current at $T_A=25^\circ\text{C}$ at Rated DC Blocking Voltage $T_A=125^\circ\text{C}$	$I_R$	5.0 500							uAmp
Typical Junction Capacitance (Note 1)	$C_J$	25							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	40							°C/W
Typical Thermal Resistance (Note 2)	$R_{\theta JL}$	15							°C/W
Operating and Storage Temperature Range	$T_J, T_{stg}$	-55 to +150							°C


### NOTES:

1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.


2- Units mounted on P.C.B. with 0.5 x 0.5" (13 x 13mm) copper pads

## RATINGS AND CHARACTERISTIC CURVES


**Fig. 1 - Derating Curve Output Rectified Current**




**Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Leg**




**Fig. 3 - Typical Forward Characteristics Per Leg**



**Fig. 4 - Typical Reverse Leakage Characteristics Per Leg**



**Fig. 5 - Typical Junction Capacitance Per Leg**



**Fig. 6 - Typical Transient Thermal Impedance**

