




Circuit Diagram



PCB Layout(Pattern Side)



NOTE:

1. Operating Force: 240gf±80gf
2. Travel : 2.4±0.3mm

NO.	Operating Type	Part No.
1	Push To Lock	K8-8585D-L1
2	Push No Lock	K8-8585D-N1
3	Push No Sound No Lock	K8-8585D-NN

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑧	Terminal	—	6	Brass strip	Plating silver	—
⑦	Contact	—	2	Phosphor bronze	Plating silver	—
⑥	Securing glue	—	2	PA66	Black	—
⑤	Spring	—	1	SUS	Natural	—
④	Base	—	1	PBT	Black	—
③	Crochet Needle	—	1	SUS	Natural	—
②	Cover	—	1	POM	Gray	—
①	KNOB	—	1	POM	White	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhang	2013/10/15	PUSHBUTTON SWITCHS

APPROVALS	PART NO.	SCALE:	PROJ:
CHECKED		1:1	
APPROVALS			
TOLERANCES ARE		DRAWING NO.	SHEET 1 OF 1
30±0.15	±0.30		
10~30	±0.20		
5~10	±0.15		
~5	±0.10		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

**HRP**  
ELECTRONICS CO.,LTD