



## LM2902/ LM2902A/ LM2904/ LM2904A

DUAL AND QUAD OPERATIONAL AMPLIFIERS

## Description

The LM2902/2904 series amplifiers consist of four and two independent high-gain operational amplifiers with very low input offset voltage specification. They have been designed to operate from a single power supply over a wide range of voltages; however operation from split power supplies is also possible. They offer low power supply current independent of the magnitude of the power supply voltage.

The LM2902/2904 series are characterized for operation from -40°C to +125°C and the dual devices are available in SO-8, MSOP-8, TSSOP-8 and the quad devices available in SO-14 and TSSOP-14 with industry standard pin-outs. Both use green mold compound as standard.

## Features

.


- Wide Power Supply Voltage Range:
  - Single Supply: 3V to 36V
  - Dual Supplies: ±1.5V to ±18V
- Very Low Supply Current Drain
  - LM2904 500µA Independent of Supply Voltage
  - LM2902 700µA Independent of Supply Voltage
- Low Input Bias Current: 20nA
- Low Input Offset Voltage:
  - A Versions: 1mV Typ
  - Non-A Version: 2mV Typ
- Large DC Voltage Gain: 100dB
- Wide Bandwidth (Unity Gain): 700KHz (Temperature Compensated)
- Internally Compensated with Unity Gain
- Input Common-Mode Voltage Range Includes Ground
- Differential Input Voltage Range Equal to the Power Supply Voltage
- Large Output Voltage Swing: 0V to V<sub>CC</sub> -1.5V
- SO-8 (Duals) and SO-14/TSSOP-14 (Quads) Packages Available
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An Automotive-Compliant Part is Available Under Separate Datasheet (<u>LM2902Q\_04Q</u>)

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.

- 2. See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


## Pin Assignments



SO-14/TSSOP-14 LM2902/ LM2902A



# **Schematic Diagram**



Functional Block Diagram of LM2902/ 2902A/ 2904/ 2904A (Each Amplifier)

# **Pin Descriptions**

LM2902, LM2902A			
Pin Name	Pin #	Function	
10UT	1	Channel 1 Output	
1IN-	2	Channel 1 Inverting Input	
1IN+	3	Channel 1 Non-Inverting Input	
V <sub>CC</sub>	4	Chip Supply Voltage	
2IN+	5	Channel 2 Non-Inverting Input	
2IN-	6	Channel 2 Inverting Input	
20UT	7	Channel 2 Output	
3OUT	8	Channel 3 Output	
3IN-	9	Channel 3 Inverting Input	
3IN+	10	Channel 3 Non-Inverting Input	
GND	11	Ground	
4IN+	12	Channel 4 Non-Inverting Input	
4IN-	13	Channel 4 Inverting Input	
40UT	14	Channel 4 Output	
LM2904, LM2904A			
10UT	1	Channel 1 Output	
1IN-	2	Channel 1 Inverting Input	
1IN+	3	Channel 1 Non-Inverting Input	
GND	4	Ground	
2IN+	5	Channel 2 Non-Inverting Input	
2IN-	6	Channel 2 Inverting Input	
20UT	7	Channel 2 Output	
V <sub>CC</sub>	8	Chip Supply Voltage	



Symbol	1	Rating	Unit	
V <sub>CC</sub>	Supply Voltage	±18 or 36	V	
VID	Differential Input Voltage		36	V
VIN	Input Voltage		-0.3 to +36	V
		SO-8	TBD	
	De che en Thermolden e de ce	MSOP-8	TBD	
$\theta_{JA}$	Package Thermal Impedance (Note 5)	TSSOP-8	TBD	°C/W
	(1000 5)	SO-14	TBD	
	TSSOP-14	TBD		
		SO-8	TBD	
	Package Thermal Impedance (Note 6)	MSOP-8	TBD	°C/W
$\theta_{JC}$		TSSOP-8	TBD	
	(1000 0)	SO-14	TBD	
		TSSOP-14	TBD	
_	Output Short-Circuit to GND (One Amplifier) (Note 7)	$V_{CC} \le 15V$ and $T_A = +25^{\circ}C$	Continuous	_
TA	Operating Temperature Range		-40 to +125	°C
TJ	Operating Junction Temperature	+150	°C	
T <sub>ST</sub>	Storage Temperature Range	-65 to +150	°C	
Human Body Mode ESD Protection (Note 8)		n (Note 8)	300	M
ESD	Machine Mode ESD Protection	150	V	

## Absolute Maximum Ratings (Note 4) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Notes: 4. Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

5. Maximum power dissipation is a function of  $T_{J(max)}$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_{J(max)} - T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of +150°C can affect reliability.

6. Maximum power dissipation is a function of  $T_{J(max)}$ ,  $\theta_{JC}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_{J(max)} - T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of +150°C can affect reliability. 7. Short circuits from outputs to V<sub>CC</sub> or ground can cause excessive heating and eventual destruction.

8. Human body model, 1.5kΩ in series with 100pF.



## Electrical Characteristics (Notes 12 & 13) (@ V<sub>CC</sub> = +5.0V, T<sub>A</sub> = +25°C, unless otherwise specified.)

LM2902, L	M2902A									
	Parameter		Conditi	ons	T <sub>A</sub>	Min	Тур	Max	Unit	
			V <sub>IC</sub> = V <sub>CMR</sub> Min,	Non-A Device	T <sub>A</sub> = +25°C	_	2	7		
V <sub>IO</sub>	Input Offset Voltage		$V_0 = 1.4V$ ,	Non-A Device	Full Range	_	—	10	mV	
VIO	input Onset Voltage		$V_{CC} = 5V$ to Max	A-Suffix Device	$T_A = +25^{\circ}C$	_	1	2	IIIV	
			Rs = 0Ω	A-Sullix Device	Full Range	—	—	4		
$\Delta V_{IO} / \Delta T$	Input Offset Voltage Ten Drift	nperature	Rs = 0Ω		Full Range	_	7	_	µV/℃	
IB	Input Bias Current		IIN+ or IIN- with OUT in	Linear Range,	T <sub>A</sub> = +25°C	_	-20	-200	nA	
ıB			V <sub>CMR</sub> = 0V (Note 9)		Full Range	_	—	-500		
lio	Input Offset Current		I <sub>IN+</sub> - I <sub>IN-</sub> , V <sub>CM</sub> = 0V		T <sub>A</sub> = +25°C	_	2	50	nA	
10	input onset ounent		11N+ - 11N-, VCM - 0V		Full Range	—	—	150	117	
$\Delta I_{\rm IO}/\Delta T$	Input Offset Current Tem Drift	perature	-		Full Range	_	10	_	pA/°C	
N	Input Common-Mode Vo	ltage			T <sub>A</sub> = +25°C	0 to V <sub>CC</sub> -1.5	—	_	v	
VCMR	V <sub>CMR</sub> Range		V <sub>CC</sub> = 30V (Note 10)		Full Range	0 to V <sub>CC</sub> -2.0	—	_	V	
	Supply Current		$V_0 = 0.5 V_{CC}$ , No Load	$V_{CC} = 30V$	Full Range	_	1.0	3.0	mA	
Icc	(Four Amplifiers)		$V_{O} = 0.5 V_{CC}$ , No Load	$V_{CC} = 5V$	Full Range	_	0.7	1.2		
•	Valtage Cain		V <sub>CC</sub> = 15V, V <sub>OUT</sub> = 1V to 11V,		T <sub>A</sub> = +25°C	25	100	_	\//m)/	
Av	Voltage Gain		$R_L \ge 2k\Omega$		Full Range	15	_	_	V/mV	
CMRR	Common Mode Rejection	n Ratio	DC, $V_{CMR} = 0V$ to $V_{CC}$ -1.5V		$T_A = +25^{\circ}C$	60	70	_	dB	
PSRR	Power Supply Rejection	Ratio	$V_{CC} = 5V$ to $30V$		$T_A = +25^{\circ}C$	70	100	_	dB	
	Amplifier to Amplifier Co	upling	f = 1kHz to 20kHz (Inp (Note 11)	ut Referred)	T <sub>A</sub> = +25°C	_	-120	_	dB	
		Sink	$V_{IN} = 1V, V_{IN} = 0V, V_{O}$ $V_{O} = 200 mV$	cc = 15V,	T <sub>A</sub> = +25°C	12	50	_	μA	
ISINK	Output Current	SILIK	$V_{IN} = 1V, V_{IN} = 0V, V_{O}$	cc = 15V,	$T_A = +25^{\circ}C$	10	20	—		
			V <sub>O</sub> = 15V		Full Range	5	_	_		
		Source	$V_{IN}^{+} = 1V, V_{IN}^{-} = 0V, V_{O}$	cc = 15V,	T <sub>A</sub> = +25°C	-20	-40	-60	mA	
ISOURCE		Source	$V_{O} = 0V$		Full Range	-10	—	_		
Isc	Short-Circuit to Ground		$V_{CC} = 5V, GND = -5V, V_O = 0V$		$T_A = +25^{\circ}C$	_	±40	±60	mA	
			$R_L = 10K\Omega$		T <sub>A</sub> = +25°C	_	V <sub>CC</sub> -1.5			
V <sub>OH</sub>	High-Level Output Voltag	ge Swing	$R_L =$	2ΚΩ,		26 — —	_	V		
			$V_{CC} = 30V$ $R_L \ge$	10KΩ Full Range	27	28	_			
Vol	Low-Level Output Voltag	e Swing	$R_L \leq 10 K \Omega$		Full Range	_	5	20	mV	

## AC Electrical Characteristics (Notes 12 & 13) (@ V<sub>CC</sub> = ±15.0V, T<sub>A</sub> = +25°C, unless otherwise specified.)

LM2902, LM2902A						
	Parameter	Conditions	Тур	Unit		
SR	Slew Rate at Unity Gain	$R_L = 1M\Omega, C_L = 30pF, V_I = \pm 10V$	0.3	V/µs		
B1	Unity Gain Bandwidth	$R_L = 1M\Omega, C_L = 20pF$	0.7	MHz		
Vn	Equivalent Input Noise Voltage	$R_{S} = 100\Omega, V_{I} = 0V, f = 1KHz$	40	nV/√Hz		

Notes: 9. The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.

The input common-mode voltage of either input signal voltage should not be allowed to go negative by more than 0.3V (@ +25°C). The upper end of the common-mode voltage range is V<sub>CC</sub> -1.5V (@ 25°C), but either or both inputs can go to +36V without damage, independent of the magnitude of V<sub>CC</sub>.
 Due to proximity of external components, insure that coupling is not originating via stray capacitance between these external parts. This typically can

be detected as this type of capacitance increases at higher frequencies. 12. Typical values are all at T<sub>A</sub>=25°C conditions and represent the most likely parametric norm as determined at the time of characterization. Actual

2. Typical values are an at  $T_A=25$  C conducts and represent the most likely parameter horn as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not guaranteed on shipped production material.

13. All limits are guaranteed by testing or statistical analysis. Limits over the full temperature are guaranteed by design, but not tested in production.



## Electrical Characteristics (Continued) (Notes 12 & 13) (@ V<sub>CC</sub> = +5.0V, T<sub>A</sub> = +25°C, unless otherwise specified.)

.M2904, L						-	D.C.	<b>T</b>	Maria	11?!	
	Parameter	ſ	Conditions		TA	Min	Тур	Мах	Unit		
			$V_{IC} = V_{CMR} Min,$	Non	-A Device	$T_A = +25^{\circ}C$	—	2	7		
Vio	Input Offset Volt	age	$V_0 = 1.4V,$			Full Range	—		10	mV	
			$V_{CC} = 5V$ to Max Rs = 0 $\Omega$	A-S	uffix Device	T <sub>A</sub> = +25°C	—	1	2	_	
		age Temperature	113 - 012			Full Range	—	_	4		
$\Delta V_{\text{IO}} / \Delta T$	Drift	age remperature	$Rs = 0\Omega$			Full Range	—	7	—	µV/°C	
1-	Input Bias Curre	ont	I <sub>IN+</sub> or I <sub>IN-</sub> with OU	T in Line	ear Range,	$T_A = +25^{\circ}C$	—	-20	-250	nA	
Ι <sub>Β</sub>	Input bias Curre		V <sub>CMR</sub> = 0V (Note 9	)		Full Range	—	_	-500		
lio	Input Offset Cur	rent	I <sub>IN+</sub> - I <sub>IN-</sub> , V <sub>CM</sub> = 0V	1		$T_A = +25^{\circ}C$	—	2	50	nA	
10	input Onset Ou	icin	$\eta_{N+} = \eta_{N-}, V_{CM} = 0V$			Full Range	—	—	150		
$\Delta I_{\rm IO}/\Delta T$	Input Offset Cur Drift	rent Temperature		—		Full Range	—	10	—	pA/°C	
						T <sub>A</sub> = +25°C	0 to		_		
V <sub>CMR</sub>	Input Common-I	Mode Voltage	V <sub>CC</sub> = 30V (Note 10)			V <sub>CC</sub> -1.5			V		
	Range				Full Range	0 to V <sub>CC</sub> -2.0	—	—			
	Supply Current		$V_{O} = 0.5 V_{CC}$ , No L	oad	$V_{CC} = 30V$	Full Range	—	0.7	2.0	2.0 mA	
Icc	(Two Amplifiers)	)	Vo = 0.5V <sub>CC</sub> , No Lo	oad	$V_{CC} = 5V$	Full Range	—	0.5	1.2	mA	
Av	Voltage Gain		$V_{CC} = 15V, V_{OUT} = 1V$ to 11V, $R_L \ge 2k\Omega$ ,		$T_A = +25^{\circ}C$	25	100	_	V/mV		
Av	Voltage Gall				Full Range	15	-	_			
CMRR	Common Mode	Rejection Ratio	DC, $V_{CMR} = 0V$ to $V_{CC}$ -1.5V		$T_A = +25^{\circ}C$	60	70	—	dB		
PSRR	Power Supply R	ejection Ratio	$V_{CC} = 5V$ to 30V		$T_A = +25^{\circ}C$	70	100	_	dB		
	Amplifier to Amp	lifier Coupling	f = 1kHz to 20kHz	(Note 11	)	$T_A = +25^{\circ}C$	_	120	_	dB	
			$V_{IN}^{-} = 1V, V_{IN}^{+} = 0V$ $V_{O} = 200 \text{mV}$	∕, V <sub>CC</sub> = 1	15V,	T <sub>A</sub> = +25°C	12	50	_	μA	
ISINK		Sink				T <sub>A</sub> = +25°C	10	20	_		
	Output Current		$V_{IN} = 1V, V_{IN} = 0V$	, V <sub>CC</sub> =	15V, V <sub>O</sub> = 15V	Full Range	5	_	_		
		Courses				T <sub>A</sub> = +25°C	-20	-40	-60	mA	
SOURCE		Source	$V_{IN}^{+} = 1V, V_{IN}^{-} = 0V, V_{CC} = 15V, V_{O} = 0V$		Full Range	-10		_	1		
I <sub>SC</sub>	Short-Circuit to Ground		$V_{CC} = 5V, GND = -5V, V_{O} = 0V$		= 0V	$T_A = +25^{\circ}C$	—	±40	±60	mA	
			R <sub>L</sub> = 10KΩ			$T_A = +25^{\circ}C$	V <sub>CC</sub> -1.5		_		
V <sub>OH</sub>	High-Level Outp	out Voltage Swing	$R_1 = 2k$		Ω,		26		—	V	
			$V_{CC} = 30V$	R <sub>L</sub> ≥ 10k	Ω	Full Range	27	28	—	]	
Vol	Low-Lever Outp	ut Voltage Swing	$R_L \leq 10 K \Omega$			Full Range	_	5	20	mV	

## AC Electrical Characteristics (Notes 12 & 13) (@ V<sub>CC</sub> = ±15.0V, T<sub>A</sub> = +25°C, unless otherwise specified.)

LM2904, LM2904A						
	Parameter	Conditions	Тур	Unit		
SR	Slew Rate at Unity Gain	$R_L = 1M\Omega, C_L = 30pF, V_I = \pm 10V$	0.3	V/µs		
B1	Unity Gain Bandwidth	$R_L = 1M\Omega, C_L = 20pF$	0.7	MHz		
Vn	Equivalent Input Noise Voltage	$R_S = 100\Omega$ , $V_I = 0V$ , $f = 1KHz$	40	nV/√Hz		

9. The direction of the input current is out of the IC due to the PNP input stage. This current is essentially constant, independent of the state of the output so no loading change exists on the input lines.

10. The input common-mode voltage of either input signal voltage should not be allowed to go negative by more than 0.3V (@+25°C). The upper end of the common-mode voltage range is V<sub>CC</sub> -1.5V (@ 25°C), but either or both inputs can go to +36V without damage, independent of the magnitude of V<sub>CC</sub>. 11. Due to proximity of external components, insure that coupling is not originating via stray capacitance between these external parts. This typically can

be detected as this type of capacitance increases at higher frequencies.

12. Typical values are all at T<sub>A</sub>=25°C conditions and represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration. The typical values are not tested and are not guaranteed on shipped production material.


13. All limits are guaranteed by testing or statistical analysis. Limits over the full temperature are guaranteed by design, but not tested in production. 5 of 15

LM2902/ LM2902A/ LM2904/ LM2904A

Notes:




## **Performance Characteristics**





# Performance Characteristics (Continued)





## **Application Information**

#### **General Information**

The LM2902/2904 series are op amps which operate with only a single power supply voltage, have true-differential inputs, and remain in the linear mode with an input common-mode voltage of  $0V_{DC}$ . These amplifiers operate over a wide range of power supply voltage with little change in performance characteristics. At +25°C amplifier operation is possible down to a minimum supply voltage of  $2.3V_{DC}$ .

Precautions should be taken to insure that the power supply for the integrated circuit never becomes reversed in polarity or that the unit is not inadvertently installed backwards in a test socket as an unlimited current surge through the resulting forward diode within the IC could cause fusing of the internal conductors and result in a destroyed unit.

Large differential input voltages can be easily accommodated and, as input differential voltage protection diodes are not needed, no large input currents result from large differential input voltages. The differential input voltage may be larger than V<sup>+</sup> without damaging the device. Protection should be provided to prevent the input voltages from going negative more than  $-0.3V_{DC}$  (@  $+25^{\circ}C$ ). An input clamp diode with a resistor to the IC input terminal can be used.

To reduce the power supply current drain, the amplifiers have a Class A output stage for small signal levels which converts to Class B in a large signal mode. These allow the amplifiers to both source and sink large output currents. Therefore both NPN and PNP external current boost transistors can be used to extend the power capability of the basic amplifiers. The output voltage needs to raise approximately 1 diode drop above ground to bias the on-chip vertical PNP transistor for output current sinking applications.

For AC applications, where the load is capacitive coupled to the output of the amplifier, a resistor should be used, from the output of the amplifier to ground to increase the Class A bias current and prevent crossover distortion. Where the load is directly coupled, as in DC applications, there is no crossover distortion.

Capacitive loads which are applied directly to the output of the amplifier reduce the loop stability margin. Values of 50pF can be accommodated using the worst-case non-inverting unity gain connection. Large closed loop gains or resistive isolation should be used if larger load capacitance must be driven by the amplifier.

The bias network of the LM2902/2904 series establishes a quiescent current which is independent of the magnitude of the power supply voltage over the range of 3V<sub>DC</sub> to 30V<sub>DC</sub>.

Output short circuits either to ground or to the positive power supply should be of short time duration. Units can be destroyed, not as a result of the short circuit current causing metal fusing, but rather due to the large increase in IC chip dissipation which will cause eventual failure due to excessive function temperatures. Putting direct short-circuits on more than one amplifier at a time will increase the total IC power dissipation to destructive levels, if not properly protected with external dissipation limiting resistors in series with the output leads of the amplifiers. The larger value of output source current which is available at +25°C provides a larger output current capability at elevated temperatures (see typical performance characteristics) than a standard IC op amp.

The circuits presented in the section on typical applications emphasize operation on only a single power supply voltage. If complementary power supplies are available, all of the standard op amp circuits can be used. In general, introducing a pseudo-ground (a bias voltage reference of  $V_{CC}/2$ ) will allow operation above and below this value in single power supply systems. Many application circuits are shown which take advantage of the wide input common-mode voltage range which includes ground. In most cases, input biasing is not required and input voltages which range to ground can easily be accommodated.




## Application Information (Continued)

#### Power Supply Bypassing and Layout


The LM29xx family operate both single supply voltage range 3V to 36V or dual supply voltage ±1.5V to ±18V.

As with any operation amplifier, proper supply bypassing is critical for low noise performance and high power supply rejection. For single supply operation system, a minimum 0.1µF bypass capacitor should be recommended to place as close as possible between the V<sub>CC</sub> Pin and GND. For dual supply operation, both the positive supply pin and negative supply pin should be bypassed to ground with a separate 0.1µF ceramic capacitor.

2.2µF tantalum capacitor can be added for better performance. Keep the length of leads and traces that connect capacitors between the LM29xx power supply pin and ground as short as possible.



## Ordering Information (Note 14)




Part Number	Baakaga Cada	Pookoging	13" Tape a	and Reel
Fait Nulliber	Package Code	Packaging	Quantity	Part Number Suffix
LM2902T14-13	T14	TSSOP-14	2,500/Tape & Reel	-13
LM2902AT14-13	T14	TSSOP-14	2,500/Tape & Reel	-13
LM2902S14-13	S14	SO-14	2,500/Tape & Reel	-13
LM2902AS14-13	S14	SO-14	2,500/Tape & Reel	-13
LM2904S-13	S	SO-8	2,500/Tape & Reel	-13
LM2904AS-13	S	SO-8	2,500/Tape & Reel	-13
LM2904AM8-13	M8	MSOP-8	2,500/Tape & Reel	-13
LM2904M8-13	M8	MSOP-8	2,500/Tape & Reel	-13
LM2904ATH-13	TH	TSSOP-8	2,500/Tape & Reel	-13
LM2904TH-13	TH	TSSOP-8	2,500/Tape & Reel	-13

Note: 14. For packaging details, go to our website at http://www.diodes.com/products/packages.html




## **Marking Information**


### (1) TSSOP-14 and SO-14



(2) SO-8




(3) MSOP-8 & TSSOP-8





# **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.




	SO-8				
Dim	Min	Max			
Α	-	1.75			
A1	0.10	0.20			
A2	1.30	1.50			
A3	0.15	0.25			
b	0.3	0.5			
D	4.85	4.95			
ш	5.90	6.10			
E1	3.85	3.95			
e	1.27	Тур			
h	-	0.35			
L	0.62	0.82			
θ	0°	8°			
All Di	mension	s in mm			


TSSOP-8


MSOP-8



TSSOP-8					
Dim	Min	Max	Тур		
а	0.09	-	-		
Α	-	1.20	-		
A1	0.05	0.15	-		
A2	0.825	1.025	0.925		
b	0.19	0.30	-		
С	0.09	0.20	-		
D	2.90	3.10	3.025		
е	-	-	0.65		
Е	-	-	6.40		
E1	4.30	4.50	4.425		
L	0.45	0.75	0.60		
All	Dimens	sions in	mm		







LM2902/ LM2902A/ LM2904/ LM2904A Document number: DS36780 Rev. 3 - 2 11 of 15 www.diodes.com


MSOP-8					
Dim	Min	Max	Тур		
Α	-	1.10	-		
A1	0.05	0.15	0.10		
A2	0.75	0.95	0.86		
A3	0.29	0.49	0.39		
b	0.22	0.38	0.30		
С	0.08	0.23	0.15		
D	2.90	3.10	3.00		
Ε	4.70	5.10	4.90		
E1	2.90	3.10	3.00		
E3	2.85	3.05	2.95		
е	-	-	0.65		
L	0.40	0.80	0.60		
а	0°	8°	4°		
X	-	-	0.750		
У	_	-	0.750		
	Dimen	sions	in mm		

SO-8



# Package Outline Dimensions (Continued)


Please see http://www.diodes.com/package-outlines.html for the latest version.



SO-14					
Dim	Min	Max			
Α	1.47	1.73			
A1	0.10	0.25			
A2	1.45	1.45 Typ			
В	0.33	0.51			
D	8.53	8.74			
ш	3.80	3.99			
e	1.27	Тур			
Н	5.80	6.20			
L	0.38	1.27			
θ	0°	8°			
All Di	mensions	s in mm			

TSSOP-14

SO-14




•	TSSOP-14					
Dim	Min	Max				
a1	7° (	4X)				
a2	0°	8°				
Α	4.9	5.10				
В	4.30	4.50				
С	-	1.2				
D	0.8	1.05				
F	1.00	Тур				
F1	0.45	0.75				
G	0.65	Тур				
К	0.19	0.30				
L	L 6.40 Typ					
All Dir	nension	s in mm				



# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.



 Dimensions
 Value (in mm)


 X
 0.60

 Y
 1.55

 C1
 5.4


 C2
 1.27


TSSOP-8



Dimensions	Value (in mm)
Х	0.45
Y	1.78
C1	7.72
C2	0.65
C3	4.16
G	0.20

MSOP-8






SO-8




# Suggested Pad Layout (Continued)

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
Х	0.60
Y	1.50
C1	5.4
C2	1.27

TSSOP-14



Dimensions	Value (in mm)
Х	0.45
Y	1.45
C1	5.9
C2	0.65

ww.diodes.com/package-outlines.html for the la



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com