Phototriac, Zero Crossing, 1.5 kV/µs dV/dt, 600 V



www.vishay.com

DESCRIPTION

The VO3062 and VO3063 triac driver family consists of a GaAs infrared LED optically coupled to a monolithic photosensitive zero crossing triac detector chip.

The 600 V blocking voltage permits control of off-line voltages up to 240 $V_{AC},$ with a safety factor of more than two, and is sufficient for as much as 380 V.

FEATURES

- 1500 V/µs dV/dt minimum
- 600 V blocking voltage
- 100 mA on-state current
- Zero crossing detector
- Low input trigger current
- 6 pin DIP package
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Household appliances
- Triac drive/AC motor drives
- Solenoid/valve controls
- Office automation equipment/machine
- Temperature (HVAC)/lighting controls
- Switching power supply

AGENCY APPROVALS

- UL1577, file no. E52744 system code H
- cUL file no. E52744, equivalent to CSA bulletin 5A
- DIN EN 60747-5-5 (VDE 0884-5) available with option 1



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

1



ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT		
INPUT							
Reverse voltage			V _R	6	V		
Forward current - continuous			I _F	60	mA		
Power dissipation			P _{diss}	100	mW		
OUTPUT							
Off state output terminal voltage		VO3062, VO3063	V _{DRM}	600	V		
Peak non-repetitive surge current	PW = 100 μs, 120 pps		I _{TSM}	1	А		
Power dissipation			P _{diss}	200	mW		
On-state RMS current			I _{T(RMS)}	100	mA		
COUPLER							
Isolation test voltage	t = 1 s		V _{ISO}	5300	V _{RMS}		
Total power dissipation			P _{tot}	300	mW		
Operating temperature range			T _{amb}	- 55 to + 100	°C		
Storage temperature range			T _{stg}	- 55 to + 150	°C		
Soldering temperature ⁽¹⁾	maximum ≤ 10 s		T _{sld}	260	°C		

Notes

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
maximum ratings for extended periods of the time can adversely affect reliability.

(1) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP) "Assembly Instructions" (<u>www.vishay.com/doc?80054</u>).

THERMAL CHARACTERISTICS				
PARAMETER	SYMBOL	VALUE	UNIT	
Maximum LED junction temperature	T _{jmax.}	125	°C	т.
Maximum output die junction temperature	T _{jmax.}	125	°C	, T
Thermal resistance, junction emitter to board	θ_{JEB}	150	°C/W	$\frac{1}{\overline{T_{c}}} = $
Thermal resistance, junction emitter to case	θ_{JEC}	139	°C/W	
Thermal resistance, junction detector to board	θ_{JDB}	78	°C/W	
Thermal resistance, junction detector to case	θ_{JDC}	103	°C/W	
Thermal resistance, junction emitter to junction detector	θ_{JED}	496	°C/W	' β _{θa}
Thermal resistance, case to ambient	θ_{CA}	3563	°C/W	1999 7 _A

Note

 The thermal model is represented in the thermal network below. Each resistance value given in this model can be used to calculate the temperatures at each node for a given operating condition. The thermal resistance from board to ambient will be dependent on the type of PCB, layout and thickness of copper traces. For a detailed explanation of the thermal model, please reference Vishay's Thermal Characteristics of Optocouplers application note.



ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT							
Reverse current	V _R = 6 V		I _R			10	μA
Forward voltage	I _F = 30 mA		V _F		1.2	1.5	V
OUTPUT							
Leakage with LED off, either direction	V _{DRM} = 600 V		I _{DRM}		10	500	nA
Critical rate of rise off-state voltage	V _D = 400 V		dV/dt	1500	2000		V/µs
COUPLER							
LED trigger current,		VO3063	I _{FT}			5	mA
current required to latch output		VO3062	I _{FT}			10	mA
Peak on-state voltage, either direction	I _{TM} = 100 mA Peak, I _F = Rated I _{FT}		V_{TM}		1.7	3	V
Holding current, either direction			Ι _Η		200		μA
Inhibit voltage (MT1-MT2 voltage above which device will not trigger)			V _{INH}		12	22	V
Leakage in inhibited state	I _F = 10 mA maximum, at rated V _{DRM} , off state		V _{DRM2}		250	1000	μA

Note

 Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

SAFETY AND INSULATION RATINGS							
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT		
Climatic classification (according to IEC 68 part 1)			55/100/21				
Pollution degree (DIN VDE 0109)			2				
Comparative tracking index	CTI	175					
Peak transient overvoltage	V _{IOTM}	8000			V _{peak}		
Peak working insulation voltage	V _{IORM}	890			V _{peak}		
Isolation resistance at T_{amb} = 100 °C, V_{DC} = 500 V	R _{IO}	10 ¹¹			Ω		
Isolation resistance at T_{amb} = 25 °C, V_{DC} = 500 V	R _{IO}	10 ¹²			Ω		
Partial discharge test voltage (method a, $V_{pd} = V_{IORM} \times 1.875$)	V _{pd}	1325			V _{peak}		
Safety rating - power	P _{SO}			400	mW		
Safety rating - input current	I _{SI}			150	mA		
Safety rating - temperature	T _{SI}			165	°C		
Clearance distance (Standard DIP-6)		7			mm		
Creepage distance (Standard DIP-6)		7			mm		
Clearance distance (400 mil DIP-6)		8			mm		
Creepage distance (400 mil DIP-6)		8			mm		

Note

 According to DIN EN60747-5-5 (see figure 4). This optocoupler is suitable for safe electrical isolation only within the safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.



TYPICAL CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified)



Fig. 1 - Forward Voltage vs. Forward Current



Fig. 2 - Off-State Leakage Current vs. Temperature



Fig. 3 - On-State Current vs. VTM



Fig. 4 - Normalized Trigger Current vs. Temperature



Fig. 5 - Turn-on Time vs. LED Current



Fig. 6 - Normalized Holding Current vs. Temperature

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





Fig. 7 - Turn-on Time vs. Temperature



VO3062, VO3063

Vishay Semiconductors

Fig. 8 - Trigger Current vs. Pulse Width





Rev. 2.0, 18-Apr-13

Document Number: 83748

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



VO3062, VO3063

Vishay Semiconductors

PACKAGE MARKING (example)



Notes

- The VDE logo is only marked on option1 parts.
- Tape and reel suffix (T) is not part of the package marking.



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.