



NOTE:

1. MATERIAL:
 - 1.1 INSULATOR: UL 94V-0
 - 1.2 CONTACT: (T=0.20mm)
 - 1.3 SHELL: (T=0.30mm)
2. ELECTRICAL CHARACTERISTICS:
 - 2.1 CONTACT RESISTANCE: 30mΩ MAXIMUM
 - 2.2 CONTACT CURRENT RATING: 1.5A
 - 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 500 V R.M.S.
- 2.4 INSULATION RESISTANCE 1000 MEGOHMS MIN
- 2.5 OPERATING TEMPERATURE: -40° C ~ 85° C
- 3 MECHANICAL CHARACTERISTICS:
 - 3.1 MATING FORCE: 3.57kg MAX
 - 3.2 UNMATED FORCE: 1.02kg MIN
 - 3.3 DURABILITY: MANDATORY: 1500 CYCLES
4. PLATING
 - 4.1 TERMINAL: 50u" MIN NICKEL ALL OVER
100u" MIN TIN ON SOLDER AREA
(1~30)u"Au ON CONTACT AREA
 - 4.2 SHELL: 50u" MIN. NICKEL ALL OVER

产品图

深圳市精拓金电子有限公司

公差一览表
TOLERANCE UNLESS OTHERWISE:

X	±0.30	X	±5.°
.X	±0.25	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.10	.XXX	±0.5°

单位 UNITS	MM	制图 DRAWING	Gavin	制图料号 PRODUCT PART NO.	
比例 SCALE	1:1	审核 CHECK	郭治富	产品名称 PRODUCT NO.	USB 3.0 A/F 直立式有卷边H11.5
日期 DATE	2016-12-05	核准 APPRO	黄国荣	角法 VIEW	版本 VER
					A0

1 2 3 4 7 8 9 10

由 Autodesk 教育版产品制作