


Vishay Semiconductors

IR Sensor Module for Remote Control Systems




MECHANICAL DATA

Pinning:

1 = carrier OUT, 2 = GND, 3 = V_S

FEATURES

- Photo detector and preamplifier in one package
- AC coupled response from 30 kHz to 55 kHz, all data formats





- Improved shielding against electrical field disturbance
- AGC to suppress ambient noise
- High sensitivity, long receiving range
- Supply voltage: 2.5 V to 5.5 V
- Carrier out signal for IR repeater applications
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


DESCRIPTION

The TSMP58138 is a miniaturized sensor for receiving the modulated signal of infrared remote control systems. A PIN diode and preamplifier are assembled on a lead frame, the epoxy package is designed as an IR filter. The modulated output signal, carrier out, can be used for repeater applications and code learning applications.


This component has not been qualified according to automotive specifications.

PARTS TABLE					
Carrier frequency 38 kHz	TSMP58138				
Package	Minicast				
Pinning	1 = carrier OUT, 2 = GND, 3 = V _S				
Dimensions (mm)	5.0 W x 6.95 H x 4.8 D				
Mounting	Leaded				
Application	Repeater				

BLOCK DIAGRAM



APPLICATION CIRCUIT



Recommended circuit for best sensitivity of the TSOP9xx38 in repeater applications. It limits the output voltage swing $\rm V_{\rm O}$ to about 0.7 V in order to avoid internal coupling.



Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT				
Supply voltage (pin 3)		Vs	-0.3 to +6	V				
Supply current (pin 3)		I _S	5	mA				
Output voltage (pin 1)		Vo	-0.3 to 5.5	V				
Voltage at output to supply		V _S - V _O	-0.3 to (V _S + 0.3)	V				
Output current (pin 1)		I _O	5	mA				
Junction temperature		T _j	100	°C				
Storage temperature range		T _{stg}	-25 to +85	°C				
Operating temperature range		T _{amb}	-25 to +85	°C				
Power consumption	T _{amb} ≤ 85 °C	P _{tot}	10	mW				
Soldering temperature	t ≤ 10 s, 1 mm from case	T _{sd}	260	°C				

Note

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only
and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification
is not implied. Exposure to absolute maximum rating conditions for extended periods may affect the device reliability.

ELECTRICAL AND OPTICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)									
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT			
Supply current (pin 3)	$E_{V} = 0, V_{S} = 5 V$	I _{SD}	0.55	0.7	0.9	mA			
	E _v = 40 klx, sunlight	I _{SH}		0.8		mA			
Supply voltage		Vs	2.5		5.5	V			
Transmission distance	$E_v = 0$, test signal see fig. 1, IR diode TSAL6200, $I_F = 400 \text{ mA}$	d		20		m			
Output voltage low (pin 1)	$I_{OSL} = 0.5 \text{ mA}, E_e = 0.7 \text{ mW/m}^2,$ test signal see fig. 1	V _{OSL}			100	mV			
Minimum irradiance	Less than 5 missing or 5 additional sub carrier pulses related to one burst	E _{e min.}		1	2	mW/m²			
Maximum irradiance	Less than 5 missing or 5 additional sub carrier pulses related to one burst	E _{e max.}	30			W/m ²			
Directivity	Angle of half transmission distance	Ψ1/2		± 45		deg			

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Output Function




Fig. 2 - Frequency Dependence of Sensitivity






Fig. 3 - Relative Spectral Sensitivity vs. Wavelength




Fig. 4 - Horizontal Directivity





Fig. 5 - Vertical Directivity



Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.