AUTOMOTIVE

ROHS

HALOGEN

FREE GREEN

(5-2008)



Vishay Semiconductors

Silicon PIN Photodiode



DESCRIPTION

TEMD7000X01 is a high speed and high sensitive PIN photodiode. It is a miniature surface mount device (SMD) including the chip with a 0.23 mm² sensitive area detecting visible and near infrared radiation.

FEATURES

- Package type: surface mount
- Package form: 0805
- Dimensions (L x W x H in mm): 2 x 1.25 x 0.85
- Radiant sensitive area (in mm²): 0.23
- · High photo sensitivity
- · High radiant sensitivity
- · Suitable for visible and near infrared radiation
- Fast response times
- Angle of half sensitivity: $\phi = \pm 60^{\circ}$
- Floor life: 168 h, MSL 3, according to J-STD-020
- · Lead (Pb)-free reflow soldering
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



· High speed photo detector

PRODUCT SUMMARY				
COMPONENT	I _{ra} (μΑ)	φ (deg)	λ _{0.1} (nm)	
TEMD7000X01	3	± 60	350 to 1120	

Note

· Test conditions see table "Basic Characteristics"

ORDERING INFORMATION					
ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM		
TEMD7000X01	Tape and reel	MOQ: 3000 pcs, 3000 pcs/reel	0805		

Note

· MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Reverse voltage		V _R	60	V	
Power dissipation	T _{amb} ≤ 25 °C	P _V	215	mW	
Junction temperature		Tj	100	°C	
Operating temperature range		T _{amb}	-40 to +100	°C	
Storage temperature range		T _{stg}	-40 to +100	°C	
Soldering temperature	Acc. reflow solder profile fig. 8	T _{sd}	260	°C	
Thermal resistance junction / ambient	Acc. J-STD-051	R _{thJA}	270	K/W	

BASIC CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 50 mA	V _F		1		V
Breakdown voltage	$I_R = 100 \mu A, E = 0$	V _(BR)	60			V
Reverse dark current	V _R = 10 V, E = 0	I _{ro}		1	3	nA
Diode capacitance	$V_R = 0 V, f = 1 MHz, E = 0$	C _D		4		pF
	$V_R = 5 \text{ V}, f = 1 \text{ MHz}, E = 0$	C _D		1.3		pF
Open circuit voltage	$E_e = 1 \text{ mW/cm}^2, \lambda = 950 \text{ nm}$	Vo		350		mV
Temperature coefficient of Vo	$E_e = 1 \text{ mW/cm}^2, \lambda = 950 \text{ nm}$	TK _{Vo}		-2.6		mV/K
Short circuit current	$E_{e} = 1 \text{ mW/cm}^{2}, \lambda = 950 \text{ nm}$	l _k		3		μA
Temperature coefficient of I _k	$E_{e} = 1 \text{ mW/cm}^{2}, \lambda = 950 \text{ nm}$	TK _{lk}		0.1		%/K
Reverse light current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$, $V_R = 5 \text{ V}$	I _{ra}	2.4	3	3.6	μA
Angle of half sensitivity		φ		± 60		deg
Wavelength of peak sensitivity		λ_{p}		900		nm
Range of spectral bandwidth		λ _{0.1}		350 to 1120		nm
Rise time	$V_R = 10 \text{ V}, R_L = 1 \text{ k}\Omega, \lambda = 820 \text{ nm}$	t _r		100		ns
Fall time	$V_R = 10 \text{ V}, R_L = 1 \text{ k}\Omega, \lambda = 820 \text{ nm}$	t _f		100		ns

BASIC CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Reverse Dark Current vs. Ambient Temperature




Fig. 2 - Relative Reverse Light Current vs. Ambient Temperature




Fig. 3 - Reverse Light Current vs. Irradiance




Fig. 4 - Reverse Light Current vs. Reverse Voltage

max. 260

max. 30 s

245 °C

300

250

Vishay Semiconductors

REFLOW SOLDER PROFILE




Fig. 8 - Lead (Pb)-free Reflow Solder Profile acc. J-STD-020




Fig. 5 - Diode Capacitance vs. Reverse Voltage

1.0 0.9 0.8 0.7 0.6 0.5 0.4 0.3 0.2 0.1 400 500 600 700 800 900

Fig. 6 - Relative Spectral Sensitivity vs. Wavelength

S(λ)_{rel} - Relative Spectral Sensitivity 1000 1100 λ - Wavelength (nm)

0 10° 20° 30° rel - Relative Radiant Sensitivity - Angular Displacement 1.0 0.9 8.0 0.7 80 94 8013

Fig. 7 - Relative Radiant Sensitivity vs. Angular Displacement

DRYPACK

Devices are packed in moisture barrier bags (MBB) to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

FLOOR LIFE

Floor life (time between soldering and removing from MBB) must not exceed the time indicated on MBB label:

Floor life: 168 h

Conditions: T_{amb} < 30 °C, RH < 60 %


Moisture sensitivity level 3, according to J-STD-020.

DRYING


In case of moisture absorption devices should be baked before soldering. Conditions see J-STD-020 or label. Devices taped on reel dry using recommended conditions 192 h at 40 °C (+ 5 °C), RH < 5 %.



PACKAGE DIMENSIONS in millimeters



BLISTER TAPE DIMENSIONS in millimeters




Issue: 1; 23.02.07

21501

Not indicated tolerances ±0.1

REEL DIMENSIONS in millimeters



Drawing-No.: 9.800-5096.01-4

Issue: 2; 26.04.10

20875



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.