VS-E4PH3006L-N3

Vishay Semiconductors



Hyperfast Soft Recovery Diode, 30 A FRED Pt® Gen 4



PRODUCT SUMMARY									
I _{F(AV)}	30 A								
V _R	600 V								
V _F at I _F	1.37 V								
t _{rr} typ.	see Recovery table								
T _J max.	175 °C								
Package	TO-247AD 2L								
Diode variation	Single die								

FEATURES

- Gen 4 FRED Pt[®] technology
- Low I_{BBM} and reverse recovery charge
- · Very low forward voltage drop
- · Polymide passivated chip for high reliability standard
- 175 °C operating junction temperature
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

DESCRIPTION

Gen 4 Fred technology, state of the art, ultrafast V_F, soft switching optimized for Discontinuous (Critical) Mode (DCM) and IGBT F/W diode.

The minimized conduction loss, optimized stored charge and low recovery current minimized the switching losses and reduce over dissipation in the switching element and snubbers.

ABSOLUTE MAXIMUM RATINGS										
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS						
Cathode to anode voltage	V _R		600	V						
Average rectified current	I _{F(AV)}	T _C = 122 °C	30	•						
Single pulse forward current	I _{FSM}	T_C = 25 °C, t_p = 8.3 ms half sine wave	240	A						
Operating junction and storage temperatures	T _J , T _{Stg}		-55 to +175	°C						

ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)										
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS				
Breakdown voltage, blocking voltage	V_{BR}, V_{R}	I _R = 100 μA	600	-	-					
		I _F = 30 A	-	1.65	2					
		I _F = 60 A	-	1.95	-					
Forward voltage	V _F	I _F = 30 A, T _J = 125 °C	-	1.44	-	V				
Forward voltage		I _F = 60 A, T _J = 125 °C	-	1.78	-					
		I _F = 30 A, T _J = 150 °C	-	1.37	1.6					
		I _F = 60 A, T _J = 150 °C	-	1.68	-					
	1	$V_{R} = V_{R}$ rated	-	-	50					
Reverse leakage current	I _R	$T_J = 150 \text{ °C}, V_R = V_R \text{ rated}$		500	μA					
Junction capacitance	CT	V _R = 600 V	-	18.3	-	pF				

Revision: 19-Jan-17 Document Number: 95897 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000







www.vishay.com

Vishay Semiconductors

DYNAMIC RECOVERY CHARACTERISTICS ($T_J = 25$ °C unless otherwise specified)										
PARAMETER	SYMBOL	TEST C	MIN.	TYP.	MAX.	UNITS				
Reverse recovery time	+	T _J = 25 °C		-	55	-	ns			
	t _{rr}	T _J = 125 °C	I _F = 30 A dI _F /dt = 1000 A/μs V _B = 400 V	-	75	-				
Peak recovery current	I _{RRM}	T _J = 25 °C		-	13	-	A			
Feat recovery current		T _J = 125 °C		-	23	-				
	Q _{rr}	T _J = 25 °C	vR - 400 v	-	500	-	nC			
Reverse recovery charge		T _J = 125 °C		-	1250	-				

THERMAL - MECHANICAL SPECIFICATIONS										
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS				
Thermal resistance, junction to case	R _{thJC}		-	-	1	°C/W				
Thermal resistance, case to heat sink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.4	-					
Weight			-	6.0	-	g				
Weight			-	0.21	-	oz.				
Mounting torque			6.0	_	12	kgf · cm				
				-	(20)	(lbf · in)				
Marking device		Case style TO-247AD 2L		E4PH	3006L					






Fig. 1 - Typical Forward Voltage Drop Characteristics











Revision: 19-Jan-17	2	Document Number: 95897
For technical questions within your region:	: DiodesAmericas@vishay.com, DiodesAsia@visha	ay.com, DiodesEurope@vishay.com
	E WITHOUT NOTICE. THE PRODUCTS DESCRIE CIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay</u>	

Vishay Semiconductors








www.vishay.com

Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current





Note

⁽¹⁾ Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$;

 $\begin{array}{l} \mathsf{Pd} = \mathsf{Forward} \ \mathsf{power} \ \mathsf{loss} = \mathsf{I}_{\mathsf{F}(\mathsf{AV})} \ \mathsf{x} \ \mathsf{V}_{\mathsf{FM}} \ \mathsf{at} \ (\mathsf{I}_{\mathsf{F}(\mathsf{AV})}/\mathsf{D}) \ (\mathsf{see} \ \mathsf{fig. 5}); \\ \mathsf{Pd}_{\mathsf{REV}} = \mathsf{Inverse} \ \mathsf{power} \ \mathsf{loss} = \mathsf{V}_{\mathsf{R1}} \ \mathsf{x} \ \mathsf{I}_{\mathsf{R}} \ (\mathsf{1} - \mathsf{D}); \ \mathsf{I}_{\mathsf{R}} \ \mathsf{at} \ \mathsf{V}_{\mathsf{R1}} = \mathsf{rated} \ \mathsf{V}_{\mathsf{R}} \end{array}$




Fig. 7 - Typical Reverse Recovery Time vs. dl_F/dt




Fig. 8 - Typical Stored Charge vs. dl_F/dt

Revision: 19-Jan-17

3

Document Number: 95897

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors






Fig. 9 - Typical Reverse Current vs. dl_F/dt

ORDERING INFORMATION TABLE

Device code	VS-	E	4	Р	Н	30	06	L	-N3	
	1	2	3	4	5	6	7	8	9	
	1 -	1 - Vishay Semiconductors product								
	2 ·	2 - Circuit configuration:								
		E = single diode, 2 pins								
	3 -	3 - FRED Pt Gen 4								
	4	• P=	TO-247	' packag	е					
	5.	- Pro	cess typ	be:						
		H =	hyperfa	st recov	very					
	6	- Cur	rent rati	ng (30 =	30 A)					
	7 -	7 - Voltage rating (06 = 600 V)								
	8 -	- L = long lead								
	9 -			ntal digit: en-free,		complia	nt, and	totally l	ead (Pb	

ORDERING INFORMATION (Example)									
PREFERRED P/N	QUANTITY PER TUBE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION						
VS-E4PH3006L-N3	25	500	Antistatic plastic tube						

LINKS TO RELATED DOCUMENTS							
Dimensions	TO-247AD 2L	www.vishay.com/doc?95536					
Part marking information	TO-247AD 2L	www.vishay.com/doc?95648					

Revision: 19-Jan-17 For technical questions within


For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors


TO-247AD 2L

DIMENSIONS in millimeters and inches



(4) Section C - C, D - D

(b, b2)



SYMBOL	MILLIMETERS		INCHES		NOTES	SYMBOL	MILLIMETERS		INCHES		NOTES	
STIVIDUL	MIN.	MAX.	MIN.	MAX.	NOTES		STIVIDUL	MIN.	MAX.	MIN.	MAX.	INUTES
А	4.65	5.31	0.183	0.209			E	15.29	15.87	0.602	0.625	3
A1	2.21	2.59	0.087	0.102			E1	13.46	-	0.53	-	
A2	1.50	2.49	0.059	0.098			е	5.46	BSC	0.215	5 BSC	
b	0.99	1.40	0.039	0.055			ØK	0.2	254	0.0	010	
b1	0.99	1.35	0.039	0.053			L	19.81	20.32	0.780	0.800	
b2	1.65	2.39	0.065	0.094			L1	3.71	4.29	0.146	0.169	
b3	1.65	2.34	0.065	0.092			ØР	3.56	3.66	0.14	0.144	
С	0.38	0.89	0.015	0.035			Ø P1	-	6.98	-	0.275	
c1	0.38	0.84	0.015	0.033			Q	5.31	5.69	0.209	0.224	
D	19.71	20.70	0.776	0.815	3]	R	4.52	5.49	0.178	0.216	
D1	13.08	-	0.515	-	4		S	5.51	BSC	0.217	7 BSC	
D2	0.51	1.35	0.020	0.053]						

Notes

⁽¹⁾ Dimensioning and tolerancing per ASME Y14.5M-1994

(2) Contour of slot optional

- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- ⁽⁵⁾ Lead finish uncontrolled in L1
- ⁽⁶⁾ Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- $^{(7)}$ Outline conforms to JEDEC $^{\circledast}$ outline TO-247 with exception of dimension Q

Revision: 20-Apr-17

Document Number: 95536 1 sia@vishay.com, DiodesEurope@vishay.com For technical questions within your region: DiodesAmericas@vishay.com, DiodesA THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.