



SBR10U200P5

10A SBR SUPER BARRIER RECTIFIER PowerDI5

### Product Summary (@ TA = +25°C)

V <sub>RRM</sub> (V)	I <sub>O</sub> (A)	V <sub>F</sub> Max (V) @ +25°C	I <sub>R</sub> Max (mA) @ +25°C
200	10	0.88	0.1

# **Description & Applications**

Packaged in the compact thermally efficient PowerDI®5 package, provides low V<sub>F</sub> and low reverse leakage at high temperatures.

It is ideal for use in the following applications:

- Bridge Diodes
- Freewheeling Diodes
- Blocking Diodes
- Reverse Protection Diodes

### **Features and Benefits**

- Ultra Low Forward Voltage Drop
- Excellent High Temperature Stability
- Patented Super Barrier Rectifier Technology
- Soft, Fast Switching Capability
- +175°C Operating Junction Temperature
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An Automotive-Compliant Part is Available Under Separate Datasheet (SBR10U200P5Q)

#### **Mechanical Data**

- Case: PowerDI5
- Case Material: Molded Plastic, "Green" Molding Compound; UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed over Copper Leadframe;
   Solderable per MIL-STD-202, Method 208 <sup>3</sup>
- Polarity: See Diagram
- Weight: 0.093 grams (Approximate)

## PowerDI5







**Bottom View** 



Note: Pins Left & Right must be electrically connected at the printed circuit board.


## Ordering Information (Note 4)

Part Number	Case	Packaging
SBR10U200P5-13	PowerDI5	5,000/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
- 2. See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

# **Marking Information**



S10U200 = Product Type Marking Code

Oli = Manufacturers' Code Marking

YYWW = Date Code Marking

YY = Last Two Digits of Year (ex: 16 for 2016)

WW = Week Code (01 to 53)

K = Factory Designator



## Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>RM</sub>	200	>
Average Rectified Output Current	lo	10	Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I <sub>FSM</sub>	180	А
Repetitive Peak Avalanche Power (1µs, +25°C)	P <sub>ARM</sub>	3,000	W

## **Thermal Characteristics**

Characteristic			Value	Unit
Typical Thermal Resistance Junction to Ambient (Note 5)			70	°C/W
Typical Thermal Resistance Junction to Case (Note 5)		$R_{\theta JC}$	14	°C/W
Typical Thermal Resistance Junction to Ambient (Note 6)		$R_{\theta JA}$	20	°C/W
Typical Thermal Resistance Junction to Case (Note 6)		$R_{\theta}$ JC	3	°C/W
Operating Temperature Range	Reverse Mode DC Forward Mode (Note 7)	TJ	-65 to +175 ≤200	°C
Storage Temperature Range		T <sub>STG</sub>	-65 to +175	°C


# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Forward Voltage Drop	V <sub>F</sub>		0.75 0.62	0.82 0.67	V	I <sub>F</sub> = 5A, T <sub>J</sub> = +25°C I <sub>F</sub> = 5A, T <sub>J</sub> = +125°C
Leakage Current (Note 8)	I <sub>R</sub>	_	0.83 —	0.88		$I_F = 10A$ , $T_J = +25$ °C $V_R = 200V$ , $T_J = +25$ °C
Leakage Guiterii (Note 6)	iK		0.18	10	111/4	$V_R = 200V, T_J = +125$ °C


Notes:


- 5. Device mounted on FR-4 PCB with minimum recommended pad layout per http://www.diodes.com/package-outlines.html.
- 6. Device mounted on FR-4 PCB with 1-inch pad layout and additional HK2 (45mm x 20mm x12mm).
- Max junction temperature guaranteed for 2 hours.
   Short duration pulse test used to minimize self heat effect.


























Fig. 8 Maximum Avalanche Power vs. Pulse Duration



# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### PowerDI5




PowerDI5					
Dim	Min	Max	Тур		
Α	1.05	1.15	1.10		
A1	0.00	0.05			
A2	0.33	0.43	0.381		
b1	0.80	0.99	0.89		
b2	1.70	1.88	1.78		
D	3.90	4.05	3.966		
D2			3.054		
Е	6.40	6.60	6.504		
е			1.84		
E1	5.30	5.45	5.37		
E2			3.549		
L	0.75	0.95	0.85		
L1	0.50	0.65	0.57		
W	1.10	1.41	1.255		
All Dimensions in mm					

# Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

### PowerDI5



Dimensions	Value (in mm)		
С	1.840		
G	0.852		
Х	1.390		
X1	3.360		
Υ	1.400		
Y1	4.860		



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com