


### Features

- N-Channel  
30V/8A,  
 $R_{DS(ON)} = 12m\Omega$  (Typ.) @  $V_{GS} = 10V$   
 $R_{DS(ON)} = 16m\Omega$  (Typ.) @  $V_{GS} = 4.5V$
- P-Channel  
-30V/-7A,  
 $R_{DS(ON)} = 18m\Omega$  (Typ.) @  $V_{GS} = -10V$   
 $R_{DS(ON)} = 25m\Omega$  (Typ.) @  $V_{GS} = -4.5V$
- Reliable and Rugged
- ESD Protected
- Lead Free and Green Devices Available (RoHS Compliant)

### Applications

- Load Switch

### Pin Description



### Absolute Maximum Ratings

Symbol	Parameter		N-Channel	P-Channel	Unit
<b>Common Ratings</b> ( $T_A = 25^\circ C$ Unless Otherwise Noted)					
$V_{DSS}$	Drain-Source Voltage		30	-30	V
$V_{GSS}$	Gate-Source Voltage		$\pm 12$	$\pm 12$	
$T_J$	Maximum Junction Temperature		150	150	$^\circ C$
$T_{STG}$	Storage Temperature Range		-55 to 150	-55 to 150	$^\circ C$
$I_S$	Diode Continuous Forward Current	$T_A = 25^\circ C$	2.7	-2.5	A
<b>Mounted on Large Heat Sink</b>					
$I_{DP}^{①}$	300 $\mu s$ Pulse Drain Current Tested	$T_A = 25^\circ C$	32	-28	A
$I_D^{②}$	Continuous Drain Current ( $V_{GS} = \pm 10V$ )	$T_A = 25^\circ C$	8	-7	A
		$T_A = 70^\circ C$	6.5	-5.6	
$P_D$	Maximum Power Dissipation	$T_A = 25^\circ C$	2	2	W
		$T_A = 70^\circ C$	1.3	1.3	
$R_{\theta JC}$	Thermal Resistance-Junction to Case		TBD	TBD	$^\circ C/W$
$R_{\theta JA}^{③}$	Thermal Resistance-Junction to Ambient		62.5	62.5	$^\circ C/W$
<b>Drain-Source Avalanche Ratings</b>					
$E_{AS}^{④}$	Avalanche Energy, Single Pulsed		TBD	TBD	mJ

**Electrical Characteristics** ( $T_A=25^\circ\text{C}$  Unless Otherwise Noted)

Symbol	Parameter	Test Condition	RU30C8H			Unit	
			Min.	Typ.	Max.		
<b>Static Characteristics</b>							
$BV_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_{DS}=250\mu A$	N	30		V	
		$V_{GS}=0V, I_{DS}=-250\mu A$	P	-30			
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=30V, V_{GS}=0V$	N		1	$\mu A$	
		$T_J=125^\circ C$			30		
		$V_{DS}=-30V, V_{GS}=0V$	P		-1		
		$T_J=125^\circ C$			-30		
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_{DS}=250\mu A$	N	1.2	1.8	2.4	V
		$V_{DS}=V_{GS}, I_{DS}=-250\mu A$	P	-1.2	-1.8	-2.4	
$I_{GSS}$	Gate Leakage Current	$V_{GS}=\pm 12V, V_{DS}=0V$	N			$\pm 10$	$\mu A$
		$V_{GS}=\pm 12V, V_{DS}=0V$	P			$\pm 10$	
$R_{DS(ON)}^{(5)}$	Drain-Source On-state Resistance	$V_{GS}=10V, I_{DS}=8A$	N		12	15	m $\Omega$
		$V_{GS}=-10V, I_{DS}=-6A$	P		18	25	
		$V_{GS}=4.5V, I_{DS}=7A$	N		16	25	
		$V_{GS}=-4.5V, I_{DS}=-5A$	P		25	35	
<b>Diode Characteristics</b>							
$V_{SD}^{(5)}$	Diode Forward Voltage	$I_{SD}=1A, V_{GS}=0V$	N			1.2	V
		$I_{SD}=-1A, V_{GS}=0V$	P			-1.2	
$t_{rr}$	Reverse Recovery Time	N-Channel $I_{SD}=8A, di_{SD}/dt=100A/\mu s$	N		12		ns
			P		17		
$Q_{rr}$	Reverse Recovery Charge	P-Channel $I_{SD}=-7A, di_{SD}/dt=100A/\mu s$	N		3		nC
			P		9		
<b>Dynamic Characteristics<sup>(6)</sup></b>							
$R_G$	Gate Resistance	$V_{GS}=0V, V_{DS}=0V, F=1MHz$	N		1.8		$\Omega$
			P		3		
$C_{iss}$	Input Capacitance	N-Channel $V_{GS}=0V, V_{DS}=15V,$ Frequency=1.0MHz	N		340		pF
			P		780		
$C_{oss}$	Output Capacitance	P-Channel $V_{GS}=0V, V_{DS}=-15V,$ Frequency=1.0MHz	N		75		
			P		155		
$C_{rss}$	Reverse Transfer Capacitance	N-Channel $V_{GS}=0V, V_{DS}=-15V,$ Frequency=1.0MHz	N		50		
			P		95		

**Electrical Characteristics** ( $T_A=25^{\circ}\text{C}$  Unless Otherwise Noted)






Symbol	Parameter	Test Condition	RU30C8H			Unit
			Min.	Typ.	Max.	
<b>Dynamic Characteristics</b> <sup>⑥</sup>						
$t_{d(ON)}$	Turn-on Delay Time	N-Channel $V_{DD}=15\text{V}, I_{DS}=8\text{A},$ $V_{GEN}=10\text{V}, R_G=6\Omega$  P-Channel $V_{DD}=-15\text{V}, I_{DS}=-7\text{A},$ $V_{GEN}= -10\text{V}, R_G=6\Omega$	N		5	ns
			P		9	
$t_r$	Turn-on Rise Time		N		3	
			P		6	
$t_{d(OFF)}$	Turn-off Delay Time		N		15	
			P		21	
$t_f$	Turn-off Fall Time		N		4	
			P		7	
<b>Gate Charge Characteristics</b> <sup>⑥</sup>						
$Q_g$	Total Gate Charge	N-Channel $V_{DS}=24\text{V}, V_{GS}=10\text{V},$ $I_{DS}=8\text{A}$  P-Channel $V_{DS}=-24\text{V}, V_{GS}= -10\text{V},$ $I_{DS}=-7\text{A}$	N		8	nC
			P		15	
$Q_{gs}$	Gate-Source Charge		N		1.2	
			P		2.5	
$Q_{gd}$	Gate-Drain Charge		N		2	
			P		3.5	

- Notes:
- ① Pulse width limited by safe operating area.
  - ② Calculated continuous current based on maximum allowable junction temperature.
  - ③ When mounted on 1 inch square copper board,  $t \leq 10\text{sec}$ . The value in any given application depends on the user's specific board design.
  - ④ Limited by  $T_{Jmax}$ . Starting  $T_J = 25^{\circ}\text{C}$ .
  - ⑤ Pulse test; Pulse width  $\leq 300\mu\text{s}$ , duty cycle  $\leq 2\%$ .
  - ⑥ Guaranteed by design, not subject to production testing.







**Ordering and Marking Information**

<b>Device</b>	<b>Marking</b>	<b>Package</b>	<b>Packaging</b>	<b>Quantity</b>	<b>Reel Size</b>	<b>Tape width</b>
RU30C8H	RU30C8H	SOP-8	Tape&Reel	2500	13"	12mm






**Typical Characteristics(N-Channel)**









**Typical Characteristics(N-Channel)**



**Typical Characteristics(P-Channel)**




**Typical Characteristics(P-Channel)**





**Package Information**

**SOP-8**



SYMBOL	MM			INCH		
	MIN	NOM	MAX	MIN	NOM	MAX
A	1.300	1.525	1.750	0.051	0.060	0.069
A1	0.050	0.150	0.250	0.002	0.006	0.010
A2	1.350	1.450	1.550	0.053	0.057	0.061
b	0.330	0.420	0.510	0.013	0.017	0.020
c	0.170	0.210	0.250	0.007	0.008	0.010
D	4.700	4.900	5.100	0.185	0.193	0.201
E	3.800	3.900	4.000	0.150	0.154	0.157
E1	5.800	6.000	6.200	0.228	0.236	0.244
e	1.270 BSC			0.050 BSC		
L	0.400	0.835	1.270	0.016	0.033	0.050
$\theta$	0°		8°	0°		8°

**Customer Service****Worldwide Sales and Service:**

Sales@ruichips.com

**Technical Support:**

Technical@ruichips.com

**Investor Relations Contacts:**

Investor@ruichips.com

**Marcom Contact:**

Marcom@ruichips.com

**Editorial Contact:**

Editorial@ruichips.com

**HR Contact:**

HR@ruichips.com

**Legal Contact:**

Legal@ruichips.com

**Shen Zhen RUICHIPS Semiconductor CO., LTD**

Room 501, the 5floor An Tong Industrial Building,  
NO.207 Mei Hua Road Fu Tian Area Shen Zhen City, CHINA

**TEL:** (86-755) 8311-5334

**FAX:** (86-755) 8311-4278

**E-mail:** Sales-SZ@ruichips.com