

Positive Thermal Coefficent

SMD0603 Series





Description

The 0603 series provides miniature surface mount resettable overcurrent protection with holding current from 0.05A to 1.00A. This world's smallest PTC is suitable for ultra portable applications where space is at a premium and the device current is low.




Features

- I(hold): 0.05~1.00A
- · Very high voltage surge capabilities
- · Available in lead-free version
- · Fast response to fault current
- · RoHS compliant, Lead- Free and Halogen-Free
- · Low resistance
- · Compact design saves board space
- · Compatible with high temperature solders

Applications


- · USB peripherals
- · Disk drives
- · CD-ROMs
- · General electronics
- · Disk drives
- · Set-top-box and HDMI
- Mobile Internet Device (MID)
- · PDAs / digital cameras
- · Game console port protection
- · Plug and play protection for motherboards and peripherals
- · Mobile phones battery and port protection

Product Name









Type Number	I _{hold} I _{ti}	I _{trip}	Maximum Time To Trip		V _{max}	I _{max}	P _{d typ}	R _{min}	R _{1max}	Package	Package Dimensions (mm)						
			Time io	o mp	пр						Α		В		С		D
	Α	Α	Current A	Time (Sec.)	V _{DC}	А	W	Ω	Ω		min	max	min	max	min	max	min
SMD0603P005TF	0.05	0.2	0.5	1	15	40	0.5	2	10	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P010TF	0.1	0.3	0.5	1	16	40	0.5	0.9	6	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P020TF	0.2	0.5	1	0.6	9	40	0.5	0.55	3.5	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P020TF/16	0.2	0.5	1	0.6	16	40	0.5	0.55	3.5	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P025TF	0.25	0.55	8	80.0	9	40	0.5	0.5	3	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P025TF/16	0.25	0.55	8	0.08	16	40	0.5	0.5	3	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P035TF	0.35	0.75	8	0.1	6	40	0.5	0.2	1.4	0603	1.45	1.85	0.65	1.05	0.4	1	0.1
SMD0603P050TF	0.5	1	8	0.1	6	40	0.5	0.1	0.8	0603	1.45	1.85	0.65	1.05	0.5	1.1	0.1
SMD0603P050TF/12	0.5	1	8	0.1	12	40	0.5	0.1	0.8	0603	1.45	1.85	0.65	1.05	0.5	1.1	0.1
SMD0603P075TF	0.75	1.4	8	0.1	6	40	0.5	0.06	0.45	0603	1.45	1.85	0.65	1.05	0.5	1.1	0.1
SMD0603P100TF	1.0	2.0	8	0.1	6	40	0.5	0.04	0.3	0603	1.45	1.85	0.65	1.05	0.5	1.1	0.1

lhold = Hold current: maximum current device will pass without tripping in 25°C still air. Itrip = Trip current: minimum current at which the device will trip in 25 °C still air.

Vmax = Maximum voltage device can withstand without damage at rated current (I max)

Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax)

Pd typ = Typical power dissipated from device when in the tripped state at 25 °C still air.

Rmin = Minimum resistance of device in initial (un-soldered) state.


R1max = Maximum resistance of device at 25 °C measured one hour after tripping or reflow soldering of 260 °C for 20 sec.





Thermal Derating Chart Recommended Hold Current (A) at Ambient Temperature (°C)									
Part Numberr	-40℃	-20℃	0℃	25℃	40℃	50 ℃	60℃	70℃	85℃
SMD0603P005TF	0.10	0.28	0.10	0.05	0.06	0.048	0.040	0.031	0.028
SMD0603P010TF	0.14	0.12	0.11	0.10	0.08	0.07	0.06	0.05	0.03
SMD0603P020TF	0.27	0.25	0.23	0.20	0.17	0.14	0.12	0.10	0.07
SMD0603P020TF/16	0.27	0.25	0.23	0.20	0.17	0.14	0.12	0.10	0.07
SMD0603P025TF	0.32	0.29	0.27	0.25	0.21	0.18	0.16	0.14	0.10
SMD0603P025TF/16	0.32	0.29	0.27	0.25	0.21	0.18	0.16	0.14	0.10
SMD0603P035TF	0.47	0.41	0.38	0.35	0.29	0.26	0.24	0.20	0.14
SMD0603P050TF	0.68	0.59	0.54	0.50	0.41	0.37	0.34	0.29	0.20
SMD0603P050TF/12	0.68	0.59	0.54	0.50	0.41	0.37	0.34	0.29	0.20
SMD0603P075TF	1.00	0.90	0.79	0.75	0.63	0.57	0.53	0.41	0.34
SMD0603P100TF	1.30	1.12	1.08	1.00	0.80	0.72	0.58	0.53	0.42


Thermal Derating Curve







Average Time-Current Curve



Environmental Specifications

Conditions	Resistance change
+85°C, 1000 hrs.	±5% typical
+85°C, 85% R.H., 168 hours	±5% typical
+85°C to -40°C, 20 times	±33% typical
MIL-STD-202,Method 215	No change
MIL-STD-202,Method 201	No change
	+85°C, 1000 hrs. +85°C, 85% R.H., 168 hours +85°C to -40°C, 20 times MIL-STD-202,Method 215


Ambient operating conditions : - 40 °C to +85 °C

Maximum surface temperature of the device in the tripped state is 125 °C





Soldering Parameters



Profile Feature	Pb-Free Assembly
Average ramp-up rate $(T_{S max} \text{ to } T_P)$	3℃/second max.
Preheat -Temperature Min $(T_{S min})$ -Temperature Max $(T_{S max})$ -Time (min to max) $(T_{S min})$ to $T_{S max}$	150℃ 200℃ 60-180 seconds
Time maintained above: -Temperature (T_L) -Time (t_L)	217℃ 60-150 seconds
Peak Temperature (T P)	260℃
Time within 5° C of actual Peak Temperature (t $_{P}$)	20-40 seconds
Ramp-down Rate	6℃/second max.
Time 25 $^{\circ}\!$	8 minutes max.
Storage Condition	0°C~35°C, ≤70%RH


- · Recommended reflow methods: IR, vapor phase oven, hot air oven, N₂ environment for lead-free
- · Recommended maximum paste thickness is 0.25mm (0.010 inch)
- · Device can be cleaned using standard industry methods and solvents.
- Note 1: All temperature refer to topside ofthe package, measured on the package body surface.
- Note 2: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.






Tape and Reel Specifications

Governing Specifications	EIA 481-1			
W	8.0 ± 0.3			
P0	4.0 ± 0.10			
P1	4.0 ± 0.10			
P2	2.0 ± 0.05			
A0	1.05 ± 0.10			
В0	1.85 ± 0.10			
B1max.	4.35			
D0	1.55+ 0.05			
F	3.5 ± 0.05			
E1	1.75 ± 0.10			
E2min.	6.25			
Т	0.6			
T1max.	0.75			
K0	0.75 ± 0.1			
Leader min.	390			
Trailer min.	160			
Reel Dimensions	3			
A max.	178			
N min.	60			
W1	9 ± 0.5			
W2	12.6 ± 0.5			



EIA Reel Dimensions



Packaging

Part Number	Halogen Free	Packaging Option	Quantity	Quantity & Packaging Codes	
SMD0603PxxxTF	Yes	Tape and Reel	4000	YR	





RuiLongYuan Electronics Co., Ltd.

- Reproducing and modifying information of the document is prohibited without permission from Ruilongyuan International Inc.
- Ruilongyuan International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Ruilongyuan International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Ruilongyuan International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible
 in comprehending the suitable use in particular applications. Ruilongyuan International Inc. makes no representation or
 warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fullyindemnify Ruilongyuan International Inc. for any damages resulting from such improper use or sale.

Tel: +86-755-8290 8296 Fax: +86-755-8290 8002 E-mail: jack@ruilon.com

