



**Silicon N-Channel Power MOSFET**   
**CS6N60F A9H**

### General Description:

CS6N60F A9H, the silicon N-channel Enhanced VDMOSFETs, is obtained by the self-aligned planar Technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. The transistor can be used in various power switching circuit for system miniaturization and higher efficiency. The package form is TO-220F, which accords with the RoHS standard.

### Features:

- | **Fast Switching**
- | **Low ON Resistance( $R_{DS(on)} \leq 1.7\Omega$ )**
- | **Low Gate Charge (Typical Data: 19.5nC)**
- | **Low Reverse transfer capacitances(Typical: 7.5pF)**
- | **100% Single Pulse avalanche energy Test**


### Applications:

Power switch circuit of adaptor and charger.

**Absolute** ( $T_C = 25^\circ C$  unless otherwise specified):


Symbol	Parameter	Rating	Units
$V_{DSS}$	Drain-to-Source Voltage	600	V
$I_D$	Continuous Drain Current	6	A
	Continuous Drain Current $T_C = 100^\circ C$	3.6	A
$I_{DM}^{a1}$	Pulsed Drain Current	24	A
$V_{GS}$	Gate-to-Source Voltage	$\pm 30$	V
$E_{AS}^{a2}$	Single Pulse Avalanche Energy	270	mJ
$E_{AR}^{a1}$	Avalanche Energy ,Repetitive	31	mJ
$I_{AR}^{a1}$	Avalanche Current	2.5	A
$dv/dt^{a3}$	Peak Diode Recovery $dv/dt$	5	V/ns
$P_D$	Power Dissipation	34	W
	Derating Factor above $25^\circ C$	0.27	W/ $^\circ C$
$T_J, T_{stg}$	Operating Junction and Storage Temperature Range	150, -55 to 150	$^\circ C$
$T_L$	Maximum Temperature for Soldering	300	$^\circ C$

$V_{DSS}$	<b>600</b>	V
$I_D$	<b>6</b>	A
$P_D(T_C=25^\circ C)$	<b>34</b>	W
$R_{DS(ON)Typ}$	<b>1.4</b>	$\Omega$



**TO-220F**  
1. Gate 2. Drain 3. Source

Inner Equivalent Principium Chart



**Electrical Characteristics** (T<sub>c</sub>= 25°C unless otherwise specified):

OFF Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
V <sub>DSS</sub>	Drain to Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	600	--	--	V
Δ BV <sub>DSS</sub> / Δ T <sub>J</sub>	Bvdss Temperature Coefficient	I <sub>D</sub> =250uA, Reference 25°C	--	0.67	--	V/°C
I <sub>DSS</sub>	Drain to Source Leakage Current	V <sub>DS</sub> = 600V, V <sub>GS</sub> = 0V, T <sub>a</sub> = 25°C	--	--	1	μA
		V <sub>DS</sub> = 480V, V <sub>GS</sub> = 0V, T <sub>a</sub> = 125°C			100	
I <sub>GSS(F)</sub>	Gate to Source Forward Leakage	V <sub>GS</sub> = 30V	--	--	100	nA
I <sub>GSS(R)</sub>	Gate to Source Reverse Leakage	V <sub>GS</sub> = -30V	--	--	-100	nA

ON Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
R <sub>DS(ON)</sub>	Drain-to-Source On-Resistance	V <sub>GS</sub> =10V, I <sub>D</sub> =3A	--	1.4	1.7	Ω
V <sub>GS(TH)</sub>	Gate Threshold Voltage	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	2.0		4.0	V
Pulse width t <sub>p</sub> ≤300μs, δ ≤2%						

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
g <sub>fs</sub>	Forward Trans conductance	V <sub>DS</sub> =30V, I <sub>D</sub> =6A		10	--	S
C <sub>iss</sub>	Input Capacitance		--	720		pF
C <sub>oss</sub>	Output Capacitance	V <sub>GS</sub> = 0V V <sub>DS</sub> = 25V f = 1.0MHz	--	75		
C <sub>rss</sub>	Reverse Transfer Capacitance		--	7.5		

Resistive Switching Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
t <sub>d(ON)</sub>	Turn-on Delay Time	I <sub>D</sub> = 6A V <sub>DD</sub> = 300V R <sub>G</sub> = 9.1Ω	--	9.5	--	ns
t <sub>r</sub>	Rise Time		--	11	--	
t <sub>d(OFF)</sub>	Turn-Off Delay Time		--	34	--	
t <sub>f</sub>	Fall Time		--	16	--	
Q <sub>g</sub>	Total Gate Charge	I <sub>D</sub> = 6A V <sub>DD</sub> = 300V V <sub>GS</sub> = 10V	--	19.5		nC
Q <sub>gs</sub>	Gate to Source Charge		--	4		
Q <sub>gd</sub>	Gate to Drain ("Miller") Charge		--	7.5		

**Source-Drain Diode Characteristics**

Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
I <sub>S</sub>	Continuous Source Current (Body Diode)		--	--	6	A
I <sub>SM</sub>	Maximum Pulsed Current (Body Diode)		--	--	24	A
V <sub>SD</sub>	Diode Forward Voltage	I <sub>S</sub> =6.0A, V <sub>GS</sub> =0V	--	--	1.5	V
t <sub>rr</sub>	Reverse Recovery Time	I <sub>S</sub> =6.0A, T <sub>j</sub> = 25 °C	--	203	--	ns
Q <sub>rr</sub>	Reverse Recovery Charge	dI <sub>F</sub> /dt=100A/us, V <sub>GS</sub> =0V	--	943	--	nC
Pulse width t <sub>p</sub> ≤300μs, δ ≤2%						

Symbol	Parameter	Typ.	Units
R <sub>θJC</sub>	Junction-to-Case	3.68	°C/W
R <sub>θJA</sub>	Junction-to-Ambient	100	°C/W

<sup>a1</sup>: Repetitive rating; pulse width limited by maximum junction temperature

<sup>a2</sup>: L=10mH, I<sub>D</sub>=7.4A, Start T<sub>j</sub>=25 °C

<sup>a3</sup>: I<sub>SD</sub>=6A,di/dt ≤100A/us,V<sub>DD</sub>≤BV<sub>DS</sub>, Start T<sub>j</sub>=25 °C



## Characteristics Curve:




Figure 1 Maximum Forward Bias Safe Operating Area




Figure 2 Maximum Power Dissipation vs Case Temperature




Figure 3 Maximum Continuous Drain Current vs Case Temperature




Figure 4 Typical Output Characteristics




Figure 5 Maximum Effective Thermal Impedance , Junction to Case



## CS6N60F A9H




Figure 6 Maximum Peak Current Capability




Figure 7 Typical Transfer Characteristics




Figure 8 Typical Drain to Source ON Resistance vs Gate Voltage and Drain Current




Figure 9 Typical Drain to Source ON Resistance vs Drain Current










Figure 10 Typical Drian to Source on Resistance vs Junction Temperature



## CS6N60F A9H



## Test Circuit and Waveform




Figure 17. Gate Charge Test Circuit




Figure 18. Gate Charge Waveform




Figure 19. Resistive Switching Test Circuit




Figure 20. Resistive Switching Waveforms




Figure 21. Diode Reverse Recovery Test Circuit




Figure 22. Diode Reverse Recovery Waveform




Figure 23. Unclamped Inductive Switching Test Circuit





Figure 24. Unclamped Inductive Switching Waveforms



## Package Information



Items	Values(mm)	
	MIN	MAX
A	9.60	10.40
B	15.40	16.20
B1	8.90	9.50
C	4.30	4.90
C1	2.10	3.00
D	2.40	3.00
E	0.60	1.00
F	0.30	0.60
G	1.12	1.42
H	3.40	3.80
	2.00	2.40
L	12.00	14.00
	6.30	7.70
N	2.34	2.74
Q	3.15	3.55
Φ P	3.00	3.30

TO-220F Package

**The name and content of poisonous and harmful material in products**

Part's Name	Hazardous Substance					
	Pb	Hg	Cd	Cr(VI)	PBB	PBDE
Limit	≤0.1%	≤0.1%	≤0.01%	≤0.1%	≤0.1%	≤0.1%
Lead Frame	○	○	○	○	○	○
Molding Compound	○	○	○	○	○	○
Chip	○	○	○	○	○	○
Wire Bonding	○	○	○	○	○	○
Solder	×	○	○	○	○	○
Note	<p>○ : means the hazardous material is under the criterion of SJ/T11363-2006.</p> <p>× : means the hazardous material exceeds the criterion of SJ/T11363-2006.</p> <p>The plumbum element of solder exist in products presently, but within the allowed range of Eurogroup's RoHS.</p>					

**Warnings**

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. It is suggested to be used under 80 percent of the maximum ratings of the device.
2. When installing the heatsink, please pay attention to the torsional moment and the smoothness of the heatsink.
3. VDMOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
4. This publication is made by Huajing Microelectronics and subject to regular change without notice.

**WUXI CHINA RESOURCES HUAJING MICROELECTRONICS CO., LTD.**

Add: No.14 Liangxi RD. Wuxi, Jiangsu, China Mail:214061 <http://www.crhj.com.cn>  
Tel: +86 0510-85807228 Fax: +86- 0510-85800864

Marketing Part: Post: 214061 Tel: +86 0510-81805277/81805336  
Fax: +86 0510-85800360/85803016  
E-mail: [sales@hj.crmicro.com](mailto:sales@hj.crmicro.com)

Application and Service: Post: 214061 Tel / Fax: +86- 0510-81805243/81805110