

# 给您一颗快乐的"芯"! YSR433S505







## 1. SCOPE

This specification is applied to a SAW resonator designed for the stabilization of transmitters such as garage door openers and security transmitters.


## 2. ELECTRICAL SPECIFICATION

### 2.1 Maximum Rating

DC Voltage VDC	10V
AC Voltage Vpp	10V50Hz/60Hz
Operation temperature	-40°C to +85°C
Storage temperature	-45°C to +85°C
Max Input Power	10dBm

## 2.2 Electronic Characteristics

Item			Unites	Minimum	Typical	Maximum
Center Frequency			MHz	433.845	433.920	433.995
Insertion Loss			dB		1.6	2.2
Quality Factor		Unload Q		8300	12000	
		50Ω Loaded Q		850	1500	
Temperature	Turnover Temperature		$^{\circ}$	10	25	40
Stability	Freq.te	mp.Coefficient	ppm/℃		0.032	
Frequency Aging			ppm/yr		<±10	
DC. Insulation Resistance			ΜΩ	1.0		
RF	Motional Resistance R1		Ω		18	26
Equivalent	Motional Inductance L1		μН		79.82	
RLC Model	LC Model Motional Capacitance C1		fF		1.685	
Transducer Static Capacitance C0			pF		2.3	






## YSR433S505








## 3. TEST CIRCUIT



## 4. DIMENSION



## 5. ENVIRONMENTAL CHARACTERISTICS

## 5-1 High temperature exposure

Subject the device to +85°C for 16 hours. Then release the resonator into the room conditions for 24 hours prior to the measurement. It shall fulfill the specifications in 2.2.

#### 5-2 Low temperature exposure

Subject the device to -40°C for 16 hours. Then release the device into the room conditions for 24 hours prior to the measurement. It shall fulfill the specifications in 2.2.



## YSR433S505



#### 5-3 Temperature cycling

Subject the device to a low temperature of  $-40^{\circ}$ C for 30 minutes. Following by a high temperature of  $+85^{\circ}$ C for 30 Minutes. Then release the device into the room conditions for 24 hours prior to the measurement. It shall meet the specifications in 2.2.

#### 5-4 Resistance to solder heat

Dip the device terminals no closer than 1.5mm into the solder bath at  $260^{\circ}$ C  $\pm 10^{\circ}$ C for  $10\pm 1$  sec. Then release the device into the room conditions for 4 hours. The device shall meet the specifications in 2.2.

#### 5-5 Solderability

Subject the device terminals into the solder bath at  $245^{\circ}$ C  $\pm 5^{\circ}$ C for 5s, More than 95% area of the terminals must be covered with new solder. It shall meet the specifications in 2.2.

#### 5-6 Mechanical shock

Drop the device randomly onto the concrete floor from the height of 1m 3 times. the device shall fulfill the specifications in 2.2.

#### 5-7 Vibration

Subject the device to the vibration for 1 hour each in x, y and z axes with the amplitude of 1.5 mm at 10 to 55 Hz. The device shall fulfill the specifications in 2.2.

## 6. REMARK

#### 6.1 Static voltage

Static voltage between signal load & ground may cause deterioration &destruction of the component. Please avoid static voltage.

#### 6.2 Ultrasonic cleaning

Ultrasonic vibration may cause deterioration & destruction of the component. Please avoid ultrasonic cleaning

#### 6.3 Soldering

Only leads of component may be soldered. Please avoid soldering another part of component.



# 给您一颗快乐的"芯"! YSR433S505









## 7. TYPCIAL APPLICATION CIRCUITS

## Typical low-power Transmitter Application



## Typical Local Oscillator Application



4/4