

# 1N4148

## List

List..... 1

Package outline..... 2

Features..... 2

Mechanical data..... 2

Maximum ratings .....2

Rating and characteristic curves..... 3

Pinning information.....4

Marking..... 4

Taping & bulk specifications for AXIAL devices..... 4

Suggested thermal profiles for soldering processes..... 5

High reliability test capabilities.....6



# 1N4148

## 150mA Axial Led Type Switching Diode-100V


### Features

- Axial lead type devices for through hole design.
- Fast speed switching.
- Silicon epitaxial planar chip structure.
- Hermetically sealed glass.
- Lead-free parts meet RoHS requirements.

### Mechanical data

- Case : Glass, DO-35G
- Lead : Axial leads, solderable per MIL-STD-202, Method 208 guaranteed
- Polarity : Indicated by cathode band
- Mounting Position : Any
- Weight : Approximated 0.125 gram

### Package outline



### Maximum ratings and Electrical Characteristics (AT $T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	Symbol	MIN.	TYP.	MAX.	UNIT
Repetitive peak reverse voltage		$V_{RRM}$			100	V
Reverse voltage		$V_R$			75	V
Peak forward surge current	$t_p = 1 \mu\text{s}$	$I_{FSM}$			2.0	A
Repetitive peak forward voltage		$I_{FRM}$			500	mA
Forward current		$I_F$			300	mA
Average forward current		$I_{FAV}$			150	mA
Power dissipation		$P_V$			500	mW
Junction temperature		$T_J$	-55		+150	$^\circ\text{C}$
Storage temperature		$T_{STG}$	-65		+150	$^\circ\text{C}$
Forward voltage	$I_F = 10 \text{ mA}$	$V_F$		0.86	1.00	V
Reverse current	$V_R = 20 \text{ V}$	$I_R$			25	nA
	$V_R = 20 \text{ V}, T_J = 150^\circ\text{C}$	$I_R$			50	$\mu\text{A}$
	$V_R = 75 \text{ V}$	$I_R$			5.0	$\mu\text{A}$
Breakdown current	$I_R = 100 \mu\text{A}, t_p/T = 0.01, t_p = 0.3 \text{ ms}$	$V_{(BR)}$	100			V
Diode capacitance	$V_R = 0 \text{ V}, f = 1 \text{ MHz}, V_{HF} = 50 \text{ mV}$	$C_D$			4.0	pF
Rectification efficiency	$V_{HF} = 2 \text{ V}, f = 100 \text{ MHz}$	$\eta_R$	45			%
Reverse recovery time	$I_F = I_R = 10 \text{ mA}, I_{RR} = 1 \text{ mA}$	$t_{rr}$			8	ns
	$I_F = 10 \text{ mA}, V_R = 6 \text{ V}, I_{RR} = 0.1 \times I_R, R_L = 100 \Omega$	$t_{rr}$			4	ns

## Rating and characteristic curves (1N4148)

FIG.1-TYPICAL FORWARD CHARACTERISTICS




FIG.3 - TYPICAL REVERSE CHARACTERISTICS




FIG.2 - TYPICAL DIODE CAPACITANCE







FIG.4 - REVERSE CURRENT VS. JUNCTION TEMPERATURE



# 1N4148


## Pinning information

Pin	Simplified outline	Symbol
Pin1 cathode Pin2 anode		

## Marking

Type number	Marking code
1N4148	1N4148

## Taping & bulk specifications for AXIAL devices



### REEL PACKING

DEVICE CASE TYPE	Q'TY 1 (PCS / REEL)	COMPONENT SPACING "A" in FIG. A	CARTON SIZE (m/m)	Q'TY 2 (PCS / CARTON)	APPROX. CROSS WEIGHT(kg)
DO-35G/52mm	10,000	5 mm	360 * 360 * 395	50,000	11.4

### AMMO PACKING

DEVICE CASE TYPE	Q'TY 1 (PCS / BOX)	INNER BOX SIZE (m/m)	CARTON SIZE (m/m)	Q'TY 2 (PCS / CARTON)	APPROX. CROSS WEIGHT(kg)
DO-35G/26mm	5,000	250 * 78 * 48	420 * 270 * 330	150,000	16.7
DO-35G/52mm	5,000	250 * 78 * 78	420 * 270 * 330	100,000	15.0


# 1N4148

BULK PACKING

DEVICE CASE TYPE	Q'TY 1 (PCS / BOX)	INNER BOX SIZE (m/m)	CARTON SIZE (m/m)	Q'TY 2 (PCS / CARTON)	APPROX. CROSS WEIGHT(kg)
DO-35G	2,000	96 * 80 * 42	410 * 335 * 265	120,000	17.4

**Suggested thermal profiles for soldering processes**

1. Lead free temperature profile wave-soldering



**1N4148****High reliability test capabilities**

Item Test	Conditions	Reference
1. Solder Resistance	at 260±5°C for 10±2sec. immerse body into solder 1/16"±1/32"	MIL-STD-750D METHOD-2031
2. Solderability	at 245±5°C for 5 sec.	MIL-STD-202F METHOD-208
3. Pull Test	0.25kg in axial lead direction for 10 sec.	MIL-STD-750D METHOD-2036
4. Bend Lead	0.25kg weight applied to each lead bending arc 90°±5° for 3 times.	MIL-STD-750D METHOD-2036
5. High Temperature Reverse Bias	V <sub>R</sub> =80% rate at T <sub>J</sub> =150°C for 168 hrs.	MIL-STD-750D METHOD-1038
6. Forward Operation Life	Rated average rectifier current at T <sub>A</sub> =25°C for 500hrs.	MIL-STD-750D METHOD-1027
7. Intermittent Operation Life	T <sub>A</sub> = 25°C, I <sub>F</sub> = I <sub>O</sub> On state: power on for 5 min. off state: power off for 5 min, on and off for 500 cycles.	MIL-STD-750D METHOD-1036
8. Pressure Cooker	15P <sub>sig</sub> at T <sub>A</sub> =121°C for 4 hrs.	JESD22-A102
9. Temperature Cycling	-55°C to +125°C dwelled for 30 min. and transferred for 5min. total 10 cycles.	MIL-STD-750D METHOD-1051
10. Thermal Shock	0°C for 5 min. rise to 100°C for 5 min. total 10 cycles.	MIL-STD-750D METHOD-1056
11. Forward Surge	Peak forward surge curren t <sub>p</sub> = 1 us	MIL-STD-750D METHOD-4066-2
12. Humidity	at T <sub>A</sub> =85°C, RH=85% for 1000hrs.	MIL-STD-750D METHOD-1021
13. High Temperature Storage Life	at 175°C for 1000 hrs.	MIL-STD-750D METHOD-1031