

Product Search Data Sheet

Note: This datasheet may be out of date

Please download the latest datasheet of DLW21SZ491XQ2#from the official website of Murata Manufacturing Co., Ltd.

https://www.murata.com/en-us/products/productdetail?partno=DLW21SZ491XQ2%23

DLW21SZ491XQ2#


"#" indicates a package specification code.

In Production RoHS REACH AEC-Q200

< List of part numbers with package codes > DLW21SZ491XQ2B DLW21SZ491XQ2L



Appearance & Shape



(0.45

(in mm)



- 1. Small size and low profile (2.0x1.2x1.2mm).
- 2. 3 types of common mode impedance 180Ω,260Ω,
 490Ω [at 100MHz] line up for various circuits.
 (DLW21SN_XQ2/DLW21SZ_XQ2 series)
- 3. The matching the characteristic impedance Enables noise suppression for differential signal line without distortion in high-speed signal transmission.
- 4. Small dimension enables higher density mounting.

Applications

Automotive Usage	Infotainment
---------------------	--------------

(0.45

Packaging Information

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	500
L	180mm Embossed Tape	2000

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date

Please download the latest datasheet of DLW21SZ491XQ2#from the official website of Murata Manufacturing

Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=DLW21SZ491XQ2%23

DLW21SZ491XQ2#

"#" indicates a package specification code.

Specifications

Shape	SMD	Operating Temperature Range	-40℃ to 105℃
Size Code (in mm)	2012	Mass(typ.)	0.011g
Size Code (in inch)	0805	Number of Circuit	1
Length	2.0mm	Operating Temperature Range(Self- temperature rise is included)	No
Length Tolerance	±0.2mm		
Width	1.2mm		
Width Tolerance	±0.2mm		
Thickness	1.2mm		
Thickness Tolerance	±0.2mm		
Common Mode Impedance (at 100MHz)	490Ω		
Common Mode Impedance (at 100MHz) Tolerance	±25%		
Rated Current	200mA		
Rated Voltage	20Vdc		
Withstanding Voltage	50Vdc		
DC Resistance(max.)	0.77Ω		
DC Resistance	0.77Ω max.		
Insulation Resistance(min.)	10ΜΩ		

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date


Please download the latest datasheet of DLW21SZ491XQ2#from the official website of Murata Manufacturing Co., Ltd.


https://www.murata.com/en-us/products/productdetail?partno=DLW21SZ491XQ2%23

DLW21SZ491XQ2#


"#" indicates a package specification code.








Impedance-Frequency Characteristics (Main Items)



Impedance-Frequency Characteristics

Differential Mode Transmission Characteristics (Typical Value)



Equivalent Circuit

3 of 3

Attention

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

