

RS1AF THRU RS1MF

PINNING

Surface Mount Fast Recovery Rectifiers Reverse Voltage - 50 to 1000 V Forward Current - 1 A

FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Juntion
- Easy to pick and place
- Fast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- pprox. Weight: 27mg 0.00086oz

Maximum Ratings and Electrical characteristics

PIN	DESCRIPTION						
1	Cathode						
2	Anode						
1	2						
TopView	1						
Marking	Code: RS1A-RS1M						

Simplified outline SMAF and symbol

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	RS1AF	RS1BF	RS1DF	RS1GF	RS1JF	RS1KF	RS1MF	Units
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	v
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	v
Maximum Average Forward Rectified Current at Ta = 65 °C	I _{F(AV)}	1						А	
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	IFSM	25						А	
Maximum Instantaneous Forward Voltage at 1 A	VF	1.3						v	
Maximum DC Reverse Current Ta = 25 °C at Rated DC Blocking Voltage Ta =125 °C	l _R	5 100						μA	
Maximum Reverse Recovery Time ¹⁾	trr	150 250 500				00	ns		
Typical Junction Capacitance 2)	Cj	15						pF	
Operating and Storage Temperature Range	Tj, Tstg	-55 ~ +150							°C

1) Measured with $I_F\!=\!0.5$ A, $I_R\!=\!1$ A, $I_{rr}\!=\!0.25$ A

2) Measured at 1MHz and applied reverse voltage of 4V D.C

SHIKE MAKE CONSCIOUS PRODUCT

CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE






RS1AF THRU RS1MF

1.2 Average Forward Current (A) 1.0 0.8 0.6 0.4 Single phase half-wave 60 Hz 0.2 resistive or inductive load 0.0 100 125 150 25 50 75 175 Ambient Temperature (°C) Fig.3 Typical Instaneous Forward Characteristics 10 Instaneous Forward Current (A) T_=25°C 1.0 0.1 pulse with 300µs 1% duty cycle 0.01 0.0 0.5 1.5 2.0 2.5 1.0 Instaneous Forward Voltage (V) Fig.5 Maximum Non-Repetitive Peak Forward Surage Current 30 Peak Forward Surage Current (A) 25 20 15 10 8.3 ms Single Half Sine Wave (JEDEC Method) 05 00 10 100 1 Number of Cycles

Fig.1 Forward Current Derating Curve

Fig.2 Typical Reverse Characteristics



SHIKE MAKE CONSCIOUS PRODUCT CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE






RS1AF THRU RS1MF

SMAF

PACKAGE OUTLINE

Plastic surface mounted package; 2 leads




Top View

Bottom View

UNIT		А	С	D	Е	e	g	HE	2
mm	max	1.1	0.20	3.7	2.7	1.6	1.2	4.9	7°
	min	0.9	0.12	3.3	2.4	1.3	0.8	4.4	
mil	max	43	7.9	146	106	63	47	193	
	min	35	4.7	130	94	51	31	173	

The recommended mounting pad size



SHIKE MAKE CONSCIOUS PRODUCT CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE

