

FM220-MH THRU FM2100-MH


Silicon epitaxial planer type

Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-O Utilizing Flame Retardant Epoxy Molding Compound.
- For surface mounted applications.
- Exceeds environmental standards of ML-S-19500 / 228
- Low leakage current

Mechanical data

Case : Moulded plastic, JEDEC SOD-123H
 Terminals : Solder plated, solderable per ML-STD-750, Method 2026
 Polarity : Indicated by cathode band
 Mounting Position : Any
 Weight : 0.0393 gram



MAXIMUM RATINGS (AT $T_A=25^{\circ}C$ unless otherwise noted)

| PARAMETER | CONDITIONS | Symbol | MIN. | TYP. | MAX. | UNIT |
|----------------------------|---|-----------|------|------|------|-----------------|
| Forward rectified current | See Fig.1 | I_O | | | 2.0 | A |
| Forward surge current | 8.3ms single half sine-wave superimposed on rate load (JEDEC methode) | I_{FSM} | | | 40 | A |
| Reverse current | $V_R = V_{RRM} T_A = 25^{\circ}C$ | I_R | | | 0.5 | mA |
| | $V_R = V_{RRM} T_A = 125^{\circ}C$ | | | | 10 | mA |
| Thermal resistance | Junction to ambient | R_{JA} | | 85 | | $^{\circ}C / w$ |
| Diode junction capacitance | $f=1MHz$ and applied 4vDC reverse voltage | C_J | | 160 | | pF |
| Storage temperature | | T_{STG} | -55 | | +150 | $^{\circ}C$ |

| SYMBOLS | MARKING CODE | V_{RRM}^{*1} (V) | V_{RMS}^{*2} (V) | V_R^{*3} (V) | V_F^{*4} (V) | Operating temperature ($^{\circ}C$) |
|-----------|--------------|-----------------------|-----------------------|-------------------|-------------------|--|
| FM220-MH | 22 | 20 | 14 | 20 | 0.50 | -55 to +125 |
| FM230-MH | 23 | 30 | 21 | 30 | | |
| FM240-MH | 24 | 40 | 28 | 40 | | |
| FM250-MH | 25 | 50 | 35 | 50 | 0.70 | -55 to +150 |
| FM260-MH | 26 | 60 | 42 | 60 | | |
| FM280-MH | 28 | 80 | 56 | 80 | 0.85 | |
| FM2100-MH | 20 | 100 | 70 | 100 | | |

*1 Repetitive peak reverse voltage
 *2 RMS voltage
 *3 Continuous reverse voltage
 *4 Maximum forward voltage

RATING AND CHARACTERISTIC CURVES (FM220-MH THRU FM2100-MH)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL FORWARD CHARACTERISTICS




FIG.3-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.4-TYPICAL JUNCTION CAPACITANCE




FIG.5 - TYPICAL REVERSE CHARACTERISTICS

