



SURFACE MOUNT FAST RECOVERY RECTIFIER


VOLTAGE 50 to 1000 Volt CURRENT 1 Ampere

FEATURES

- For surface mounted applications
- · Low profile package
- Built-in strain relief
- Easy pick and place
- Fast Recovery times for high efficiency
- Plastic package has Underwriters Laboratory Flammability Classification 94V-O
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

- Case: SMA(W) molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Color band denotes cathode end
- Standard packaging: 12mm tape (EIA-481)
- Weight: 0.002 ounces, 0.068 grams



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.

PARAMETER	SYMBOL	RS1AW	RS1BW	RS1DW	RS1GW	RS1JW	RS1KW	RS1MW	UNITS
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	800	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Rectified Current T _L =90 °C	I _{F(AV)}	1.0						А	
Peak Forward Surge Current :8.3ms single half sine-wave superimposed on rated load	I _{FSM}	30				А			
Maximum Forward Voltage at 1.0A	V _F	1.3					V		
Maximum DC Reverse Current at Rated DC $T_J=25^{\circ}C$ Blocking Voltage $T_J=125^{\circ}C$	C I _R	5.0 150					μА		
Maximum Reverse Recovery Time (Note 1)	t _{rr}	150 250		5	00	ns			
Maximum Junction capacitance (Note 2)	C	12					pF		
Typical Junction Resistance(Note 3)	$R_{_{\theta JA}}$ $R_{_{\theta JL}}$	100 32				°C / W			
Operating Junction and Storage Temperature Rating		-55 to +150						°C	

NOTES:1. Reverse Recovery Test Conditions: I_F =0.5A, I_R =1A, I_{rr} =0.25A

- 2. Measured at 1 MHz and applied $V_r = 4$ volts.
- 3. 8 mm^2 (0.013 mm thick) land areas.





RATING AND CHARACTERISTIC CURVES




Fig.1 FORWARD CURRENT DERATING CURVE




Fig.2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




Fig.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS





Fig.4 TYPICAL JUNCTION CAPACITANCE





MOUNTING PAD LAYOUT



ORDER INFORMATION

Packing information

T/R - 7.5K per 13" plastic Reel

T/R - 1.8K per 7" plastic Reel





Part No_packing code_Version

RS1AW_R1_00001 RS1AW_R2_00001

For example:



Packing Code XX			Version Code XXXXX				
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code	
Tape and Ammunition Box (T/B)	Α	N/A	0	HF	0	serial number	
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number	
Bulk Packing (B/P)	В	13"	2				
Tube Packing (T/P)	Т	26mm	X				
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y				
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U				
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D				





Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties
 of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation.
 Customers are responsible in comprehending the suitable use in particular applications.
 Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.