




MSB40D THRU MSB40M

GLASS PASSIVATED SURFACE MOUNT BRIDGE RECTIFIER RECTIFIERS

Voltage Range - 200 to 1000 Volts Current - 4.0 Ampere

UMSB



Top View

Bottom View

Side View

Dimensions in inches and (millimeters)

FEATURES

- ◆ Glass Passivated Chip Junction
- ◆ Reverse Voltage - 100 to 1000 V
- ◆ Forward Current - 4.0 A
- ◆ High Surge Current Capability
- ◆ Designed for Surface Mount Application

MECHANICAL DATA

- ◆ Case: UMSB
- ◆ Terminals: Solderable per MIL-STD-750 , Method 2026

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz,resistive or inductive load, for capacitive load derate current by 20%.

MDD Catalog Number	SYMBOLS	MSB40D	MSB40G	MSB40J	MSB40K	MSB40M	UNITS
Marking code		MB40D	MB40G	MB40J	MB40K	MB40M	
Maximum repetitive peak reverse voltage	V_{RRM}	200	400	600	800	1000	VOLTS
Maximum RMS voltage	V_{RMS}	140	280	420	560	700	VOLTS
Maximum DC blocking voltage	V_{DC}	200	400	600	800	1000	VOLTS
Maximum Average Forward Rectified Current	$I_{F(AV)}$	4.0					Amps
Peak Forward Surge Current @ 8.3ms single half sine-wave	I_{FSM}	95					Amps
Maximum Forward Voltage @ $T_J = 25^\circ C$ @ 4.0A	V_F	1.1					Volts
Maximum DC reverse current $T_A=25^\circ C$ at rated DC blocking voltage $T_A=125^\circ C$	I_R	5 100					uA uA
Typical junction Capacitance per element (Note 1)	C_J	40					pF
Operating temperature range	T_J	-55 to +150					°C
storage temperature range	T_{STG}	-55 to +150					°C

Note: 1. Measured at 1MHz and applied reverse voltage of 4 V D.C.

2. Mounted on glass epoxy PC board with $4 \times 1.5'' \times 1.5''$ (3.81×3.81 cm) copper pad.



RATINGS AND CHARACTERISTIC CURVES MSB40D THRU MSB40M

Fig.1 Average Rectified Output Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Instantaneous Forward Characteristics




Fig.4 Typical Junction Capacitance





Fig.5 Maximum Non-Repetitive Peak Forward Surge Current



The curve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!

