

Wire Wound SMD Power Inductor



◆ Features

- 1、Magnetic-resin shielded construction reduces buzz noise to ultra-low levels;
- 2、Metallization on ferrite core results in excellent shock resistance and damage-free durability;
- 3、Closed magnetic circuit design reduces leakage flux and Electro Magnetic Interference (EMI);
- 4、30% higher current rating than conventional inductors of equal size;
- 5、Take up less PCB real estate and save more power.



◆ Applications

- 1、LED Lighting;
- 2、Mobile devices with multifunction such as adding color TV and camera;
- 3、Flat-screen TVs, blue-ray disc recorders, set top boxes;
- 4、Notebooks, desktop computers, servers, graphic cards;
- 5、Portable gaming devices, personal navigation systems, personal multimedia devices;
- 6、Automotive systems
- 7、Telecomm base stations


◆ Lead Free Part Numbering

SLW 5020 S 100 M S T
(1) (2) (3) (4) (5) (6) (7)

- (1) Series Type
- (2) Dimension: L X H
- (3) Material Code
- (4) Inductance: 2R2=2.2 μ H ;
100=10 μ H; 101=100 μ H
- (5) Inductance Tolerance: M= \pm 20%, N= \pm 30%
- (6) Company Code
- (7) Packaging : Tape Carrier Package

◆ Dimensions

Recommended Land Pattern




Unit:mm

| Series | A | B | C | D | E | F | a Typ. | b Typ. | c Typ. |
|----------|---------------|---------------|---------|---------------|----------------|----------------|--------|--------|--------|
| SLW5020S | 5.0 \pm 0.2 | 5.0 \pm 0.2 | 2.0Max. | 4.0 \pm 0.2 | 1.25 \pm 0.2 | 2.50 \pm 0.2 | 2.1 | 1.5 | 4.4 |

◆ Electrical Characteristics

- 1) Operating temperature range (Including self-heating): $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
- 2) Storage temperature range (packaging conditions): $-10^{\circ}\text{C} \sim +40^{\circ}\text{C}$ and RH 70% (Max.)


◆ Construction and material




| Code | Part Name | Material Name |
|------|--------------------|--|
| ① | Ferrite Core | Ni-Zn Ferrite |
| ② | Wire | Polyurethane system enameled copper wire |
| ③ | Magnetic Glue | Epoxy resin and magnetic powder |
| ④ | Plating Electrodes | Ag |
| | | Ni |
| | | Sn |
| ⑤ | Outer Electrodes | Top surface solder coating Sn、Ag、Cu |

◆ REFLOW-PROFILE

Limit Profile



Standard Profile (for EOC Solder paste S70G-HF)



◆ Specification

| Part Number | Inductance @100KHz, 1V (μ H) | DC Resistance $\pm 30\%$ (Ω) | Min.Self-resonant Frequency (MHz) | Saturation Current(A) | Heat Rating Current (A) |
|-------------------------|---|--|--------------------------------------|--------------------------|----------------------------|
| | | DCR | S.R.F | Isat | Irms |
| CMLW5020S Series | | | | | |
| SLW5020SR47NST | 0.47 \pm 30% | 0.013 | 160 | 6.15 | 4.60 |
| SLW5020SR68NST | 0.68 \pm 30% | 0.017 | 120 | 5.50 | 4.00 |
| SLW5020S1R0NST | 1.0 \pm 30% | 0.020 | 97 | 4.33 | 3.70 |
| SLW5020S1R5NST | 1.5 \pm 30% | 0.026 | 80 | 3.85 | 3.20 |
| SLW5020S2R2MST | 2.2 \pm 20% | 0.035 | 61 | 3.85 | 2.90 |
| SLW5020S3R3MST | 3.3 \pm 20% | 0.044 | 46 | 3.25 | 2.40 |
| SLW5020S4R7MST | 4.7 \pm 20% | 0.057 | 33 | 2.50 | 2.25 |
| SLW5020S5R6MST | 5.6 \pm 20% | 0.064 | 33 | 2.30 | 2.05 |
| SLW5020S6R8MST | 6.8 \pm 20% | 0.087 | 30 | 1.80 | 1.70 |
| SLW5020S100MST | 10 \pm 20% | 0.110 | 24 | 1.79 | 1.50 |
| SLW5020S150MST | 15 \pm 20% | 0.165 | 20 | 1.44 | 1.25 |
| SLW5020S220MST | 22 \pm 20% | 0.235 | 16 | 1.18 | 1.05 |
| SLW5020S330MST | 33 \pm 20% | 0.370 | 13 | 0.97 | 0.83 |
| SLW5020S470MST | 47 \pm 20% | 0.525 | 11 | 0.81 | 0.70 |
| SLW5020S680MST | 68 \pm 20% | 0.885 | 8.8 | 0.70 | 0.53 |
| SLW5020S101MST | 100 \pm 20% | 1.060 | 7.6 | 0.57 | 0.49 |

◆ Note


- 1: All test data is referenced to 20°C ambient;
- 2: Rated current: Isat or Irms, whichever is smaller;
- 3: Isat: DC current at which the inductance drops approximate 30% from its value without current;
- 4: Irms: DC current that causes the temperature rise ($\Delta T = 40^\circ\text{C}$) from 20°C ambient.

◆ Standard Packing Quantity: 2500 pcs/reel

◆ TYPICAL ELECTRICAL CHARACTERISTICS

SLW5020S Series

Temperature vs. DC Current Characteristics



Inductance vs. DC Current Characteristics

