

### Features

- Transient protection for high-speed data lines  
IEC 61000-4-2 (ESD)  $\pm 30\text{kV}$  (Air)  
 $\pm 30\text{kV}$  (Contact)  
IEC 61000-4-4 (EFT) 40A (5/50 ns)  
Cable Discharge Event (CDE)
- Package optimized for high-speed lines
- Ultra-small package (1.0mm $\times$ 0.6mm $\times$ 0.55mm)
- Protects one data, control or power line
- Low capacitance: 12pF (Typical)
- Low leakage current: 0.01 $\mu\text{A}$  @  $V_{RWM}$  (Typical)
- Low clamping voltage
- Each I/O pin can withstand over 1000 ESD strikes for  $\pm 8\text{kV}$  contact discharge

### Description

CS0801M is a low-capacitance Transient Voltage Suppressor (TVS) designed to provide electrostatic discharge (ESD) protection for data, control or power lines. With typical capacitance of 12pF only, CS0801M is designed to protect parasitic-sensitive systems against over-voltage and over-current transient events. It complies with IEC 61000-4-2 (ESD), Level 4 ( $\pm 15\text{kV}$  air,  $\pm 8\text{kV}$  contact discharge), IEC 61000-4-4 (electrical fast transient - EFT) (40A, 5/50 ns), very fast charged device model (CDM) ESD and cable discharge event (CDE), etc.

CS0801M uses ultra-small uDFN-2L package. Each CS0801M device can protect one data line. It offers system designers flexibility to protect single data line where space is a premium concern.

### Applications

- Portable Electronics
- Desktops, Servers and Notebooks
- Cellular Phones
- MP3 Ports
- Digital Camera Ports
- Subscriber Identity Module (SIM) card


### Mechanical Characteristics

- DFN1.0x0.6-2 package
- Flammability Rating: UL 94V-0
- Marking: Part number, date code
- Packaging: Tape and Reel

### Circuit Diagram



### Pin Configuration




uDFN-2L  
(Top View)

## Absolute Maximum Rating

Symbol	Parameter	Value	Units
$I_{PP}$	Peak Pulse Current (8/20 $\mu$ s)	4	A
$P_{PK}$	Peak Pulse Power (8/20 $\mu$ s)	50	Watts
$V_{ESD}$	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	$\pm 30$ $\pm 30$	kV
$T_{OPT}$	Operating Temperature	-55/+125	$^{\circ}$ C
$T_{STG}$	Storage Temperature	-55/+150	$^{\circ}$ C

## Electrical Characteristics (T = 25 $^{\circ}$ C)


Symbol	Parameter
$V_{RWM}$	Nominal Reverse Working Voltage
$I_R$	Reverse Leakage Current @ $V_{RWM}$
$V_{BR}$	Reverse Breakdown Voltage @ $I_T$
$I_T$	Test Current for Reverse Breakdown
$V_C$	Clamping Voltage @ $I_{PP}$
$I_{PP}$	Maximum Peak Pulse Current
$C_{ESD}$	Parasitic Capacitance
$V_R$	Reverse Voltage
f	Small Signal Frequency




Symbol	Test Condition	Minimum	Typical	Maximum	Units
$V_{RWM}$				5.0	V
$I_R$	$V_{RWM} = 5V, T = 25^{\circ}C$ Between I/O_1 and I/O_2		0.01	1.0	$\mu$ A
$V_{BR}$	$I_T = 1mA$ Between I/O_1 and I/O_2	5.5	6.0		V
$V_C$	$I_{PP} = 1A, t_p = 8/20\mu s$ Between I/O_1 and I/O_2			10.0	V
$V_C$	$I_{PP} = 4A, t_p = 8/20\mu s$ Between I/O_1 and I/O_2			12.5	V
$R_{DYN}$	Dynamic Resistance		0.4		$\Omega$
$C_{ESD}$	$V_R = 0V, f = 1MHz$ Between I/O_1 and I/O_2		12		pF



## TLP Measurement of I/O\_1 to I/O\_2




## Voltage Sweeping of I/O\_1 to I/O\_2




## Capacitance vs. Voltage of I/O\_1 to I/O\_2 (f = 1MHz)


Capacitance vs. Reverse Voltage




Normalized Capacitance vs. Reverse Voltage



## ESD Clamping of I/O\_1 to I/O\_2 (+8kV Contact per IEC 61000-4-2)




## ESD Clamping of I/O\_1 to I/O\_2 (-8kV Contact per IEC 61000-4-2)



## Package Outline


- uDFN-2L package
- 2 leads, very small package
- MSL-1




Package Dimensions (Controlling dimensions are in millimeters)

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Minimum	Maximum	Minimum	Maximum
A	0.400	0.550	0.016	0.022
A1	0.000	0.050	0.000	0.002
A3	0.125 REF		0.005 REF	
D	0.950	1.050	0.037	0.041
E	0.550	0.650	0.022	0.026
b	0.200	0.300	0.008	0.012
e	0.650 BSC		0.026 BSC	
L	0.450	0.550	0.018	0.022

## Tape and Reel Specification



Symbol	W	A0	B0	K0	E	F	P	P0	P2	T
Dimensions (mm)	8.00±0.1	0.7±0.05	1.15±0.05	0.55±0.05	1.75±0.1	3.5±0.05	2.0±0.1	4.0±0.1	2.0±0.05	0.2±0.05



Symbol	Reel Size	M	N	W	W1	H	S	K	R
Dimensions (mm)	Φ178	178.0±1.0	60.0±1.0	11.5±0.5	9.0±0.5	13.0±0.5	2.0±0.1	11.0±0.2	1.0±0.05

## Marking Codes



### Note:

- (1) "F" is part number, fixed
- (2) "M" is date code, which is the assembly month in three years, changing as (1~9, 0, A~Z)

## Ordering Information

Part Number	Working Voltage	Quantity Per Reel	Reel Size
CS0801M	5V	10,000	7 Inch