




贴片保险丝(抗浪涌型)

SMD Fuse (High Inrush Current Withstand) 63V/32V



测试标准:

Testing Standard:
UL248-1 UL248-14

额定分断能力:

Interrupting Rating:
50 Amperes at 63V DC(1A~4A)
100 Amperes at 32V DC(5A)

工作温度:

Operating Temperature:
-55°C ~ +125°C

材料:

Materials:
Substrate:ceramic/glass cover
Termination:sliver over-plated with nickel and tin
Element:silver


焊接方法:

Soldering Method:
Wave soldering: 260°C, 10s max

包装:

Packaging:
Automaton taped 3000PCS per roll,
90000PCS per carton

Time-Current Characteristics
电流-时间曲线图



电气特性: Electrical Characteristics

额定电流 Ampere Rating	额定电流的% % of Ampere Rating	熔断时间 Opening Time
1A~5A	100%	4 hours Min(大于4小时)
1A~5A	250%	5 s Max(小于5秒)
1A~5A	300%	0.1 s ~ 3 s
1A~5A	1000%	0.2 ms ~ 20 ms

目录编号: Catalog No.C:63V D:32V

目录编号 Catalog No.	额定电流 Ampere Rating	额定电压 Voltage Rating	标示 Marking	熔化热能 ² T Melting Integral (A ² .S)	认证 Approvals
					● 表示已获认证 ● 表示认证中
12H1100C	1A	63V	H	0.19	●
12H1150C	1.5A	63V	K	0.47	●
12H1200C	2A	63V	N	1.63	●
12H1250C	2.5A	63V	O	1.81	●
12H1300C	3A	63V	P	2.79	●
12H1350C	3.5A	63V	R	2.95	●
12H1400C	4A	63V	S	3.8	●
12H1500D	5A	32V	T	6.3	●