





SRT RoHS Compliant



微型保险丝(延时型)

Micro Fuse (Time-Lag) 250V



测试标准:
Testing Standard:
 IEC60127-1 IEC20167-3 GB9364.1 GB9364.3


额定分断能力:
Interrupting Rating:
 35A or 10In Whichever is greater

工作温度:
Operating Temperature:
 -55°C ~ +125°C

材料:
Materials:
 Case:thermoplastic nylon
 Base:thermoplastic nylon
 Lead wire:tinned copper wire

焊接方法:
Soldering Method:
 Wave soldering: 260°C, 10s max
 Manual soldering: 370°C, 5s max

Time-Current Characteristics
 电流-时间曲线图



电气特性: Electrical Characteristics

额定电流的% % of Ampere Rating	熔断时间 Opening Time
210%	2 min Max(小于2分钟)
275%	400 ms~10 s
400%	150 ms~3 s
1000%	20 ms~150 ms

目录编号: Catalog No.A:250V.

目录编号 Catalog No.	额定电流 Ampere Rating	额定电压 Voltage Rating	最大电压降(mv) Max Voltage Drop	熔化热能 ² T Melting Integral (A ² .S)	认证 Approvals						
					UL US	VDE	CCC	CQC	PS E JET	K	
SRT0250A	250mA	250V	240	0.2	●	●	●	●	●	●	●
SRT0315A	315mA	250V	220	0.3	●	●	●	●	●	●	●
SRT0400A	400mA	250V	200	0.5	●	●	●	●	●	●	●
SRT0500A	500mA	250V	190	0.9	●	●	●	●	●	●	●
SRT0630A	630mA	250V	180	1.2	●	●	●	●	●	●	●
SRT0800A	800mA	250V	160	3.9	●	●	●	●	●	●	●
SRT1100A	1A	250V	140	5.8	●	●	●	●	●	●	●
SRT1125A	1.25A	250V	130	12.8	●	●	●	●	●	●	●
SRT1160A	1.6A	250V	120	14.7	●	●	●	●	●	●	●
SRT1200A	2A	250V	100	21.9	●	●	●	●	●	●	●
SRT1250A	2.5A	250V	100	42.6	●	●	●	●	●	●	●
SRT1315A	3.15A	250V	100	72	●	●	●	●	●	●	●
SRT1400A	4A	250V	100	83.2	●	●	●	●	●	●	●
SRT1500A	5A	250V	100	148	●	●	●	●	●	●	●
SRT1630A	6.3A	250V	100	195	●	●	●	●	●	●	●