



GOOD-ARK

SB370 thru SB3B0

Schottky Barrier Rectifiers

Reverse Voltage 70 to 100 Volts


Forward Current 3.0 Amperes

Features

- ◆ Metal-Semiconductor junction with guard ring
- ◆ Epitaxial construction
- ◆ Low forward voltage drop
- ◆ High current capability
- ◆ The plastic material carries UL recognition 94V-0
- ◆ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications



DO-201AD



Dimensions in inches and (millimeters)

Mechanical Data

- ◆ Case : JEDEC DO-201AD molded plastic
- ◆ Polarity : Color band denotes cathode
- ◆ Weight : 0.041 ounce, 1.15 grams
- ◆ Mounting position : Any

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

PARAMETER	SYMBOL	SB370	SB380	SB390	SB3B0	UNIT
Maximum repetitive peak reverse voltage	VRRM	70	80	90	100	V
Maximum RMS voltage	VRMS	49	56	63	70	V
Maximum DC blocking voltage	VDC	70	80	90	100	V
Maximum average forward rectified current at TL(see Fig.1)	IF(AV)			3		A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	IFSM			100		A
Maximum forward voltage at 3.0A DC, $T_j=25^\circ\text{C}$	VF			0.79		V
Maximum forward voltage at 3.0A DC, $T_j=100^\circ\text{C}$	VF			0.69		V
Maximum DC reverse current at rated DC blocking voltage	$T_j=25^\circ\text{C}$ $T_j=125^\circ\text{C}$	IR		0.10		mA
				5		
Typical thermal resistance junction to ambient(Note1)	$R_{\theta JA}$			40		$^\circ\text{C/W}$
Typical thermal resistance junction to lead(Note1)	$R_{\theta JL}$			18		$^\circ\text{C/W}$
Typical thermal resistance junction to case(Note1)	$R_{\theta JC}$			23		$^\circ\text{C/W}$
Typical junction capacitance.Measured at 1.0MHz and applied reverse voltage of 4.0V DC	C _j			90		pF
Operating junction temperature range	T _J			- 55 to + 150		$^\circ\text{C}$
Storage temperature range	T _{TSG}			- 55 to + 150		$^\circ\text{C}$

Note: 1. Thermal Resistance at .375"(9.5mm)Lead Length, PC Board Mounted.

RATINGS AND CHARACTERISTIC CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

