


www.vishay.com

Vishay Semiconductors

HEXFRED® Ultrafast Soft Recovery Diode, 15 A



TO-247AC modified



PRODUCT SUMMARY	
Package	TO-247AC modified (2 pins)
I _{F(AV)}	15 A
V_{R}	600 V
V _F at I _F	1.2 V
t _{rr} typ.	19 ns
T _J max.	150 °C
Diode variation	Single die

FEATURES

- Ultrafast and ultrasoft recovery
- Very low I_{RRM} and Q_{rr}
- Designed and qualified according to JEDEC®-JESD47







ROHS
COMPLIANT
HALOGEN
FREE
Available

BENEFITS

- Reduced RFI and EMI
- Reduced power loss in diode and switching transistor
- Higher frequency operation
- Reduced snubbing
- Reduced parts count

DESCRIPTION

VS-HFA15PB60... is a state of the art ultrafast recovery diode. Employing the latest in epitaxial construction and advanced processing techniques it features a superb combination of characteristics which result in performance which is unsurpassed by any rectifier previously available. With basic ratings of 600 V and 15 A continuous current, the VS-HFA15PB60... is especially well suited for use as the companion diode for IGBTs and MOSFETs. In addition to ultrafast recovery time, the HEXFRED® product line features extremely low values of peak recovery current (I_{RRM}) and does not exhibit any tendency to "snap-off" during the th portion of recovery. The HEXFRED features combine to offer designers a rectifier with lower noise and significantly lower switching losses in both the diode and the switching transistor. These HEXFRED advantages can help to significantly reduce snubbing, component count and heatsink sizes. The HEXFRED VS-HFA15PB60... is ideally suited for applications in power supplies and power conversion systems (such as inverters), motor drives, and many other similar applications where high speed, high efficiency is needed.

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS		
Cathode to anode voltage	V_R		600	V		
Maximum continuous forward current	I _F	T _C = 100 °C	15			
Single pulse forward current	I _{FSM}		150	Α		
Maximum repetitive forward current	I _{FRM}		60			
Maximum power dissipation	P _D	T _C = 25 °C	74	- w		
Maximum power dissipation		T _C = 100 °C	29			
Operating junction and storage temperature range	T _J , T _{Stg}		-55 to +150	°C		



VS-HFA15PB60PbF, VS-HFA15PB60-N3

Vishay Semiconductors

ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS	TEST CONDITIONS			MAX.	UNITS
Cathode to anode breakdown voltage	V _{BR}	I _R = 100 μA		600	-	-	
Maximum forward voltage	V _{FM}	I _F = 15 A	See fig. 1	-	1.3	1.7	V
		I _F = 30 A		-	1.5	2.0	
		I _F = 15 A, T _J = 125 °C		-	1.2	1.6	
Maximum reverse		V _R = V _R rated	Coofie 0	-	1.0	10	
leakage current	I _{RM}	$T_J = 125 ^{\circ}\text{C}, V_R = 0.8 \text{x} V_R \text{rated}$	See fig. 2	-	400	1000	μA
Junction capacitance	C _T	V _R = 200 V	See fig. 3	-	25	50	pF
Series inductance	L _S	Measured lead to lead 5 mm from p	ackage body	-	12	-	nH

DYNAMIC RECOVERY CHARACTERISTICS (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CON	MIN.	TYP.	MAX.	UNITS	
	t _{rr}	$I_F = 1.0 \text{ A}, dI_F/dt = 200 \text{ A}$	Vμs, V _R = 30 V	-	19	-	
Reverse recovery time See fig. 5, 10	t _{rr1}	T _J = 25 °C		-	42	60	ns
000 fig. 0, 10	t _{rr2}	T _J = 125 °C	$I_F = 15 \text{ A}$ $dI_F/dt = 200 \text{ A/}\mu\text{s}$ $V_R = 200 \text{ V}$	-	74	120	
Peak recovery current	I _{RRM1}	T _J = 25 °C		-	4.0	6.0	A nC
See fig. 6	I _{RRM2}	T _J = 125 °C		-	6.5	10	
Reverse recovery charge	Q _{rr1}	T _J = 25 °C		-	80	180	
See fig. 7	Q _{rr2}	T _J = 125 °C		-	220	600	IIC
Peak rate of fall of recovery current during t _b See fig. 8	dI _{(rec)M} /dt1	T _J = 25 °C		-	188	-	A/µs
	dI _{(rec)M} /dt2	T _J = 125 °C		-	160	-	Ανμδ

THERMAL - MECHANICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS	
Lead temperature	T _{lead}	0.063" from case (1.6 mm) for 10 s	-	-	300	°C	
Thermal resistance, junction to case	R _{thJC}		-	-	1.7		
Thermal resistance, junction to ambient	R _{thJA}	Typical socket mount		-	40	K/W	
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.25	-		
Weight			-	6.0	-	g	
vveignit			-	0.21	-	OZ.	
Mounting torque			6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)	
Marking device		Case style TO-247AC modified (JEDEC)	HFA15PB60				





www.vishay.com Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current




Fig. 2 - Typical Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics



VS-HFA15PB60PbF, VS-HFA15PB60-N3

Vishay Semiconductors

www.vishay.com




Fig. 5 - Typical Reverse Recovery Time vs. dI_F/dt




Fig. 6 - Typical Recovery Current vs. dl_F/dt




Fig. 7 - Typical Stored Charge vs. dl_F/dt




Fig. 8 - Typical dl_{(rec)M}/dt vs. dl_F/dt

Vishay Semiconductors





Fig. 9 - Reverse Recovery Parameter Test Circuit



- (1) dI_F/dt rate of change of current through zero crossing
- (2) I_{RRM} peak reverse recovery current
- (3) $\rm t_{rr}$ reverse recovery time measured from zero crossing point of negative going $\rm I_F$ to point where a line passing through 0.75 $\rm I_{RRM}$ and 0.50 $\rm I_{RRM}$ extrapolated to zero current.
- (4) \mathbf{Q}_{rr} area under curve defined by \mathbf{t}_{rr} and \mathbf{I}_{RRM}

$$Q_{rr} = \frac{t_{rr} \times I_{RRM}}{2}$$

(5) $dI_{(rec)M}/dt$ - peak rate of change of current during t_b portion of t_{rr}


Fig. 10 - Reverse Recovery Waveform and Definitions

VS-HFA15PB60PbF, VS-HFA15PB60-N3

Vishay Semiconductors

ORDERING INFORMATION TABLE

Device code



Vishay Semiconductors product

2 - HEXFRED® family

Electron irradiated

- Current rating (15 = 15 A)

PB = TO-247AC modified

6 - Voltage rating: (60 = 600 V)

7 - Environmental digit:

PbF = lead (Pb)-free and RoHS-compliant

-N3 = halogen-free, RoHS-compliant, and totally lead (Pb)-free

ORDERING INFORMATION (Example)							
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION				
VS-HFA15PB60PbF	25	500	Antistatic plastic tube				
VS-HFA15PB60-N3	25	500	Antistatic plastic tube				


LINKS TO RELATED DOCUMENTS					
Dimensions		www.vishay.com/doc?95541			
Part marking information	TO-247AC modified PbF	www.vishay.com/doc?95225			
Part marking information	TO-247AC modified -N3	www.vishay.com/doc?95442			



Vishay Semiconductors

TO-247AC modified - 50 mils L/F

DIMENSIONS in millimeters and inches



View B

SYMBOL	MILLIM	IETERS	INCHES		NOTES
STWIBOL	MIN.	MAX.	MIN.	MAX.	NOTES
Α	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.17	1.37	0.046	0.054	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.34	0.065	0.092	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
С	0.38	0.89	0.015	0.035	
c1	0.38	0.84	0.015	0.033	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

Section C - C, D - D, E - E

SYMBOL	MILLIM	IETERS	INC	HES	NOTES
OTIVIDOL	MIN.	MAX.	MIN.	MAX.	NOTES
D2	0.51	1.35	0.020	0.053	
E	15.29	15.87	0.602	0.625	3
E1	13.46	-	0.53	-	
е	5.46	BSC	0.215	BSC	
ØK	0.254		0.010		
L	14.20	16.10	0.559	0.634	
L1	3.71	4.29	0.146	0.169	
ØΡ	3.56	3.66	0.14	0.144	
Ø P1	-	7.39	-	0.291	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	0.178	0.216	
S	5.51 BSC		0.217 BSC		

Notes

- (1) Dimensioning and tolerance per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- (7) Outline conforms to JEDEC® outline TO-247 with exception of dimension c and Q



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.