

PK Series


- Endurance :1,000 hours at 135°C
- High Temperature Resistance
- RoHS Compliant and lead-free
- Recommended Applications: Large LED Lanterns power




◆ SPECIFICATIONS

| Items | Characteristics | | | | | |
|--|--|--------------------------------------|------|----|----|------------------|
| Category Temperature Range | -55 to +135°C | | | | | |
| Rated Working Voltage Range | 6.3 to 25Vdc | | | | | |
| Nominal Capacitance Range | 10~2200 μF | | | | | |
| Capacitance Tolerance | ±20%(M) (at 20°C, 120Hz) | | | | | |
| DC Leakage Current | I ≤ 0.2CV or 500μA whichever is greater(at 20°C after 2 minutes) | | | | | |
| | Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) | | | | | |
| Dissipation Factor (tan δ) | Rated Voltage (VDC) | 6.3 | 10 | 16 | 20 | 25 |
| | tanδ (Max.) | 0.08 | 0.12 | | | (at 20°C, 120Hz) |
| ESR(100K~300KHz,20°C) | Value in characteristics table | | | | | |
| Temperature Characteristic (Impedance Ratio at 100KHz) | Z (+150°C) / Z (+20°C) ≤ 1.25 | | | | | |
| | Z (-55°C) / Z (+20°C) ≤ 1.25 | | | | | |
| Endurance | After applying rated voltage with rated ripple current for 1000 hours at 150°C, the capacitors shall meet the following requirements. | | | | | |
| | Appearance | No significant damage | | | | |
| | Capacitance Change | ≤±20% of the initial value | | | | |
| | D.F. (tanδ) | ≤150% of the initial specified value | | | | |
| | ESR | ≤150% of the initial specified value | | | | |
| | Leakage Current | ≤The initial specified value | | | | |
| Humidity Test | After subjecting 90 to 95% RH for 1000 hours at 60°C .no voltage, The capacitors shall meet the requirement as Endurance. | | | | | |
| Surge Test | After subjecting to 1,000 cycles each consisting of charge with the surge voltage specified at normal temperature for 30 seconds through a protective resistor and discharge for 5 minutes 30 seconds, the capacitors shall meet the following requirements. | | | | | |
| | Appearance | No significant damage | | | | |
| | Capacitance Change | ≤±20% of the initial value | | | | |
| | D.F. (tanδ) | ≤150% of the initial specified value | | | | |
| | ESR | ≤150% of the initial specified value | | | | |
| | Leakage Current | ≤The initial specified value | | | | |

◆ DIMENSIONS [mm]



◆ MARKING



| ØD | 5 | 6.3 | 8 | 10 |
|----|-------------|-----|-----|-----|
| Ød | 0.5 | 0.5 | 0.6 | 0.6 |
| F | 2.0 | 2.5 | 3.5 | 5.0 |
| ØD | ØD+0.5 max. | | | |
| L | L+1.0 max. | | | |

◆ PART NUMBER SYSTEM

