Note: This datasheet may be out of date.

Please download the latest datasheet of PTFM04BD471Q2N34BS from the official website of Murata Manufacturing Co., Ltd.

https://www.murata.com/en-us/products/productdetail?partno=PTFM04BD471Q2N34BS

## PTFM04BD471Q2N34BS












### Appearance & Shape







### **Features**

- 1. PTFM\_S Series is fixed easily because of a screw clamp type.
- 2. Compact and light design as well as excellent thermal response.
- 3. Contactless operation provides a prolonged service life, yet permits noiseless operation.
- 4. The operating point of "POSISTOR" is set on the steepest point along the resistance-temperature characteristic curve, thus performing the overheat protective operation securely.
- 5. PTFM\_S Series is certified by UL/cUL/VDE. It is suitable for a powersupply, etc, required the safety standard.



Limited Usage

Consumer Grade



## Packaging Information

Packaging	Specifications	Minimum Order Quantity
BS	Bulk(Bag)	200

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/03/09



Note: This datasheet may be out of date.  $\underline{ \text{Please download the latest datasheet of PTFM04BD471Q2N34BS from the official website of Murata} \\$ 

Manufacturing Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=PTFM04BD471Q2N34BS

## PTFM04BD471Q2N34BS



Max. Voltage	16V
Sensing Temperature	100°C
Measure Condition of Sensing Temperature	TS℃
Resistance (25°C)	100Ω
Resistance Value Tolerance (at 25°C)	max.
Resistance	330Ω
Measure Condition of Resistance	max.(TS-10°C)
Resistance Value(2)	470Ω
Measure Condition of Resistance(2)	min.(TS°C)
Operating Temperature Range	-10°C to 110°C
Shape	Lead
Mass	0.62g

2 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




URL: https://www.murata.com/


Last updated :2018/03/09

# PTFM04BD471Q2N34BS









Resistance-Temperature Characteristics Range

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/