


压线端子

详情说明



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8	6
AMP.	9	12	17	18	30	35	50	70	95

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE	DIMENSION inch(mm)								Q'TY BOX
	BRAZED SEAM	BUTTED SEAM		d2	W	F	L	E	D	d1	T	
12-10 A.W.G. 4-6 mm ²	<input type="checkbox"/> SNBS5-4	<input type="checkbox"/> SNS5-4	#8	0.169 4.3	0.327 8.3	0.276 7	0.72 18.3	0.236 6	0.220 5.600	0.134 3.4	0.039 1	1000
12-10 A.W.G. 4-6 mm ²	<input type="checkbox"/> SNBS5-6	<input type="checkbox"/> SNS5-6	1/4	0.252 6.4	0.354 9	0.276 7	0.72 18.3	0.236 6	0.220 5.600	0.134 3.4	0.039 1	1000