CHIP COIL (CHIP INDUCTORS) LQH3NPN□□□□GRL REFERENCE SPECIFICATION

1. Scope

This reference specification applies to LQH3NPN GR series, Chip coil (Chip Inductors).

2. Part Numbering

Ρ LQ Н Ν 220 M G R (ex) Product ID Structure Dimension Applications Category Inductance Tolerance Dimension Other Packaging (L×W) L:Ф180Taping and (T) Characteristics

3. Rating

Operating Temperature Range

(Ambient temperature; Self-temperature rise is not included)

(Product temperature; Self- temperature rise is included)

(except LQH3NPN680/101/151/181/221/251MGR) -40 to + 125°C

(Ambient temperature; Self-temperature rise is not included)

(except LQH3NPN680/101/151/181/221/251MGR) -40 to + 85°C

(only LQH3NPN680/101/151/181/221/251MGR)

-40 to + 105°C

(Product temperature; Self- temperature rise is included)

-40 to + 105°C (only LQH3NPN680/101/151/181/221/251MGR)

· Storage Temperature Range. -40 to +105°C (except LQH3NPN680/101/151/181/221/251MGR)

-40 to +85°C (only LQH3NPN680/101/151/181/221/251MGR)

		Indu	uctance			F	Rated Current(r	mA)
Customer	Murata Part Number			DC Resistance (Ω)	Self Resonant Frequency (MHz min)	*1	-	sed on ature rise
Part Number		(µH)	Tolerance (%)			Based on inductance change	*3 Ambient temperature (85°C)	*4 Ambient temperature (105°C)
	LQH3NPNR47NGRL	0.47	N:±30	0.047±20%	180	2820	2540	1520
	LQH3NPN1R0MGRL	1.0		0.062±20%	100	1700	2080	1240
	LQH3NPN1R5MGRL	1.5		0.074±20%	80	1400	2040	1220
	LQH3NPN2R2MGRL	2.2		0.087±20%	50	1180	1730	1030
	LQH3NPN3R3MGRL	3.3		0.12±20%	30	1050	1580	940
	LQH3NPN4R7MGRL	4.7		0.14±20%	27	850	1520	910
	LQH3NPN6R8MGRL	6.8		0.23±20%	25	720	1140	680
	LQH3NPN100MGRL	10		0.28±20%	20	570	1120	670
	LQH3NPN150MGRL	15		0.39±20%	15	480	900	540
	LQH3NPN220MGRL	22	M:±20	0.53±20%	10	390	750	450
	LQH3NPN330MGRL	33		0.86±20%	8	320	600	360
	LQH3NPN470MGRL	47		1.4±20%	5	260	460	270
	LQH3NPN680MGRL	68		2.1±20%	6	220	280	-
	LQH3NPN101MGRL	100		3.2±20%	5	190	220	-
	LQH3NPN151MGRL	150		4.9±20%	3	160	180	-
	LQH3NPN181MGRL	180		6.4±20%	2	130	160	-
	LQH3NPN221MGRL	220		7.5±20%	2	120	150	-
	LQH3NPN251MGRL	250		8.0±20%	2	110	140	-

^{*1:} When applied Rated current to the Products, Inductance will be within ±30% of initial inductance value range.

Keep the temperature(ambient temperature plus self-generation of heat) under 105°C. (only LQH3NPN680/101/151/181/221/251MGR)

When applied rated current to the Products, temperature rise caused by self-generated heat shall be limited to 20°C max. (only LQH3NPN680/101/151/181/221/251MGR)

*4: When applied Rated current to the Products ,temperature rise caused by self-generated heat shall be limited to 20°Cmax.

^{*2:} Keep the temperature (ambient temperature plus self-generation of heat) under 125°C. (except LQH3NPN680/101/151/181/221/251MGR)

^{*3:} When applied Rated current to the Products ,temperature rise caused by self-generated heat shall be limited to 40°C max. (except LQH3NPN680/101/151/181/221/251MGR)

Reference Only


4. Testing Conditions

Unless otherwise specified>

Temperature : Ordinary Temperature (15 to 35°C) Humidity : Ordinary Humidity (25 to 85 %(RH)) <In case of doubt>

Temperature : $20 \pm 2^{\circ}$ C Humidity : 60 to 70 %(RH) Atmospheric Pressure : 86 to 106 kPa

5. Appearance and Dimensions



6. Product Marking

Inductance

 $10\mu H \rightarrow 100$

7. Electrical Performance

No.	Item	Specification	Test Method
7.1	Inductance	Inductance shall meet item 3.	Measuring Equipment: KEYSIGHT 4192A or equivalent Measuring Frequency: 1MHz
7.2	DC Resistance	DC Resistance shall meet item 3.	Measuring Equipment: Digital multi meter
7.3	Self Resonant Frequency(S.R.F)	S.R.F shall meet item 3.	Measuring Equipment: KEYSIGHT E4991A or equivalent



8. Mechanical Performance


No.	Item	Specification	Test Method
8.1	Shear Test	Chip coil shall not be damaged.	Substrate: Glass-epoxy substrate Force: 10N Hold Duration: 5±1s Chip coil Substrate
8.2	Bending Test		Substrate: Glass-epoxy substrate (100×40×1.0mm) Speed of Applying Force: 0.5mm / s Deflection: 2mm Hold Duration: 5seconds. Pressure jig Pressure jig
8.3	Vibration	Chip coil shall not be damaged.	Oscillation Frequency: 10 to 2000 to 10Hz for 20 minutes Total amplitude: 1.5 mm or Acceleration amplitude 98m/s² whichever is smaller. Testing Time: A period of 2 hours in each of 3 mutually perpendicular directions.(Total 6 hours)
8.4	Solderability	The wetting area of the electrode shall be at least 90% covered with new solder coating.	Flux:Ethanol solution of rosin,25(wt)% (Immersed for 5s to 10s) Solder: Sn-3.0Ag-0.5Cu Pre-Heating:150±10°C / 60 to 90seconds Solder Temperature:240±5°C Immersion Time:3±1 s
8.5	Resistance to Soldering Heat	Appearance: No damage Inductance Change: within ±20%	Flux: Ethanol solution of rosin,25(wt)% (Immersed for 5s to 10s) Solder: Sn-3.0Ag-0.5Cu Pre-Heating: 150±10°C / 60 to 90seconds Solder Temperature: 270±5°C Immersion Time: 10±1 s Then measured after exposure in the room condition for 24±2 hours.

9. Environmental Performance (It shall be soldered on the substrate.)

No.	Item	Specification	Test Method
9.1	Heat Resistance	Appearance:No damage Inductance Change : within ±10%	Temperature: Maximum Operating temperature (Self-temperature rise is not included) ±2°C Time: 1000h (+48h , -0h) Then measured after exposure in the room condition for 24±2 hours.
9.2	Cold Resistance		Temperature: -40±2°C Time: 1000h (+48h , -0h) Then measured after exposure in the room condition for 24±2 hours.

No.	Item	Specification	Test Method
9.3	Humidity	Appearance:No damage Inductance Change : within ±10%	Temperature: 85±2°C Humidity: 80~85%(RH) Time: 1000h (+48h , -0h) Then measured after exposure in the room condition for 24±2 hours.
9.4	Temperature Cycle		1 cycle: 1 step: - Minimun Operating temperature (Self-temperature rise is not included)±2°C / 30±3 min 2 step: Ordinary temp. / 10 to 15 min 3 step: Maximum Operating temperature (Self-temperature rise is not included)±2°C / 30±3 min 4 step: Ordinary temp. / 10 to 15 min Total of 100 cycles Then measured after exposure in the room condition for 24±2 hours.

10. Specification of Packaging



Dimension of the Cavity is measured at the bottom side.

10.2 Specification of Taping

- (1) Packing quantity (standard quantity)
 - 3,000 pcs / reel
- (2) Packing Method

Products shall be packed in the each embossed cavity of plastic tape and sealed by cover tape.

- (3) Sprocket hole
 - The sprocket holes are to the right as the tape is pulled toward the user.
- (4) Spliced point

Plastic tape and Cover tape has no spliced point.

(5) Missing components number


Missing components number within 0.1 % of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.

10.3 Pull Strength

Embossed carrier tape	10N min.
Cover tape	5N min.


10.4 Peeling off force of cover tape

	•
Speed of Peeling off	300mm/min
Peeling off force	0.2 to 0.7N (minimum value is typical)



10.5 Dimensions of Leader-tape, Trailer and Reel

There shall be leader-tape(cover tape) and trailer-tape (empty tape) as follows.



10.6 Marking for reel

Customer part number, MURATA part number, Inspection number(*1), RoHS marking(*2), Quantity etc · · ·

*1) < Expression of Inspection No.>

□□ <u>OOOO</u> <u>×××</u> (1) (2) (3)

(1) Factory Code

(2) Date F

First digit : Year / Last digit of year

Second digit : Month / Jan. to Sep. \rightarrow 1 to 9, Oct. to Dec. \rightarrow O, N, D

Third, Fourth digit : Day

(3) Serial No.

*2) « Expression of RoHS marking »


ROHS $-\underline{Y}$ ($\underline{\triangle}$) (1) (2)

- (1) RoHS regulation conformity
- (2) MURATA classification number

10.7 Marking for Outside package (corrugated paper box)

Customer name, Purchasing order number, Customer part number, MURATA part number, RoHS marking (*2), Quantity, etc \cdots

10.8. Specification of Outer Case



Outer Case	e Dimension	ıs (mm)	Standard Reel Quantity
W	D	Н	in Outer Case (Reel)
186	186	93	5

Above Outer Case size is typical. It depends on a quantity of an order.

11. A Caution

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (6) Transportation equipment (vehicles, trains, ships, etc.)
- (2) Aerospace equipment
- (7) Traffic signal equipment
- (3) Undersea equipment
- (8) Disaster prevention / crime prevention equipment
- (4) Power plant control equipment
- (9) Data-processing equipment
- (5) Medical equipment
- (10) Applications of similar complexity and /or reliability requirements to the applications listed in the above



12. Notice

This product is designed for solder mounting. (Reflow soldering only)


Please consult us in advance for applying other mounting method such as conductive adhesive.

12.1 Land pattern designing (Reflow Soldering)

Recommended land pattern for reflow soldering is as follows:

It has been designed for Electric characteristics and solderability.

Please follow the recommended patterns. Otherwise, their performance which includes electrical performance or solderability may be affected, or result to "position shift" in soldering process.



12.2 Flux, Solder

Flux	 Use rosin-based flux. Don't use highly acidic flux with halide content exceeding 0.2(wt)% (chlorine conversion value). Don't use water-soluble flux.
Solder	 Use Sn-3.0Ag-0.5Cu solder Standard thickness of solder paste : 100μm to 150μm

Other flux (except above) Please contact us for details, then use.


12.3 soldering conditions (Reflow)

Pre-heating should be in such a way that the temperature difference between solder and product surface is limited to 100°C max. Cooling into solvent after soldering also should be in such a way that the temperature difference is limited to 100°C max.

Insufficient pre-heating may cause cracks on the product, resulting in the deterioration of product quality.

• Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.



	Standard Profile	Limit Profile	
Pre-heating	150~180	°C 、90s±30s	
Heating	above 220°C、30s∼60s	above 230°C、60s max.	
Peak temperature	245±3°C	260°C,10s	
Cycle of reflow	2 times	2 time	

Reference Only

12.4 Reworking with soldering iron.

The following conditions must be strictly followed when using a soldering iron.


Pre-heating	150°C,1 min
Tip temperature	350°C max.
Soldering iron output	80W max.
Tip diameter	ϕ 3mm max.
Soldering time	3(+1,-0)s
Times	2 times

Note: Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the products due to the thermal shock.

12.5 Product's location

The following shall be considered when designing and laying out P.C.B.'s.

(1) P.C.B. shall be designed so that products are not subject to the mechanical stress due to warping the board.




Products shall be located in the sideways direction to the mechanical stress.


(2) Components location on P.C.B. separation.

It is effective to implement the following measures, to reduce stress in separating the board. It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.

Contents of Measures	Stress Level
(1) Turn the mounting direction of the component parallel to the board separation surface.	A > D*1
(2) Add slits in the board separation part.	A > B
(3) Keep the mounting position of the component away from the board separation surface.	A > C



- *1 A > D is valid when stress is added vertically to the perforation as with Hand Separation. If a Cutting Disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.
- (3) Mounting Components Near Screw Holes
 When a component is mounted near a screw hole,
 it may be affected by the board deflection that occurs
 during the tightening of the screw. Mount the component
 in a position as far away from the screw holes as possible.





12.6 Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1) Cleaning temperature shall be limited to 60°C max.(40°C max for IPA.)
- (2) Ultrasonic cleaning shall comply with the following conditions with avoiding the resonance phenomenon at the mounted products and P.C.B.

Power: 20 W / I max. Frequency: 28kHz to 40kHz Time: 5 minutes max.

- (3) Cleaner
 - 1. Alternative cleaner
 - · Isopropyl alcohol (IPA)
 - 2. Aqueous agent
 - PINE ALPHA ST-100S
- (4) There shall be no residual flux and residual cleaner after cleaning.

In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.

(5) Other cleaning

Please contact us.

12.7 Resin coating

The inductance value may change due to high cure-stress of resin to be used for coating/molding products.

An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating condition etc. Some resin contains some impurities or chloride possible to generate chlorine by hydrolysis under some operating condition may cause corrosion of wire of coil, leading to open circuit.

So, please pay your careful attention when you select resin in case of coating/molding the products with the resin.

Prior to use the coating resin, please make sure no reliability issue is observed by evaluating products mounted on your board.

12.8 Caution for use

- Sharp material such as a pair of tweezers or other material such as bristles of cleaning brush, shall not be touched to the winding portion to prevent the breaking of wire.
- · Mechanical shock should not be applied to the products mounted on the board to prevent the breaking of the core.

12.9 Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the product.

Bending

Twisting



12.10 Storage and Handling Requirements

(1) Storage period

Use the products within 12 months after delivered.

Solderability should be checked if this period is exceeded.

- (2) Storage conditions
 - Products should be stored in the warehouse on the following conditions.

Temperature: -10 ~ 40°C

Humidity : 15 to 85% relative humidity No rapid change on temperature and humidity

The electrode of the products is coated with solder. Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization of electrode, resulting in poor solderability.

- Products should not be stored on bulk packaging condition to prevent the chipping of the core and the breaking of winding wire caused by the collision between the products.
- · Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- (3) Handling Condition

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

13. A Note

- (1) Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the reference specifications.
- (3) The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering