



用于电子修复BST-13的长型迷你对角线钳

- ▶ 品牌名称: BEST
- ▶ 型号: BEST-13
- ▶ 类型: 长鼻子
- ▶ 材料: 碳钢
- ▶ 应用程序: 多功能
- ▶ 类型: 长扁嘴钳
- ▶ 材质: 碳钢+ PVC手柄涂层
- ▶ 表面处理: 防锈油
- ▶ 尺寸: 135毫米
- ▶ 包: 12个/箱
- ▶ N.W.: 101g / pc
- ▶ G.W.: 1.42kg / 盒



Features

1. 狭窄的空间工作的理想选择
2. 不同的大小可用
3. 不同的质量可以根据客户的需求定制。

Specification

模型:	BEST-13长鼻子刀
材料:	碳钢+ PVC手柄涂层
热处理:	身体酸化42-50HRC 刀片高频54-62HRC
表面处理:	防锈油
尺寸:	135毫米
包:	12支/盒
N.W.	101克/ PC
毛重:	1.42公斤/盒


PRODUCT DISPLAY



PRODUCT SIZE

Name: Needle-nose pliers
Model: BST-13
Material: 60CR-V
Brand: BEST
Hardness: HRC38-42
Blade Hardness: HRC56-62
Size: 125mm
Range: HRC20

below: hard wire Φ 1.5mm,
 copper wire or aluminum
 wire Φ 0.1-2.0mm
Process: using repeated
 forging, the surface is
 polished after grinding
 and processing by
 precision machining.



PRODUCT DETAILS



Cutting range

- HRC20 below: hard wire Φ 1.5mm, copper wire or aluminum wire Φ 0.1-2.0mm
- Made of high quality alloy steel CR-V
- For family, electronic maintenance, manufacturing and other industries

PRODUCT PHOTOGRAPH



User manual

⚠ Warning

This model is not insulated tools. Please use it when power off.

⚠ Attention


- To protect user safe, please use protective glasses.
- As the cut material will fly out, make sure no one beside you and no easy damaged things beside you, then begin working.
- This product is not a dedicated pressure equipment.
- When stored, please assure the blade at the closed state and can not be touched by children.
- Do not let the plier tip rub something.
- Please do not directly touch the blade part with hand.
- Do not use in cutting hard materials and steel wire, etc.
- Do not use the pliers above its cutting capability and coarse wire.

PRODUCT PACKAGING

WEIGHT:90G



FRONT



FRONT