



Linear Type RDC10 Series

Travel		22mm
Mounting method		Horizontal type
Total resistance		10kΩ
Linearity		±0.5%
Operating life		200,000 cycles
Length of lever		4.5mm
Length of terminal		2mm
Operating temperature range		-30°C to +85°C
Mechanical performance	Operating force	0.25N max.
Electrical performance	Total resistance tolerance	±30%
	Rated voltage	5V DC
Environmental test	Cold	-40°C 240h
	Dry heat	90°C 240h
	Damp heat	60°C, 90 to 95%RH 240h
Minimum order unit (pcs.)	Japan	2,100
	Export	4,200


Dimensions




Mounting Hole Dimensions



Circuit Diagram





Lever Dimensions



Linearity

With rated voltage applied between terminals 1 and 3, the straight line which connects the measured output values VB and VA at specified reference positions B and A is assumed to be an ideal straight line, so that deviation against the ideal straight line when the voltage applied between terminals 1 and 3 is assumed to be 100% can be expressed as a percentage.





Packing Specifications

Tray

Number of packages (pcs.)	s 1 case / Japan	2,100
	1 case / export packing	4,200
Export package measurements (mm)		374×508×302

Soldering Conditions

Reference for Hand Soldering

Tip temperature	350℃ max.
Soldering time	3s max.

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Place your purchase order in N minimum package units (N: integer).
- 3. Ask us for the export packaging unit.
- 4. Products other than those listed in above products are also available. Please contact us for details.
- 5. This products can be used in vehicles.

Although these products are designed to perform over a wide operating temperature range, please ensure that you receive and read the formal delivery specifications before use.