

# Piezoelectronic buzzers

Pin terminal/Lead lines/SMD(Without oscillator circuit)

# PS series

Pin terminal type

**PS12** 

**PS14** 

**PS17** 

**PS19** 

Lead wire type

**PS15** 

SMD type

PST14



### Piezoelectronic buzzers

Product compatible with RoHS directive

Pin terminal/Lead lines/SMD(Without oscillator circuit)

# **Overview of the PS series**


#### **FEATURES**

- O Sounding body(unimorph) that piezo bonded the diaphragm is used, and attach on circuit, and is easy design high performance efficiency piezoelectric buzzer.
- They feature extremely low power consumption in comparison to electromagnetic units.
- O Because these buzzers are designed for external excitation, the same part can serve as both a musical tone oscillator and a buzzer.
- They can be used with automated inserters. Moisture-resistant models are also available.
- The lead wire type(PS1550L40N) with both-sided adhesive tape installed easily is prepared.

#### APPLICATION


Electric ranges, washing machines, computer terminals, various devices that require speech synthesis output.

#### ■ RECOMMENDED OPERATING CIRCUIT EXAMPLE



 $<sup>^*</sup>$  Resistor to do charging and discharging to a piezoelectric element (Value of about 1k $\!\Omega$  is good efficiency).

#### SOUND MEASURING METHOD



RoHS Directive Compliant Product: See the following for more details. https://product.tdk.com/info/en/environment/rohs/index.html



# **Overview of the PS series**

#### **■ PRODUCT LINEUP**

			Outside dimensions			Characteristics		
Туре		Part No.	Outside diameter (mm)	Height [excluding terminal] (mm)	Terminal pitch (mm)	Sound pressure (dB(A)/10cm)	Frequency (kHz)	Input voltage (Vo-P)[rectangular waves]
PS12		PS1240P02BT	ø12.2	6.5	5	70 min.	4	3
1 312		PS1240P02CT3	ø12.2	3.5	5	60 min.	4	3
PS14		PS1440P02BT	ø14	8	5	75 min.	4	3
F314		PS1420P02CT	ø14	11	5	70 min.	2	5
		PS1720P02	ø17	8	10	70 min.	2	3
PS17		PS1740P02E	ø17	7.5	10	75 min.	4	3
		PS1740P02CE	ø17	4.6	10	60 min.	4	3
PS19		PS1927P02	ø19	10.5	20	90 min.	2.7	10
P319	F219	PS1920P02	ø19	10.5	20	80 min.	2	10
PST14	<b>\$</b> \$	PST1423P02	□ 14	(9)	_	84 min.	2.3	24Vp-p (±12V0-p)
PS15	•	PS1550L40N	ø15	1.6	_	Depend on the installation condition	-	20V0-P max.

Туре		Part No.	Application	Features	
PS12		PS1240P02BT	For warning and alarm sounds of home appliances(air condi- tioners, refrigerators, fan forced heaters, cordless telephones, etc.)	Compact/automatic mountable/12.7mm pitch radial taping	
F312		PS1240P02CT3		Thin type/automatic mountable/12.7mm pitch radial taping	
PS14		PS1440P02BT		High sound pressure/automatic mountable/15mm pitch radial taping	
		PS1420P02CT		Low frequency tone/automatic mountable/15mm pitch radial taping	
		PS1720P02		Low frequency tone / High sound pressure	Low frequency tone / High sound pressure
PS17		PS1740P02E		High sound pressure	
		PS1740P02CE		Thin type	
PS19		PS1927P02	- machines, drying machines,	High sound pressure / Water-proof processing element	
P519		PS1920P02		Low frequency tone / Water-proof processing element	
PST14	<b>\$</b> \$	PST1423P02	applicable to automobile equipment	SMD / Taping products	
PS15		PS1550L40N	Digital camera	Thin type / Installation easy	

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.





### PS1240P02BT

#### **FEATURES**

- O Miniature size(ø12.2×T6.5mm).
- O High cost performance.
- O Suitable for automatic radial taping machine (12.7mm-pitch).

#### **SHAPE & DIMENSIONS**











#### **SPECIFICATIONS**

Sound pressure	70dB(A)/10cm min.	[at 4kHz, 3Vo-P rectangular waves, measuring temperature: 25±5°C, humidity: 60±10%]
Operating temperature range	-10 to +70°C	
Storage conditions	+5 to +40°C, 20 to 70	%RH, please use within 6 months
Maximum input voltage	30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit	2500 pieces	[500 pieces/1 reel×5 reels]

#### ■FREQUENCY SOUND PRESSURE CHARACTERISTICS





Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.





### PS1240P02CT3

#### **FEATURES**

- Thin type(ø12.2×T3.5mm).
- O Suitable for automatic radial taping machine (12.7mm-pitch).

#### ■SHAPE & DIMENSIONS










#### **SPECIFICATIONS**

Sound pressure	60dB(A)/10cm min.	[at 4kHz, 3Vo-P rectangular waves, measuring temperature: 25±5°C, humidity: 60±10%]
Operating temperature range	−10 to +70°C	
Storage conditions	+5 to +40°C, 20 to 70°	%RH, please use within 6 months
Maximum input voltage	30V <sub>0-Р</sub> max.	[without DC bias]
Minimum delivery unit	2500個	[500 pieces/1 reel×5 reels]







Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.





### PS1440P02BT


#### **FEATURES**

- O High sound pressure.
- Miniature size(ø14×T8mm).
- O Suitable for automatic radial taping machine (15mm-pitch).

#### **SHAPE & DIMENSIONS**













#### **SPECIFICATIONS**

Sound pressure	75dB(A)/10cm min. [at 4kHz, 3Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]		
Operating temperature range	-10 to +70°C		
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months		
Maximum input voltage	30Vo-P max. [without DC bias]		
Minimum delivery unit	1750 pieces [350 pieces/1 reel×5 reels]		

#### FREQUENCY SOUND PRESSURE CHARACTERISTICS

#### ☐SINE WAVE DRIVE









### PS1420P02CT


#### **FEATURES**

- O Low frequency tone(2kHz).
- O Suitable for automatic radial taping machine (15mm-pitch).

#### ■SHAPE & DIMENSIONS









Dimensions in mm




#### **SPECIFICATIONS**

Sound pressure	70dB(A)/10cm min.	[at 2kHz, 5Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]	
Operating temperature range	−10 to +70°C		
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months		
Maximum input voltage	30V₀-p max.	[without DC bias]	
Minimum delivery unit	1750 pieces	[350 pieces/1 reel×5 reels]	







Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




### PS1720P02

#### **FEATURES**

- O Low frequency tone.
- O High sound pressure.

#### **SHAPE & DIMENSIONS**





Tolerance: ±0.3 Dimensions in mm



#### **SPECIFICATIONS**

Sound pressure	70dB(A)/10cm min. [at 2kHz, 3Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]
Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	30Vo-P max. [without DC bias]
Minimum delivery unit	1500 pieces





Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




### PS1740P02E

#### **FEATURES**

O High sound pressure.

#### **SHAPE & DIMENSIONS**









#### **SPECIFICATIONS**

Sound pressure	75dB(A)/10cm min. [at 4kHz, 3Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]
Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	30Vo-P max. [without DC bias]
Minimum delivery unit	1500 pieces

#### FREQUENCY SOUND PRESSURE CHARACTERISTICS

#### □SINE WAVE DRIVE





Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




### PS1740P02CE

#### **FEATURES**

O Thin type.

#### **SHAPE & DIMENSIONS**









Tolerance: ±0.3 Dimensions in mm


#### **SPECIFICATIONS**

Sound pressure	60dB(A)/10cm min. [at 4kHz, 3Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]
Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	30Vo-P max. [without DC bias]
Minimum delivery unit	1500 pieces

#### FREQUENCY SOUND PRESSURE CHARACTERISTICS







Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




### PS1920P02

#### **FEATURES**

- O Low frequency tone(2kHz).
- O Piezo element is coated with water proof processing.


#### **SHAPE & DIMENSIONS**






#### **SPECIFICATIONS**

Sound pressure	80dB(A)/10cm min. [at 2kHz, 10Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]
Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	20Vo-P max. [without DC bias]
Minimum delivery unit	600 pieces







Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




### PS1927P02

#### **FEATURES**

- O High sound pressure.
- O Piezo element is coated with water proof processing.

#### **SHAPE & DIMENSIONS**







#### **SPECIFICATIONS**

Sound pressure	90dB(A)/10cm min. [at 2.7kHz, 10Vo-P rectangular waves, measuring temperature:25±5°C, humidity:60±10%]
Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	20Vo-P max. [without DC bias]
Minimum delivery unit	600 pieces

#### ■ FREQUENCY SOUND PRESSURE CHARACTERISTICS





Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.




# **SMD type PST14**


### PST1423P02

#### **FEATURES**

- O These high reliability electromagnetic buzzers are applicable to automobile equipment.
- O Suitable for surface mount process(SMD). Stand up to reflow process twice.


#### **SHAPE & DIMENSIONS**







#### ■ RECOMMENDED LAND PATTERN




Dimensions in mm


#### **SPECIFICATIONS**

☐SINE WAVE DRIVE

Sound pressure	84dB(A)/10cm min [at 2.3kHz 24VP-P (±12V) rectangular waves, measuring temperature:25±5°C, humidity:60±10%]
Operating temperature range	-40 to +85°C
Storage conditions	Store the environment of the room temperature 5 to 40°C, humidity 20 to 70%RH, please use within the 6 months.
Maximum input voltage	32V <sub>P-P</sub> (±16V) max
Minimum ordering unit	1250 pieces

#### **■ FREQUENCY SOUND PRESSURE CHARACTERISTICS**






Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.



# **SMD type PST14**

### PST1423P02

#### ■ RECOMMENDED REFLOW PROFILE



Preheating			Soldering	g	Peak	Peak		
Temp.		Time	Temp.	Time	Temp.	Time		
T1	T2	t1	Т3	t2	T4	t3		
150°C	180°C	60 to 120s	230°C	20 to 40s	250 to 260°C	5s max.		




# **SMD type PST14**

### PST1423P02


#### **PACKAGING STYLE**

#### **TAPING SPECIFICATIONS**




В	С	D	N	R	W1	
2.5±0.3	ø13.2±0.3	21.0±0.4	ø100±2	(R1.15)	24.5+2/-0	

#### **PRODUCTS INSTALL STATUS**



Dimensions in mm

#### □Carrier tape dimensions



Dimensions in mm

F	G	Т	W	A0	B0	D0	D1	E1	E2	K0	P0	P1	P2
11.5±0.1	(3.5)	0.5±0.05	24.0±0.3	14.5±0.2	14.5±0.2	ø1.5+0.1/-0	ø1.5±0.1	17.5±0.1	22.25+0.2/-0	9.5±0.1	4.0±0.1	20.0±0.1	2.0±0.1




# **Lead wire type PS15**

#### PS1550L40N

#### **FEATURES**

- Miniature size(ø15×T1.6mm).
- O High cost performance.
- O The installation of this type is easy with both-sided tape.
- This product adopts an excellent both-sided adhesive tape in bonding and the sound characteristic.

#### ■ SHAPE & DIMENSIONS






#### **SPECIFICATIONS**


Operating temperature range	-10 to +70°C
Storage conditions	+5 to +40°C, 20 to 70%RH, please use within 6 months
Maximum input voltage	20Vo-P max. [without DC bias]
Minimum delivery unit	4000 pieces

#### FREQUENCY SOUND PRESSURE CHARACTERISTICS

#### ☐SINE WAVE DRIVE



#### □SQUARE WAVE DRIVE



\* The frequency characteristic changes depending on the case shape and the installation method.



### REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

### SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

### REMINDERS Please be sure to read the specifications of TDK electromagnetic buzzer(hereinafter referred to as "the buzzer") before use. On not apply DC bias to the piezoelectric buzzer; otherwise insulation resistance may become low and affect the performance. On not supply any voltage higher than applicable to the piezoelectric buzzer. On Do not use the piezoelectric buzzer outdoors. It is designed for indoor use. If the piezoelectric buzzer has to be used outdoors, provide it with waterproofing measures; it will not operate normally if subjected to moisture. On ont wash the piezoelectric buzzer with solvent or allow gas to enter it while washing; any solvent that enters it may stay inside a long time and damage it. O A piezoelectric ceramic material of approximately 100μm thick is used in the sound generator of the buzzer. Do not press the sound generator through the sound release hole otherwise the ceramic material may break. Do not stack the piezoelectric buzzers without packing. On not apply any mechanical force to the piezoelectric buzzer; otherwise the case may deform and result in improper operation. On not place any shielding material or the like just in front of the sound release hole of the buzzer; otherwise the sound pressure may vary and result in unstable buzzer operation. Make sure that the buzzer is not affected by a standing wave or the like. O Be sure to solder the buzzer terminal at 350°C max.(80W max.)(soldering iron trip) within 5 seconds using a solder containing silver. O Avoid using the piezoelectric buzzer for a long time where any corrosive gas H2S, etc.) exists; otherwise the parts or sound generator may corroded and result in improper operation. Be careful not to drop the piezoelectric buzzer.

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

High safety and reliability is needed, and or, there is fear that failure, wrong movement, failure of product damages and worldly goods etc related to life and health of people, or do not use for equipment(as nuclear power equipment-?automobile?-aircraft-?medical?

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)

device) with fear that significant influence is had socially.

- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications