

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

ALL RIGHTS RESERVED.

LOC
ALDIST
2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J5	REVISED PER ECR-16-008286	25JUL2016	BW	RS

NOTES:

Bemerkungen:

- 1 2-6µm Sn OVER Ni IN CRIMP-AREA
2-6µm Sn über Ni in der Crimpzone
- 2 0.8µm Au OVER Ni IN CONTACT-AREA
0.8µm Au über Ni in der Kontaktzone
- 3 SUITABLE FOR Ø1.0-2.5mm
Für Isolations Ø1.0-2.5mm geeignet
- 4 0.8µm Au OVER 1.3µm Ni ON INSIDE OF WIRE BARREL AND CONTACT AREA
0.8µm Au über 1.3µm Ni in der Drahtcrimp und Kontaktzonen, sonst 1.3µm Ni

SUPERSEDED BY 350851-7	926895-7	926884-7	BRASS	1 2
SUPERSEDED BY 350851-7	926895-6	926884-6	PHOS BRONZE	1 2
	926895-3	926884-3	PHOS BRONZE	PRE-TIN
OBSOLETE	926895-2	926884-2	BRASS	4
	926895-1	926884-1	BRASS	PRE-TIN
	LOOSE PIECE	PART NO.	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. Skoda	07NOV2005	TE Connectivity	
DIMENSIONS: mm		CHK R. Vlcek	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	-	NAME UNIVERSAL MNL SOCKET 0.2-0.8 mm ² WIRE RANGE	
0 PLC ±0.2		PRODUCT SPEC 108-1031	-	SIZE A3	
1 PLC ±0.2		APPLICATION SPEC 114-18011	-	CAGE CODE 00779	DRAWING NO 926884
2 PLC ±0.2		WEIGHT -	-	RESTRICTED TO -	
3 PLC ±		CUSTOMER DRAWING	-	SCALE 5:1	SHEET 1 OF 1
4 PLC ±				REV J5	
ANGLES ±°					
FINISH SEE TABLE					

1470-19 (3/11)