





Silicon N-Channel Power MOSFET

## PIN Connection TO-220F

$V_{DSS}$	600	V
$I_D$	10	A
$P_D (T_C=25^\circ C)$	125	W
$R_{DS(ON)}$	0.63	$\Omega$



## Marking Diagram



Y = Year  
 A = Assembly Location  
 WW = Work Week  
 FIR10N60F = Specific Device Code

## Features

- Fast Switching
- ESD Improved Capability
- Low Gate Charge (Typical Data:60nC)
- Low Reverse transfer capacitances(Typical:28pF)
- 100% Single Pulse avalanche energy Test

## Applications

Power switch circuit of adaptor and charger.

## Absolute (Tc= 25°C unless otherwise specified)

Symbol	Parameter	Rating	Units
$V_{DSS}$	Drain-to-Source Voltage	600	V
$I_D$	Continuous Drain Current	10	A
	Continuous Drain Current $T_C = 100^\circ C$	6.4	A
$I_{DM}^{a1}$	Pulsed Drain Current	40	A
$V_{GS}$	Gate-to-Source Voltage	$\pm 20$	V
$E_{AS}^{a2}$	Single Pulse Avalanche Energy	300	mJ
$E_{AR}^{a1}$	Avalanche Energy ,Repetitive	30	mJ
$I_{AR}^{a1}$	Avalanche Current	8.0	A
$dv/dt^{a3}$	Peak Diode Recovery dv/dt	5.5	V/ns
$P_D$	Power Dissipation	125	W
	Derating Factor above 25°C	1.0	W/°C
$V_{ESD(G-S)}$	Gate source ESD (HBM-C= 100pF, R=1.5k $\Omega$ )	4000	V
$T_J, T_{stg}$	Operating Junction and Storage Temperature Range	150, -55 to 150	°C
$T_L$	Maximum Temperature for Soldering	300	°C

**Electrical Characteristics** (Tc= 25°C unless otherwise specified)

<b>OFF Characteristics</b>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
V <sub>DSS</sub>	Drain to Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	600	--	--	V
Δ BV <sub>DSS</sub> / Δ T <sub>J</sub>	Bvdss Temperature Coefficient	I <sub>D</sub> =250uA, Reference 25°C	--	0.74	--	V/°C
I <sub>DSS</sub>	Drain to Source Leakage Current	V <sub>DS</sub> = 600V, V <sub>GS</sub> = 0V, T <sub>a</sub> = 25°C	--	--	25	μA
		V <sub>DS</sub> = 480V, V <sub>GS</sub> = 0V, T <sub>a</sub> = 125°C	--	--	250	
V <sub>GSO</sub>	Gate Source Breakdown Voltage	I <sub>GS</sub> = ±1mA (Open Drain)	±20			V
I <sub>GSS(F)</sub>	Gate to Source Forward Leakage	V <sub>GS</sub> = +20V	--	--	10	μA
I <sub>GSS(R)</sub>	Gate to Source Reverse Leakage	V <sub>GS</sub> = -20V	--	--	-10	μA

<b>ON Characteristics</b>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
R <sub>DS(ON)</sub>	Drain-to-Source On-Resistance	V <sub>GS</sub> =10V, I <sub>D</sub> =5A	--	0.63	0.75	Ω
V <sub>GS(TH)</sub>	Gate Threshold Voltage	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	2.0	3.0	4.0	V
Pulse width tp ≤ 380μs, δ ≤ 2%						

<b>Dynamic Characteristics</b>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
g <sub>fs</sub>	Forward Transconductance	V <sub>DS</sub> =15V, I <sub>D</sub> =5.0A	--	8.5	--	S
C <sub>iss</sub>	Input Capacitance	V <sub>GS</sub> = 0V V <sub>DS</sub> = 25V f = 1.0MHz	--	1430	--	pF
C <sub>oss</sub>	Output Capacitance		--	160	--	
C <sub>rss</sub>	Reverse Transfer Capacitance		--	28	--	

<b>Resistive Switching Characteristics</b>						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
t <sub>d(ON)</sub>	Turn-on Delay Time	I <sub>D</sub> = 10.0A V <sub>DD</sub> = 300V V <sub>GS</sub> = 10V R <sub>G</sub> = 4.7Ω	--	20	--	ns
t <sub>r</sub>	Rise Time		--	20	--	
t <sub>d(OFF)</sub>	Turn-Off Delay Time		--	55	--	
t <sub>f</sub>	Fall Time		--	30	--	
Q <sub>g</sub>	Total Gate Charge	I <sub>D</sub> = 10.0A V <sub>DD</sub> = 480V V <sub>GS</sub> = 10V	--	60	70	nC
Q <sub>gs</sub>	Gate to Source Charge		--	12	--	
Q <sub>gd</sub>	Gate to Drain ("Miller") Charge		--	28	--	







Source-Drain Diode Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$I_S$	Continuous Source Current (Body Diode)		--	--	10	A
$I_{SM}$	Maximum Pulsed Current (Body Diode)		--	--	40	A
$V_{SD}$	Diode Forward Voltage	$I_S=10.0A, V_{GS}=0V$	--	--	1.5	V
$t_{rr}$	Reverse Recovery Time	$I_S=10.0A, T_j = 25^\circ C$ $dI_F/dt=100A/us,$ $V_{GS}=0V$	--	600	--	ns
$Q_{rr}$	Reverse Recovery Charge		--	4.3	--	nC
$I_{RRM}$	Reverse Recovery Current		--	13	--	A
Pulse width $t_p \leq 380\mu s, \delta \leq 2\%$						

Symbol	Parameter	Typ.	Units
$R_{\theta JC}$	Junction-to-Case	1.0	$^\circ C/W$
$R_{\theta JA}$	Junction-to-Ambient	62	$^\circ C/W$

<sup>a1</sup>: Repetitive rating; pulse width limited by maximum junction temperature


<sup>a2</sup>:  $L=10.0mH, I_P=10A, Start T_j=25^\circ C$

<sup>a3</sup>:  $I_{SD}=10A, di/dt \leq 100A/us, V_{DD} \leq BV_{DS}, Start T_j=25^\circ C$


**Electrical Characteristic Curves**
**Fig. 1  $I_D - V_{DS}$** 

**Fig. 2  $I_D - V_{GS}$** 

**Fig. 3  $R_{DS(on)} - I_D$** 

**Fig. 4  $I_S - V_{SD}$** 

**Fig. 5 Capacitance -  $V_{DS}$** 

**Fig. 6  $V_{GS} - Q_G$** 


## Electrical Characteristic Curves


**Fig. 7  $V_{DSS} - T_J$**




**Fig.8  $R_{DS(on)} - T_J$**




**Fig. 9  $I_D - T_C$**




**Fig. 10 Safe Operating Area**




**Fig. 10 Gate Charge Test Circuit & Waveform**




**Fig. 11 Resistive Switching Test Circuit & Waveform**




**Fig. 12 E<sub>AS</sub> Test Circuit & Waveform**



**Fig. 13 Diode Reverse Recovery Time Test Circuit & Waveform**


## Package Dimensions

### TO-220F



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH
3. 221D-01 THRU 221D-02 OBSOLETE, NEW STANDARD 221D-03.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.617	0.635	15.67	16.12
B	0.392	0.419	9.96	10.63
C	0.177	0.193	4.50	4.90
D	0.024	0.039	0.60	1.00
F	0.116	0.129	2.95	3.28
G	0.100 BSC		2.54 BSC	
H	0.118	0.135	3.00	3.43
J	0.018	0.025	0.45	0.63
K	0.503	0.541	12.78	13.73
L	0.048	0.058	1.23	1.47
N	0.200 BSC		5.08 BSC	
Q	0.122	0.138	3.10	3.50
R	0.099	0.117	2.51	2.96
S	0.092	0.113	2.34	2.87
U	0.239	0.271	6.06	6.88